

Farnell InOne Product Submission – Cooper B-Line

EC Product Range



EC Range 19" Free-standing Equipment Cabinet

The new EC range from Cooper B-Line combines quality, functionality and style in a cost effective enclosure solution for cabling and hardware installations.

- 2 door styles available - lockable, aesthetic glass with side ventilation or plain steel
- Fully adjustable 19" mounting angles
- Open base design with optional plinth
- Lockable lift off side panels
- Interchangeable top panels
- Jacking Feet for correct levelling
- Compatible with Cooper B-Line Access and Fusion accessories
- Flat packed for easy movement / storage

Part No. (Flat Packed)	Description
E2766K1NGSPPVG	27U Cabinet 600W, 600D
E2768K1NGSPPVG	27U Cabinet 600W, 800D
E4266K1NGSPPVG	42U Cabinet 600W, 600D
E4268K1NGSPPVG	42U Cabinet 600W, 800D
E4288K1CGSPPVG	42U Cabinet 800W, 800D
EGD276G	EC Ventilated Glass Door, 27U, 600W
EGD426G	EC Ventilated Glass Door, 42U, 600W
EGD428G	EC Ventilated Glass Door, 42U, 800W
ESD276G	EC Steel Door, 27U, 600W
ESD426G	EC Steel Door, 42U, 600W
ESD428G	EC Steel Door, 42U, 800W



Base Options

EC cabinets come with a multifunctional corner plate with jacking feet fitted as standard. The plate can be used to bolt the cabinet to a floor, or alternatively it can also be fitted with castors.

An optional plinth kit is also available which covers the raised base area for a neat finish. The plinth plates can be individually removed to allow cable access if required.

Castors can be added to provide easy cabinet mobility. Jacking feet (already fitted) then secure the cabinet into position

Part Codes	
ECC	Set of 4 Castors
ECMP66	Plinth Kit, 600W x 600D
ECMP68	Plinth Kit, 600W x 800D
ECMP88	Plinth Kit, 800W x 800D




Earth Kit

Provides earth continuity for any EC cabinet


Part No	Description
EEK	EC Earth Kit

EC Cabinet Assembly Instructions


Step 1




Step 2




Step 3




Step 4




**Step 4a
(800 Wide Only)**



Step 5



**Step 6
(Side panels)**



**Step 7
(Doors)**

