

IE-XM-RJ45/IDC-B

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



Weidmüller terminal rail outlets should be your first choice when you need to connect

- installation cables,
- RJ45 cables,
- FO cables with ST connectors.

Features:

- IP 20
- Cat.6
- suitable for mounting on TS35 terminal rail
- 1 E (5.08 mm) pitch dimension to DIN 43880
- inspection window for labelling

General ordering data

Order No.	8891980000
Part designation	IE-XM-RJ45/IDC-B
Version	Terminal rail outlet, RJ45 module EIA/TIA 568 B, IP 20, Cat.6 (IEC 11801)
GTIN (EAN)	4032248636938
Qty.	1 pc(s).

IE-XM-RJ45/IDC-B

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com

Technical data

temperature

Ambient temperature (operational)

Connection elements

Connection 1	RJ45	Connection 2	IDC
Configuration	Inspection window for labelling 1 TE pitch dimension acc. to DIN 43880. insta-compatible	Protection class	IP 20
Housing main material	PA 66 UL 94: V-0	Colour	light grey
Type of mounting	TS 35	Category	Cat.6 (IEC 11801)
Wiring	Colour-coded pin assignment to EIA/TIA T568 A	Plugging cycles	750 plugging cycles for plugs to IEC 60603-7

Approvals

Approvals institutes GERMLLOYD; GOSTME25

Classifications

eClass 5.1 27-25-05-04 eClass 6.0 27-25-05-04