


## Weidmüller IE-LINE

### Mounting rail outlet FO

- IP 20
- TS35



### Mounting rail outlet FO

#### Application:

Weidmüller mounting rail outlets should be your first choice in the switchgear cabinet when you need to connect

- fibre optic cable with SC-Duplex-, SCRJ- and LC-duplex connectors.

#### Variations:

- 8946970000: SC-Duplex Multi-mode
- 8946980000: SC-Duplex Single-mode
- 8946990000: SCRJ Multi-mode
- 8947000000: SCRJ Single-mode
- 8947010000: LC-Duplex Multi-mode
- 8947020000: LC-Duplex Single-mode

### Ordering data

Fibre-optic		Type	Order No.
	LCD multi-mode	IE-TO-LCD-MM	8947010000
	LCD single-mode	IE-TO-LCD-SM	8947020000
	SCD multi-mode	IE-TO-SCD-MM	8946970000
	SCD single-mode	IE-TO-SCD-SM	8946980000
	SCRJ multi-mode	IE-TO-SCRJ-MM	8946990000
	SCRJ single-mode	IE-TO-SCRJ-SM	8947000000

### Accessories

markers		Type	Order No.
	9*11 mm, white	ESG 9/11K MC NEUTRAL	1857440000
Labels			
	9*11 mm, white	LM MT DIN A5 9/11 WS	1964070000
	9*11 mm, blue	LM MT DIN A5 9/11 BL	1964100000
	9*11 mm, yellow	LM MT DIN A5 9/11 GE	1964110000
	9*11 mm, grey	LM MT DIN A5 9/11 GR	1964080000
	9*11 mm, green	LM MT DIN A5 9/11 GN	1964120000
	9*11 mm, orange	LM MT DIN A5 9/11 OR	1964090000
Note			

### Technical data

Protection class	IP 20
Housing material	PA UL94 VO
Colour	light grey (RAL 7035)
Installation	for terminal rail TS35
Plugging cycles	1000 plugging cycles for plugs to IEC 61754
Operating temperature, min. / max.	-25 °C / 70 °C

Note: