

# GP Batteries

**Data Sheet**

**Model No.: GP24AU**

## NO MERCURY ADDED

Description : Mercury Free Alkaline Manganese Battery, AAA Size

Chemical System : Alkaline Manganese

Nominal Voltage : 1.5 Volts

Nominal Dimensions: Ø10.5 mm x 44.5 mm

Terminals : Protruded positive(+) and flat negative(-) contacts

Jacket : Foil jacket


Applications : All electronic devices, e.g. toys, photographic equipment, data banks, calculators, audio appliances, remote controls, paging machines.

Warranty Period : 36 months

Average Weight : 11.4g

### Typical Service Life:

Discharge Resistance	Discharge Condition	End Point Voltage	Service Life
20 Ohms	24 Hrs/ Day	0.9V	16.5 Hrs



### Cross References:

GP	JIS	IEC	Eveready	Duracell	Varta
24AU	LR03	LR03	E92	MX2400	4003

