


Nylon Terminal Strips 12 Way

Features

- Moulded from PA66
- Natural colour
- Easily cut to size
- UL, CSA, IMQ, KEMA, VDE, SEMKO, DEMKO, OVE, SEV depending on series
- Available with or without wire protectors
- Self extinguishing
- Can be supplied pre-cut to specified number of poles



Specification

Voltage (max)	450Vac
Working temperature	120 °C
Short period	160 °C
No. of poles	12
Moulding	UL94-V2 Self-extinguishing
Conducting bush	Brass
Screws	6µ Zinc, colour passivated and tropicalised
Wire protectors	Stainless steel

Notes: UL94-VO (160 °C) flame retardant version available on request. Available pre-cut to length for volume orders.

Type No.	Size	Wire Protector	Cable Acceptance	Length	Width	Height	Fixing Holes	Insert diameter	Fixing hole pitch	Screw	Max Current
CTBS431/12W	8mm/6A	No	4.0mm ²	93.5mm	16.4mm	14.7mm	2.8mm	2.9mm	8.0mm	M 3.0	24A
CTBS431/12	8mm/6A	Yes	2.5mm ²	9.35mm	16.4mm	14.7mm	2.8mm	2.9mm	8.0mm	M 3.0	24A
CTBS432/12W	10mm/10A	No	4.0mm ²	116.0mm	18.1mm	16.0mm	3.2mm	3.0mm	10.0mm	M 3.0	24A
CTBS432/12	10mm/10A	Yes	2.5mm ²	116.0mm	18.1mm	16.0mm	3.2mm	3.0mm	10.0mm	M 3.0	24A
CTBS433/12W	10mm/10A	No	4.0mm ²	116.7mm	20.1mm	17.6mm*	3.2mm	3.2mm	10.0mm	M 3.0	32A
CTBS433/12	10mm/10A	Yes	2.5mm ²	116.7mm	20.1mm	17.6mm*	3.2mm	3.2mm	10.0mm	M 3.0	32A
CTBS434/12W	12mm/16A	No	10.0mm ²	139.8mm	23.1mm	21.0mm	3.2mm	4.0mm	12.0mm	M 3.5	41A
CTBS434/12	12mm/16A	Yes	6.0mm ²	139.8mm	23.1mm	21.0mm	3.2mm	4.0mm	12.0mm	M 3.5	41A
CTBS435/12W	14.5mm/32A	No	16.0mm ²	174.0mm	31.6mm	24.6mm	4.2mm	4.5mm	14.5mm	M 4.0	57A
CTBS435/12	14.5mm/32A	Yes	10.0mm ²	174.0mm	31.6mm	24.6mm	4.2mm	4.5mm	14.5mm	M 4.0	57A
CTBS438/12W	19.5mm/64A	No	25.0mm ²	209.0mm	37.2mm	33.6mm	4.5mm	7.4mm	18mm	M 5.0	101A


Notes: Voltage and current rating vary with approvals

*20mm for raised base versions CTBS433/12WR and CTBS433/12R

Pluggable Terminal Strips Plug in

Features

- Moulded from PLP
- White colour
- Easily cut to size
- Self extinguishing
- IMQ, CE Approved



Specification

Voltage (max)	450Vac
Working temperature	85 °C
Short period	110 °C
No. of poles	12
Moulding	UL94-V2 Self-extinguishing Polypropylene
Conducting bush	Brass
Screws	6µ Zinc, colour passivated and tropicalised

Notes: UL94-VO (160 °C) flame retardant version available on request. Available pre-cut to length for volume orders.

Type No.	Size	Length	Width	Height	Fixing Holes	Insert diameter	Fixing hole pitch	Screw	Max Current
CTBS431/12M	8mm/6A	94.9mm	16.4mm	14.7mm	2.8mm	2.9mm	8.0mm	M3	17.5A
CTBS431/12F	8mm/6A	94.9mm	16.4mm	14.7mm	2.8mm	2.9mm	8.0mm	M3	17.5A
CTBS433/12M	10mm/10A	116.5mm	20.1mm	16.6mm	3.2mm	3.4mm	10.0mm	M3	24A
CTBS433/12F	10mm/10A	116.5mm	20.1mm	16.6mm	3.2mm	3.4mm	10.0mm	M3	24A
CTBS434/12M	12mm/10A	139.8mm	23.2mm	20.1mm	3.2mm	4.3mm	12.0mm	M3.5	57A
CTBS434/12F	12mm/10A	139.8mm	23.2mm	20.1mm	3.2mm	4.3mm	12.0mm	M3.5	57A