

Junior 3/8" range.

▶ Ratchets 3/8"

3/8" "Junior" ratchets

Facom round head ratchets

⇒ J.171
● ● ○ ○ ○ ○



⇒ J.161
○ ● ○ ○ ○ ○



⇒ J.151A
○ ○ ○ ○ ○ ○



⇒ J.174
● ● ● ○ ○ ○



⇒ J.153A
○ ● ● ○ ○ ●



⇒ J.161E
○ ● ○ ● ● ○



⇒ J.155A
○ ● ○ ○ ○ ●



⇒ J.157A
○ ● ● ○ ○ ●



⇒ J.158A
○ ● ● ○ ○ ●



⇒ J.159A
○ ● ● ○ ○ ●



The solution for congested spaces

Compact :

- The Facom ratchet mechanism ensures a very compact round head design.

Precise :

- 72 tooth mechanism gives increments of only 5°.



High performance :

- Meet the requirements of ISO 3315, DIN 312 NF ISO 3315.

Metal grip ratchets

- Ideal for environments where PVC grips are vulnerable to solvent attack.


⇒ J.156

Ratchet attachment.
Female drive :  3/8"
Male drive :  3/8".



Facom VSE 1000 V insulated ratchets



See the "VSE" series range of 1000 V insulated tools on page  661

