

## ▶ multi-blade screwdrivers

**New**

### AM Multi-blade sets

- Compact set offering a selection of drive patterns.
- Double-ended blades.
- Handle fits 1/4" hexagon shank on blades.
- Blade retaining spring within handle.
- AM.1 comes in a plastic box.
- AM.2-AM.3-AM.4 come in a compact wallet.

# Protwist®



Icon	Handle	●	⊕	⊗	⊛	Torx Plus® Tamper resistant	Qty	ΔΔ g
<b>AM.1</b>	AM.D	AMZ.S 4-6,5 AMZ.S 5,5-7	AMZ.P 0-1 AMZ.P 2-3			AMZ.X 10-15 AMZ.X 20-25 AMZ.X 30-40	16	775
<b>AM.2</b>	AM.D	AMZ.S 4-6,5 AMZ.S 5,5-7	AMZ.P 1-2	AMZ. D1-2			5	350
<b>AM.3</b>	AM.D	AMZ.S 4-6,5 AMZ.S 5,5-7	AMZ.P 1-2			AMZ.X 10-15 AMZ.X 20-25 AMZ.X 30-40	7	450
<b>AM.4</b>	AM.D	AMZ.S 4-6,5 AMZ.S 5,5-7				AMZ.XRP 10-15 AMZ.XRP 20-25 AMZ.XRP 30-40	5	350

### AMZ Reversible blades

- Length 175 mm.
- Length outside the handle 125 mm.
- Chrome finish.

ΔΔ : 40 g.

Icon	Pattern	Contents
<b>AMZ.S4-6,5</b>	●	0,8 x 4 - 1,2 x 6,5
<b>AMZ.S5,5-7</b>	●	1 x 5,5 - 1,5 x 7
<b>AMZ.PO-1</b>	⊕	PH.0 - PH.1
<b>AMZ.P2-3</b>	⊕	PH.2 - PH.3
<b>AMZ.P1-2</b>	⊕	PH.1 - PH.2
<b>AMZ.D0-1</b>	⊗	PZ.0 - PZ.1
<b>AMZ.D2-3</b>	⊗	PZ.2 - PZ.3
<b>AMZ.D1-2</b>	⊗	PZ.1 - PZ.2
<b>AMZ.H2,5</b>	○	2,5
<b>AMZ.H3</b>	○	3
<b>AMZ.H4</b>	○	4
<b>AMZ.H5</b>	○	5
<b>AMZ.H6</b>	○	6
<b>AMZ.X8-9</b>	⊛	T.8 - T.9
<b>AMZ.X10-15</b>	⊛	T.10 - T.15
<b>AMZ.X20-25</b>	⊛	T.20 - T.25
<b>AMZ.X30-40</b>	⊛	T.30 - T.40
<b>AMZ.XRP10-15</b>	Tamper Torx® Plus	TT+10-15
<b>AMZ.XRP20-25</b>	Tamper Torx® Plus	TT+20-25
<b>AMZ.XRP30-40</b>	Tamper Torx® Plus	TT+30-40
<b>AMZ.E</b>		Porte-embout 6 pans 1/4"

