

DATA SHEET



PART NO: S 2171MN

ISSUE NO: 1

CATALOGUE NO: AD-1230RBS2.1

CUSTOMER NO: N/A

DESCRIPTION 12Vdc Regulated 300mA UK Plug Top Adaptor



INPUT VOLTS	230Vac
FREQUENCY	50Hz
MAG CURRENT (max.)	60mA
O/P VOLTS NO LOAD	
O/P VOLTS NO LOAD	12.2Vdc
O/P VOLTS	
O/P CURRENT	
O/P VOLTS	12.0Vdc
O/P CURRENT	300mA
FLASH TEST	3.75KVac
OUTPUT CONNECTOR	2.1x5.5x12mm
OUTPUT POLARITY	Centre +VE
LEAD LENGTH	1.8Mtr
APPROVALS	N/A
LENGTH	81mm
DEPTH	55mm
WIDTH	56.5mm
WEIGHT	370grams

LABELLING:



MATERIAL : PVC SHEET

BASE : BLACK COLOUR

WORDS : WHITE COLOUR

SIZE : 38.4 x 20.4mm

SCHEMATIC:

