

DATA SHEET



PART NO: T 3182ST

ISSUE NO: 1

CATALOGUE NO: AD-0501000REU2.1

CUSTOMER NO: N/A

DESCRIPTION 5Vdc 1000mA Regulated Euro Plugtop Adaptor



INPUT VOLTS	230Vac
FREQUENCY	50Hz
MAG CURRENT (max.)	60mA
O/P VOLTS NO LOAD	
O/P VOLTS NO LOAD	5.1Vdc
O/P VOLTS	
O/P CURRENT	
O/P VOLTS	5.0Vdc
O/P CURRENT	1000mA
FLASH TEST	3.75KV
OUTPUT CONNECTOR	2.1x5.5x12mm
OUTPUT POLARITY	Centre +ve
LEAD LENGTH	1.8mtr
APPROVALS	N/A
LENGTH	99mm
DEPTH	48mm
WIDTH	61mm
WEIGHT	500g

LABELLING:

AC-DC ADAPTOR
 Model No. : AD-0501000R
 Eingang/Input : 230VAC 50Hz 17W
 Ausgang/Output : 5VDC 1000mA 5.0VA
 STONTRONICS LIMITED

CAUTION: DO NOT REMOVE COVER

MATERIAL : PVC SHEET

BASE : BLACK COLOUR

WORDS : WHITE COLOUR

SIZE : 40 x 30mm

SCHEMATIC:

