


Prototyping Boards Dual Inline



RE100-HP

- SRBP-paper FR2 1.5 mm single-sided 35 µm CU
- organic soldering protection (OSP)

- 37 x 56 single-hole conductor 2.1 mm Ø
- hole spacing 2.50 x 2.50 mm
- hole dia 1.0 mm
- connector 32/ 64/ 96-channel DIN 41612 type C
- size 100 x 160 mm