



Scotch®

35 Vinyl Electrical Colour Coding Tape

Data Sheet



Product Description

Scotch Brand 35 Vinyl Electrical Colour Coding Tape is an electrical grade polyvinyl chloride tape with a pressure sensitive rubber adhesive, available in nine fade resistant colours. Scotch 35 Tape is designed for use in phase identification, colour coding of motor leads and piping systems, and for marking safety areas. This abrasion and weather resistant tape has excellent electrical insulating properties, wraps smoothly, conforms well and holds over a wide range of temperatures. Scotch 35 Tape is resistant to moisture, alkalies, acids and corrosion. It is an Underwriters' Laboratories Listed and Canadian Standard Association Certified "Insulating Tape".

- ❖ UL Listed; UL 510 Standard "Insulating Tape" (product category OANZ), File E129200.
- ❖ CSA certification; Standard C22.2 No. 197-M1983 "PVC Insulating Tape", File LR 48769.
- ❖ Polyvinyl chloride (PVC) backing.
- ❖ Pressure-sensitive rubber based adhesive.
- ❖ Colour Coded for job identification and safety.
- ❖ Nine fade-resistant colours.

Typical Data/Physical Properties

Temperature Rating

UL510 80°C (176°F)
 CSA (Continuous Operation) 105°C (221°F)
 Colours: Red, Yellow, Blue, Brown, Grey, White, Green, Orange, Violet

Thickness

ASTM D1000 0.178mm

Break Strength

ASTM D1000 30N/10mm
 22°C (72°F)

Ultimate Elongation

ASTM D1000 225%

Adhesion to Steel

ASTM D1000 2.2N/10mm
 22°C (92°F)

Adhesion to Backing

ASTM D1000 2.2N/10mm
 22°C (72°F)

Flammability

UL510 1 sec.

ASTM D1000 4 sec.

Accelerated Ageing:

ASTM D1000 100%

Flagging

ASTM D1000 <2.5mm

Electrical Properties

Voltage Rating UL510 600V

Dielectric Breakdown

ASTM D1000	Standard Condition	45kV/mm
	High Humidity Condition	90% of Standard Condition

Insulation Resistance

ASTM D1000	>1 x 10 ⁶ Megohms
High Humidity Method	

Note: These are typical values and should not be used for specification purposes.

3M UK PLC

Electrical Products

3M Centre, Cain Road
 Bracknell, Berkshire RG12 1JU
 Telephone: 01344 858616
 Fax: 01344 858758

3M Ireland

Sales Office

3M House, Adelphi Centre
 Dun Laoghaire, Co Dublin, Ireland
 Telephone: 353 1 280 3555
 Fax: 353 1 280 3509

3M UK PLC

Sales Office

PO Box 393
 Bedford MK41 0YE
 Telephone: 01234 229462
 Fax: 01234 229433



Scotch®

35 Vinyl Electrical Colour Coding Tape

Data Sheet

Specifications

The tape is based on polyvinyl chloride (PVC) and/or its copolymers and has a rubber-based, pressure-sensitive adhesive. The tape shall be 0.178mm thick, and be UL Listed and marked per UL Standard 510 as "Flame Retardant and Weather Resistant". The tape shall be compatible with synthetic cable insulations, jackets and splicing compounds. The tape will remain stable and will not telescope more than 2.5mm when maintained at temperatures below 50°C (120°F).

Installation Techniques

The tape shall be applied with sufficient tension to produce a uniform wind. Wrap tape up-hill when taping from a smaller diameter surface to a larger diameter surface. Apply the tape with no tension on the last wrap to prevent flagging.

Maintenance

Scotch 35 Tape complies with the requirements of UL 510 for storage. When maintained under normal storage conditions, the tape will remain stable and has a five year shelf-life.

Availability

Scotch 35 vinyl electrical colour coding tape is available from your local 3M authorised distributor in the following standard roll size: 19mm x 20M

Other lengths and widths are available by special request.

Important Notice

Technical information provided by 3M is based on experience and/or tests believed to be reliable, but their accuracy is not guaranteed and the results may not be relevant to every user's application. For this reason 3M does not accept responsibility or liability, direct or consequential, arising from reliance upon any information provided and the user should determine the suitability of the products for their intended use. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence. All questions of liability relating to 3M products are governed by the seller's terms of sale subject where applicable to the prevailing law. If any goods supplied or processed by or on behalf of 3M prove on inspection to be defective in material or workmanship, 3M will (at its option) replace the same or refund to the Buyer the price paid for the goods or services. Except as set out above, all warranties and conditions, whether express or implied, statutory or otherwise are excluded to the fullest extent permissible at law.

3M and Scotch are trademarks of the 3M Company. Printed in the UK.
© 3M United Kingdom PLC, 2003.

3M UK PLC

Electrical Products

3M Centre, Cain Road
Bracknell, Berkshire RG12 1JU
Telephone: 01344 858616
Fax: 01344 858758

3M Ireland

Sales Office

3M House, Adelphi Centre
Dun Laoghaire, Co Dublin, Ireland
Telephone: 353 1 280 3555
Fax: 353 1 280 3509

3M UK PLC

Sales Office

PO Box 393
Bedford MK41 0YE
Telephone: 01234 229462
Fax: 01234 229433