



INDUSTRIAL BUZZERS


ACOUSTIC

Acoustic Signals Industrial Buzzers > Adaptahorn Series

Product overview

The Adaptahorn buzzer has a powerful output giving a penetrating, low frequency sound. With a variety of mounting options, they can be used in almost any

application, both indoors and outdoors. Adaptahorns are available as a grill version for flush mounting and also as a weatherproof version. Back box pre-tapped at 3/4" NPT. M20 adaptor available upon request.




Features

- High output penetrating sound
- Volume control
- Durable, long life mechanism
- Continuously rated

Material

Zinc Alloy

Code No:	Voltage:	Frequency:	Current:
ABK877-G1	24v Dc ---	350-400 Hz	0.16 A
ABK876-N5	120v Ac ~	350-400 Hz	0.13 A
ABK876-R5	230v Ac ~	350-400 Hz	0.06 A



Kg 1.6

50/60 Hz

°C -35+66

IP 65

CONTINUOUS

INDUSTRIAL

APPROVAL AND CONFORMITIES



dB 112