

# 3M

# Value Duct Tape

## 1900

Technical Data

April, 2007

**Product Description** 3M™ Value Duct Tape 1900 is a conformable cloth duct tape made with polyethylene film over cloth scrim and synthetic rubber adhesive. A good choice for non-critical applications.

Product Construction	Backing	Adhesive	Color	Standard Roll Length	Standard Width
	Polyethylene over cloth scrim	Synthetic rubber	Silver	50 yds. (45.7 m)	1.88 in. (48 mm) 2.83 in. (72 mm)

**Typical Physical Properties** **Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.**

		ASTM Test Method
Adhesion to Steel:	58 oz./in. width (63.5 N/100 mm)	D-3330
Tensile Strength:	16 lbs./in. width (280.2 N/100 mm)	D-3759
Elongation at Break:	12%	D-3759
Thickness:	5.8 mils (0.147 mm)	D-3652
Temperature Use Range:	Up to 200°F (93°C)	

- Features**
- Polyethylene backing provides moisture resistance to tape applications.
  - Synthetic rubber adhesive sticks well to many surfaces.
  - Easy tear.
  - Low profile.
  - Individual roll wrap preserves integrity of the roll with less waste and easy identification.

- Application Ideas**
- Tool box tape for non-critical uses.
  - Light duty sealing and holding.
  - Marking.

# 3M™ Value Duct Tape

## 1900

---

**Storage** Store under normal conditions of 60° to 80°F (16° to 27°C) and 40 to 60% R.H. in the original carton.

---

**Shelf Life** To obtain best performance, use this product within 12 months from date of manufacture.

---

**Product Use** All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

---

**Warranty and Limited Remedy** Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.

---

**Limitation of Liability** Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



**Industrial Business  
Industrial Adhesives and Tapes Division**

3M Center, Building 21-1W-10, 900 Bush Avenue  
St. Paul, MN 55144-1000  
800-362-3550 • 877-369-2923 (fax)  
www.3M.com/industrial



*Recycled Paper*  
40% pre-consumer  
10% post-consumer

3M is a trademark of 3M Company.  
Printed in U.S.A.  
©3M 2007 70-0711-0177-1 (4/07)