



A range of high quality UK manufactured phono plugs made from machined brass with various plating options.

- Centre contact available in solid pin.
- Ground contact with unique 'T' shape slot for maximum contact area.
- Internal cable clamp for secure cable connection.
- Spring strain relief.
- Colour coded ID rings for easy cable identification.
- Attractive body styling.
- Maximum cable size 5.5mm

Material	
Centre contact	:Brass, silver plated
Ground contact	:Brass, nickel plated
Insulation	:Noryl SE1
Cable clamp	:Brass, silver plated
Spring	:Spring steel, nickel plated
Cap	:Brass, nickel plated

Rating – 5A at 200 Vdc/150 Vac max.
 Insulation resistance – 100M Ω at 500 Vdc

Dimensions



Deltron Part No.	Description
333-0000	NICKEL PLATED
333-0100	NICKEL PLATED (BLACK ID RING)
333-0200	NICKEL PLATED (BLUE ID RING)
333-0500	NICKEL PLATED (BLUE ID RING)
333-0600	NICKEL PLATED (RED ID RING)
333-0700	NICKEL PLATED (YELLOW ID RING)

CONVERTED FROM PS0357 ISS2 (06.12.93) IN JAN 2003

DrgNo 333 SERIES	TITLE PROFESSIONAL PHONO PLUG	ALL DIMENSIONS IN MM ANGLES IN DECIMAL DEGREES		
DELTRON Components	ISSUE 2 GENERAL SPECIFICATION FOR 333 SERIES	CUSTOMER		FILTER REF
		Aprvd Date 31/01/03	Aprvd By MC	Drwn by BS
				Sheet 1 / 1