


A range of high quality UK manufactured phono plugs made from machined brass with various plating options.

- Centre contact available in solid pin.
- Ground contact with unique 'T' shape slot for maximum contact area.
- Internal cable clamp for secure cable connection.
- Spring strain relief.
- Colour coded ID rings for easy cable identification.
- Attractive body styling.
- Maximum cable size 5.5mm

**Material**

- Centre contact :Brass, flash gold plated
- Ground contact :Brass, flash gold plated
- Insulation :Noryl SE1
- Cable clamp :Brass, flash gold plated
- Spring :Spring steel, flash gold plated
- Cap :Brass, flash gold plated

Rating – 5A at 200 Vdc/150 Vac max.  
 Insulation resistance – 100M Ω at 500 Vdc



Deltron Part No.	Description
334-0000	FLASH GOLD PLATED
334-0100	FLASH GOLD PLATED (BLACK ID RING)
334-0200	FLASH GOLD PLATED (BLUE ID RING)
334-0500	FLASH GOLD PLATED (RED ID RING)
334-0600	FLASH GOLD PLATED (WHITE ID RING)
334-0700	FLASH GOLD PLATED (YELLOW ID RING)

CONVERTED FROM PS0358 ISS2 (04.01.94) IN JAN 2003

DrgNo 334 SERIES		TITLE PROFESSIONAL PHONO LINE PLUG			ALL DIMENSIONS IN MM ANGLES IN DECIMAL DEGREES		
		ISSUE 2 GENERAL SPECIFICATION FOR 334 SERIES		CUSTOMER		FILTER REF	
				Aprvd Date 31/01/03	Aprvd By MC	Drwn by BS	Scale: NTS