


C1210C476M4PACTU

aka C1210C476M4PAC7800

Capacitor, ceramic, 47 uF, +/-20% Tol, 16V, X5R, 1210



Dimensions (mm)

Specifications

ID	Dimension	Tolerance
L	3.20	+/-0.20
W	2.50	+/-0.20
T	2.5	+/-0.2
B	0.50	+/-0.25

Manufacturer:	KEMET
Capacitance:	47 uF
Chip Size:	1210
Voltage:	16V
Temperature Coefficient:	X5R
Tolerance:	+/-20%
Application:	Std Chip
Termination Type:	Tin
Marked:	No
Dissipation Factor:	10%
Insulation Resistance:	21.28 MOhm
Dielectric Strength:	40V
Package Kind:	T&R
Package Size:	7in
Package Type:	Plastic Tape
Package Quantity:	1000