


Capacitor, tantalum, 10 uF, +/-10% Tol, 16V@85C, Lead Spacing=2.54 mm



Dimensions (mm)

Specifications

ID	Dimension	Tolerance	Manufacturer:	KEMET
D	5.5	+0	Value:	10 uF
H	8.9	+0	Voltage DC @ 85C:	16V
S	2.54	+/-0.38	Voltage DC @ 125C:	10V
LL	12.7	+/-1.26	Tolerance:	+/-10%
			Body Type:	Radial Conformal ('dipped')
			Temperature Range:	-55/+125C
			Application:	General Purpose
			Termination Type:	Tin
			Leakage Current:	1.3 uA
			Dissipation Factor:	6%
			Package Kind:	Bulk
			Package Type:	Bag