



B82442X002

| Kit contents | Values | Datasheets |
|-----------------|---------|---|
| B82442T1102K050 | 1uH | http://www.epcos.com/inf/30/db/ind_2008/b82442t.pdf |
| B82442T1103K050 | 10uH | http://www.epcos.com/inf/30/db/ind_2008/b82442t.pdf |
| B82442T1104K050 | 100uH | http://www.epcos.com/inf/30/db/ind_2008/b82442t.pdf |
| B82442T1105K050 | 1000uH | http://www.epcos.com/inf/30/db/ind_2008/b82442t.pdf |
| B82442T1106K050 | 10000uH | http://www.epcos.com/inf/30/db/ind_2008/b82442t.pdf |
| B82442T1223K050 | 22uH | http://www.epcos.com/inf/30/db/ind_2008/b82442t.pdf |
| B82442T1224K050 | 220uH | http://www.epcos.com/inf/30/db/ind_2008/b82442t.pdf |
| B82442T1225K050 | 2200uH | http://www.epcos.com/inf/30/db/ind_2008/b82442t.pdf |
| B82442T1472K050 | 4.7uH | http://www.epcos.com/inf/30/db/ind_2008/b82442t.pdf |
| B82442T1473K050 | 47uH | http://www.epcos.com/inf/30/db/ind_2008/b82442t.pdf |
| B82442T1474K050 | 470uH | http://www.epcos.com/inf/30/db/ind_2008/b82442t.pdf |
| B82442T1475K050 | 4700uH | http://www.epcos.com/inf/30/db/ind_2008/b82442t.pdf |

**3 Pieces per Value
Kit Quantity: 36**