

334 SK Slotted Screwdriver



Application: For slotted screws
Blade: Hexagonal, with bolster from 0,8 x 4,5, mat nickel
Tip: DIN 5264-A, ISO 2380, Lasertip®
Handle: Kraftform®, multi-component

Code	mm	mm	mm	mm	mm	mm	mm	mm	mm
05007670001	0,6	3,5	4	0	75	81	9/64"	3"	10
05007671001	0,8	4,0	4	0	90	81	5/32"	3 1/2"	10
05007672001	0,8	4,5	5	8	90	98	0,178"	3 1/2"	10

350 SK PH Screwdriver for Phillips screws



Application: For Phillips screws
Blade: Hexagonal, sizes 1-3 with bolster, mat nickel
Tip: DIN 5260-PH, ISO 8764-PH, Lasertip®
Handle: Kraftform® with anti-roll protection, multi-component

Code	mm	mm	mm	mm	mm	mm	mm
05008750001 ¹⁾	PH 0			60	81	2 3/8"	5
05008751001	PH 1	5	8	80	98	3 1/8"	10
05008752001	PH 2	6	10	100	105	4"	10
05008753001	PH 3	8	13	150	112	6"	5

¹⁾ without Lasertip®

334 SK/6 Rack Schraubendrehersatz Kraftform® Plus Lasertip® + Rack



Schraubendrehersatz mit Lasertip® Sechskantklingen + Rack

Anwendung: Schlitz- und Kreuzschlitzschrauben Phillips-Recess
Ausführung: 6-teilig im Fensterkarton + Rack

Code			
0500768001	334 SK	1 x 0,6x3,5x75; 1 x 0,8x4,0x90; 1 x 1,0x5,5x100; 1 x 1,2x6,5x125	1
	350 SK PH	1 x PH 1x80; 1 x PH 2x100	

1160 i/7 Safety Screwdriver Set Kraftform® Comfort VDE + Voltage Tester



Application: For slotted and Phillips screws
Content: 7 pieces set in display carton

Code			
05031575001	1160 i VDE	1 x 0,4x2,5x80; 1 x 0,6x3,5x100; 1 x 0,8x4,0x100; 1 x 1,0x5,5x125	1
	1162 i PH VDE	1 x PH 1x80; 1 x PH 2x100	
	4115	1 x 0,5x3,0x65	

8700-6/BDC - Bit-Check® - Rapidaptor®



1 BiTorsion® bit holder Rapidaptor® 897/4 R with quick-release chuck to suit most popular power tools or for use in electronic drills.

Code			
05056370001	897/4 R	1 x 1/4"x75	10
	800/1 BDC	1 x 1,0x5,5x25; 1 x 1,2x6,5x25	
	851/1 BDC PH	1 x PH 1x25; 1 x PH 2x25	
	855/1 BDC PZ	1 x PZ 1x25; 1 x PZ 2x25	

8700-9/BTZ - Bit-Check® - Rapidaptor®



1 BiTorsion® bit holder Rapidaptor® 897/4 R with quick-release chuck to suit most popular power tools or for use in electronic drills.

Code			
05056374001	897/4 R	1 x 1/4"x75	10
	800/1 BTZ	1 x 0,8x5,5x25; 1 x 1,0x5,5x25; 1 x 1,2 x6,5x25	
	851/1 BTZ PH	1 x PH 1x25; 1 x PH 2x25; 1 x PH 3x25	
	855/1 BTZ PZ	1 x PZ 1x25; 1 x PZ 2x25; 1 x PZ 3x25	