








# Supreme Cutters and Pliers



## TAPERED

### 7190-7191



Product code	EAN code	A mm inch	B mm inch	C mm inch	D mm inch	F mm inch	Capacity mm inch	Bevel		
7190	0052479	109.0 4.29	9.0 0.35	9.0 0.35	6.0 0.24	1.0 0.04	0.2 - 1.25 0.01 - 0.05	Micro	50	1
7191	0052509	109.0 4.29	9.0 0.35	9.0 0.35	6.0 0.24	1.0 0.04	0.1 - 1.25 0.01 - 0.05	Flush	50	1



If a Supreme cutter or pliers is desired with ESD-safe sleeves, then add the suffix CO or DS to the product code (Example: 7190 CO)






# Supreme Cutters and Pliers

## ANGLE

### REVERSE



**7280**


Product code	EAN code	A mm inch	B mm inch	C mm inch	D mm inch	G mm inch	Capacity mm inch	Bevel		
7280	0052523	118.0 4.64	18.0 0.71	9.0 0.35	6.0 0.24	3.5 0.14	0.2 - 0.8 0.01 - 0.03	Flush	54	10



### MINIATURE

**7285**

Product code	EAN code	A mm inch	B mm inch	C mm inch	D mm inch	G mm inch	Capacity mm inch	Bevel		
7285	0052530	120.0 4.72	20.0 0.79	9.0 0.35	6.0 0.24	6.7 0.26	0.2 - 1.0 0.01 - 0.04	Flush	56	1








# Supreme Cutters and Pliers

## ANGLE

### END



#### 7290-7291


Product code	EAN code 731415+	A mm inch	B mm inch	C mm inch	G mm inch	Capacity mm inch	Bevel		
7290	0052547	108.0 4.25	8.0 0.31	10.5 0.41	15.0 0.59	0.35 - 1.25 0.01 - 0.05	Micro	56	1
7291	0052554	108.0 4.25	8.0 0.31	10.5 0.41	15.0 0.59	0.35 - 1.25 0.01 - 0.05	Flush	56	1



### END

#### 7293



Product code	EAN code 731415+	A mm inch	B mm inch	C mm inch	G mm inch	Capacity mm inch	Bevel		
7293	0052592	108.0 4.25	8.0 0.31	10.5 0.41	8.0 0.31	0.35 - 1.25 0.01 - 0.05	Flush	56	1






# Supreme Cutters and Pliers



## MINIATURE END

Product code	EAN-code	A mm inch	B mm inch	C mm inch	D mm inch	E mm inch	F mm inch	Capacity mm inch	Bevel		
7292	0052578	115.0 4.53	15.0 0.59	9.0 0.35	6.0 0.24	3.2 0.13	4.0 0.16	0.35 - 0.8 0.01 - 0.03	Flush	54	1

**7292**




## PLIERS

Product code	EAN-code	A mm inch	B mm inch	C mm inch	D mm inch	E mm inch	F mm inch	Jaw shape		
7490	0052646	120.0 4.72	20.0 0.79	9.0 0.35	6.0 0.24	1.2 0.05	3.2 0.13	Smooth	53	1

**FLAT NOSE**

**7490**








# Supreme Cutters and Pliers

## PLIERS

### ROUND NOSE


**7590**





Product code	EAN code	A mm inch	B mm inch	C mm inch	D mm inch	E mm inch	F mm inch	Jaw shape		
7590	0052660	120.0 4.72	20.0 0.79	9.0 0.35	6.0 0.24	1.0 0.04	Ø 0.5 Ø 0.02	Very fine	54	1

### SNIPE NOSE

**7890-7891**





Product code	EAN code	A mm inch	B mm inch	C mm inch	D mm inch	E mm inch	F mm inch	Jaw shape		
7890	0052691	132.0 5.20	32.0 1.26	9.0 0.35	6.0 0.24	1.2 0.05	0.8 0.03	Smooth	60	1
7891	0052714	132.0 5.20	32.0 1.26	9.0 0.35	6.0 0.24	1.2 0.05	0.8 0.03	Serrated	59	1



# Supreme Cutters and Pliers


## PLIERS

### SHOULDER POINT WITH BENT TIP



Product code	EAN code	A	B	C	D	E	F	Jaw shape		
	731415+	mm inch	mm inch	mm inch	mm inch	mm inch	mm inch		g	
7892	0052738	129.0 5.08	29.0 1.14	9.0 0.35	6.0 0.24	1.2 0.05	0.8 0.03	Smooth	59	1



**7892**



### SHORT SHOULDER POINT WITH BENT TIP

Product code	EAN code	A	B	C	D	E	F	Jaw shape		
	731415+	mm inch	mm inch	mm inch	mm inch	mm inch	mm inch		g	
7893	0052769	120.0 4.72	20.0 0.79	9.0 0.35	6.0 0.24	1.2 0.05	0.8 0.03	Smooth	56	1



**7893**

