


Atlas Light Trade Platform Steps

Data Sheet - Page 1 of 1

YOUNGMAN

INNOVATIVE WORK AT HEIGHT SOLUTIONS

Date 10/02/05
Issue B



Description: 3, 4, 5, 6, 7, 8 Tread Light Trade Steps

Note: 3 Tread = 2 Treads + Platform

Dimensions Common throughout range

	Platform size (mm)	Tread depth (mm)	Tread Pitch (mm)	Tread Height (mm)	Vertical height of knee rail above platform	Stile size Front (mm)	Stile Size Rear (mm)	Depth (mm)
3,4,5 Tread	275 - 252 x 260	80	230	215	605	40 x 20	33 x 20	120
6,7,8 Tread						50 x 20		

Code	No. of Treads	Platform height (mm)	Open Spread (mm)	Max.Working Height (mm)	Approx. Weight (kg)	Packing size (mm)			Boxed Volume (m3)
						Length	Width	Depth	
353312	3	567	639	2067	2.8	1255	409	120	0.062
354312	4	779	793	2279	3.4	1484	433	120	0.077
355312	5	995	931	2495	4.1	1714	457	120	0.094
356312	6	1217	1085	2717	5.1	1947	482	120	0.113
357312	7	1426	1237	2926	5.8	2176	507	120	0.132
358312	8	1640	1371	3140	6.8	2405	532	120	0.154

Technical Data: Duty Rating: 110kg

Material: Aluminium alloy (Platform, stiles, rear legs, and treads), Zinc plated steel (crossbars)

Plastic feet and end caps (Colour: Black)

Zinc plated steel fittings

Nylon opening restraint

Classification: EN 131