



Main Features

- 7 Inputs (5 Audio + 2 Video)
- Motor-driven Master Volume Control
- Tone Control (Bass, Treble)
- Balance Control
- A/B Speaker Selection
- Binding Post Speaker Terminals
- Front Panel Headphone Output
- Front Panel MIC Input with Level Control
- Full Function TEAC "UR" Remote Control

General Specifications

- Output Power: 90W + 90W (4 ohms, 1kHz, 0.5% THD)
60W + 60W (8 ohms, 1kHz, 0.5% THD)
- Audio Input: x 7
- Audio Output: x 2
- Speaker Terminal: Binding Post (Speaker A, B)
- Auxiliary AC Outlet: x 1 (Switched, VDE type, 1A max)
- Operation: 230V AC, 50Hz (EUR)
- Dimension (W x H x D): 17-1/8" x 5-5/8" x 14"
435 x 142 x 355 mm
- Weight: 21.4 lbs. 9.7 kg

