

# In-Line Fuseholder

For 5 x 15mm or 5 x 20mm Fuses



**CATALOG SYMBOL:** HHT  
IN-LINE FUSEHOLDER

#### Specifications:

**Body Material:** Black thermoplastic  
**Wire Leads:** 16 Awg; nominal o.d. 0.14"; color: red  
**Terminals:** Brass  
**Lead Pull Test:** Withstands 10 lbs. pull  
**Temperature Range:** -40°C to +80°C


#### Electrical Ratings:

5 x 15mm rated 5A at 32V  
 5 x 20mm rated 10A at 32V


#### Dimensions:

**Wire Lead Length:** 13" ± .05"  
**Body Length:** 1.84"  
**Body Diameter:** 0.42"  
**Shipping Weight:** 17.5 lbs. per 1000 pieces

#### Dimensional Data



- Accepts 5 x 15mm or 5 x 20mm fuses.
- Two piece screw together assembly.
- An economical and versatile fuseholder for normal environments.
- Wire leads included.



#### Catalog Numbers

Catalog Number	Description/ Qty.
HHT	Standard Pack (100-in)
BK/HHT	Bulk Pack (1,000-in)

The only controlled copy of this Data Sheet is the electronic read-only version located on the Bussmann Network Drive. All other copies of this Data Sheet are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Bussmann reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Bussmann also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.