

Multimeter Accessories



TL-130A

Model TL-130A

General Purpose DMM Kit

If you need only one basic accessory kit for your meter, this is the one. Attach probes or clips to the sheath plug to complete your test. Soft, flexible silicone leads make movement easy. Kit is voltage and current rated for either electronic or electrical applications.

- All components compliant to IEC61010-2-031
- Silicone Lead Wire length 60" (1.5m)
- Tri-fold Velcro Pouch



CP-3

Model CP-3

DC/AC Current Clamp

- Converts any DMM to a current clamp
- Measures current without disconnecting circuit under test
- Measures to 400A DC or AC
- Outputs 1 mV per Amp, operates on 2V range of any DMM



TL-50

Model TL-50

Maxi-Pro DMM Kit

Complete accessory kit for all your DMM testing needs. Includes soft, flexible silicone lead wire easy movement and Tri-Fold Velcro Pouch for convenient storage.

- All components compliant to IEC61010-2-031
- Silicone lead wire length 60" (1.5m)
- Tri-fold Velcro Pouch

Features

	model		
	TL-130A		
4mm Straight to Right-Angle Silicone Leads, 1.5m	1000V	CATIII	12A
Probe Bodies w/Ø2mm Tip	1000V	CATIII	36A
Alligator Style Clips	1000V	CATIII	20A
Alligator Clips	300V	CATI	3A

Specifications

	model
	CP-3
(Accuracy specified at 18° to 28°C)	
Current Range	2A to 400A, DC or AC
Frequency Response (AC)	50 Hz - 400 Hz
Accuracy	±(2% reading + 2A)
Input Resistance	10kΩ min.
Maximum Conductor Size	1.1" (30mm)
Power Requirement	9V battery, NEDA 1604
Battery Life	100 hr typical
Operating Temperature	0° to 40°C, <70% RH
Storage Temperature	-20° to + 70°C, <80% RH

Features

	model		
	TL-50		
4mm Straight to Right-Angle Silicone Leads, 1.5m	1000V	CATIII	12A
Probe Bodies w/Ø2mm Tip	1000V	CATIII	36A
Pincer Style Clips	1000V	CATIII	6A
Fully Insulated Alligator Clips	1000V	CATIII	20A
Alligator Clips	300V	CATI	3A
Spade Lug Adapters	42V (1000V)		36A
Banana Plug Adapters	42V (1000V)		36A



TL-10

Model TL-10

SMD Probe Kit

Extended, slim-line probe body for easy reach. Use with small SMD components or general purpose test points. Includes soft, flexible silicone lead wires for easy movement and clear, PVC Pouch for convenient storage.

- All components compliant to IEC61010-2-031
- Silicone Lead Wire length 60" (1.5m)
- Clear PVC Pouch



PR-650A

Model PR-650A

RF DMM Probe

All purpose RF demodulator probe, usable with most DMMs. Allows a DMM to measure sine wave AC signals: $1V_{eff} = 1V_{DC}$ Features light weight design.

Specifications

	model
	PR-650A
Bandwidth	100kHz to 650MHz
Accuracy	± 1dB (100kHz-300MHz) ± 3dB (300MHz-650MHz)
Input Voltage	100V
HF Voltage	35Veff
Actuating Voltage	350mV
DMM Input	
Impedance	10MΩ
Input Capacitance	8pF
Cable Length	48" (1.2m)

Features

	model		
	TL-50		
4mm Straight to Right-Angle Silicone Leads, 1.5m	1000V	CATIII	12A
Probe Bodies w/Ø2mm Tip	1000V	CATIII	36A
Pincer Style Clips	1000V	CATIII	6A
Fully Insulated Alligator Clips	1000V	CATIII	20A
Alligator Clips	300V	CATI	3A
Spade Lug Adapters	42V (1000V)		36A
Banana Plug Adapters	42V (1000V)		36A



PR-28A

Model PR-28A

40 kV High Voltage DMM Probe

If the voltages you need to measure are above the specifications of general purpose probes, B+K Precision has a higher voltage probe for you.

Features

	model		
	PR-28A		
Attenuation	x1000	Impedance	1000MΩ
Voltage (AC)	20kV	Accuracy (AC & DC)	± 3%
Voltage (DC)	40kV	Cable Length	48" (1.2m)
Bandwidth	60Hz		