

| Product Type | MTBF[h] | FIT[Fit] | ref | comment |
|---------------|---------|----------|-----|---------|
| 3F88L-130-SI | 108000 | 9246 | M | |
| 3F88L-132-SD | 110000 | 9090 | M | |
| 3G23D-TK3F2 | 509000 | 1961 | M | |
| 3G23D-TK3H2 | 647000 | 1544 | M | |
| 3G296-MH2H4 | 838000 | 1192 | M | |
| 3G296-MH2H5 | 830000 | 1204 | M | |
| 3G2A2-DI212 | 283000 | 3531 | M | |
| 3G2A2-DO211 | 259000 | 3851 | M | |
| 3G2A2-II001 | 355000 | 2815 | M | |
| 3G2A2-II002 | 598000 | 1672 | M | |
| 3G2A2-IM211 | 287000 | 3480 | M | |
| 3G2A2-LK001 | 166000 | 6021 | M | |
| 3G2A2-LK005 | 154000 | 6484 | M | |
| 3G2A2-MP831 | 515000 | 1939 | M | |
| 3G2A2-MR831 | 583000 | 1714 | M | |
| 3G2A2-OC221 | 161000 | 6187 | M | |
| 3G2A2-PS221 | 218000 | 4585 | M | |
| 3G2A2-PS222 | 828000 | 1207 | M | |
| 3G2A3-PS221 | 500000 | 2000 | M | |
| 3G2A4-IA121 | 418000 | 2392 | M | |
| 3G2A4-MR431 | 3131000 | 319 | M | |
| 3G2A4-OA121 | 506000 | 1973 | M | |
| 3G2A5-AD001 | 130000 | 7652 | M | |
| 3G2A5-AD002 | 130000 | 7652 | M | |
| 3G2A5-AD003 | 130000 | 7652 | M | |
| 3G2A5-AD004 | 130000 | 7652 | M | |
| 3G2A5-AD005 | 130000 | 7652 | M | |
| 3G2A5-AD006 | 116000 | 8551 | M | |
| 3G2A5-AD007 | 116000 | 8551 | M | |
| 3G2A5-AD101 | 98000 | 10146 | R | |
| 3G2A5-AE001 | 3005000 | 333 | M | |
| 3G2A5-AP001 | 650000 | 1538 | M | |
| 3G2A5-AP002 | 440000 | 2269 | M | |
| 3G2A5-AP003 | 7042000 | 142 | M | |
| 3G2A5-ASC01 | 330000 | 3027 | M | |
| 3G2A5-ASC01-D | 330000 | 3027 | M | |
| 3G2A5-ASC02 | 319000 | 3127 | M | |
| 3G2A5-ASC03 | 467000 | 2140 | R | |
| 3G2A5-ASC04 | 467000 | 2140 | R | |
| 3G2A5-ASP01 | 521000 | 1917 | R | |
| 3G2A5-ASP02 | 675000 | 1480 | R | |
| 3G2A5-BC031 | 4003000 | 250 | R | |
| 3G2A5-BC051 | 534000 | 1873 | M | |
| 3G2A5-BC061 | 3389000 | 295 | R | |
| 3G2A5-BC081 | 534000 | 1873 | M | |
| 3G2A5-BC082 | 534000 | 1873 | M | |
| 3G2A5-BC091 | 3003000 | 333 | R | |
| 3G2A5-BI051 | 1068000 | 936 | M | |
| 3G2A5-BI081 | 831000 | 1202 | M | |
| 3G2A5-BI083 | 649000 | 1539 | M | |
| 3G2A5-BP001 | 510000 | 1957 | M | |
| 3G2A5-CMT01 | 430000 | 2326 | M | |
| 3G2A5-CN111 | 1204000 | 830 | M | |
| 3G2A5-CN121 | 1204000 | 830 | M | |
| 3G2A5-CN312N | 1204000 | 830 | R | |
| 3G2A5-CN511 | 1204000 | 830 | M | |
| 3G2A5-CP131 | 173000 | 5780 | R | |
| 3G2A5-CT001 | 170000 | 5855 | M | |
| 3G2A5-CT012 | 170000 | 5855 | M | |
| 3G2A5-CT021 | 398000 | 2511 | R | |
| 3G2A5-CT041 | 175000 | 5695 | R | |
| 3G2A5-DA001 | 107000 | 9275 | M | |
| 3G2A5-DA002 | 107000 | 9275 | M | |
| 3G2A5-DA003 | 107000 | 9275 | M | |

| | | | |
|----------------|---------|-------|---|
| 3G2A5-DA004 | 107000 | 9275 | M |
| 3G2A5-DA005 | 107000 | 9275 | M |
| 3G2A5-DA101 | 78000 | 12807 | R |
| 3G2A5-DA101-T | 100000 | 10000 | R |
| 3G2A5-DT021 | 47000 | 21172 | R |
| 3G2A5-DT022 | 47000 | 21172 | R |
| 3G2A5-DUM01 | 880000 | 1136 | M |
| 3G2A5-ED001 | 276000 | 3621 | M |
| 3G2A5-FDI03 | 403000 | 2476 | M |
| 3G2A5-FDI03E | 403000 | 2476 | M |
| 3G2A5-FZ001 | 108000 | 9182 | R |
| 3G2A5-GDI01 | 1007000 | 992 | M |
| 3G2A5-GDI11 | 220000 | 4534 | R |
| 3G2A5-GDI12 | 187000 | 5327 | R |
| 3G2A5-GPI01 | 261000 | 3830 | R |
| 3G2A5-IA121 | 418000 | 2392 | M |
| 3G2A5-IA122 | 190000 | 5241 | M |
| 3G2A5-IA122-G | 190000 | 5241 | R |
| 3G2A5-IA123 | 418000 | 2392 | R |
| 3G2A5-IA221 | 403000 | 2480 | M |
| 3G2A5-IA222 | 403000 | 2480 | M |
| 3G2A5-IA223 | 190000 | 5241 | M |
| 3G2A5-ID111 | 352000 | 2835 | M |
| 3G2A5-ID112 | 352000 | 2835 | M |
| 3G2A5-ID114 | 122000 | 8145 | M |
| 3G2A5-ID211 | 352000 | 2835 | M |
| 3G2A5-ID212 | 257000 | 3884 | M |
| 3G2A5-ID213 | 352000 | 2835 | M |
| 3G2A5-ID215 | 245000 | 4072 | M |
| 3G2A5-ID215-G | 245000 | 4072 | R |
| 3G2A5-ID216 | 332000 | 3004 | M |
| 3G2A5-ID218 | 213000 | 4683 | M |
| 3G2A5-ID218CN | 245000 | 4072 | M |
| 3G2A5-ID218-FK | 245000 | 4072 | R |
| 3G2A5-ID219 | 122000 | 8145 | R |
| 3G2A5-ID219-FK | 280000 | 3565 | R |
| 3G2A5-ID21N | 331000 | 3017 | M |
| 3G2A5-ID411 | 122000 | 8145 | M |
| 3G2A5-ID501CN | 245000 | 4072 | M |
| 3G2A5-IDA02 | 517000 | 1931 | R |
| 3G2A5-IDA22 | 517000 | 1931 | R |
| 3G2A5-IDS01 | 673000 | 1485 | R |
| 3G2A5-IDS01-V1 | 580000 | 1722 | R |
| 3G2A5-IDS02 | 444000 | 2248 | R |
| 3G2A5-IDS21 | 580000 | 1722 | R |
| 3G2A5-IDS22 | 444000 | 2248 | R |
| 3G2A5-IF101 | 233000 | 4287 | M |
| 3G2A5-II001 | 1926000 | 519 | M |
| 3G2A5-II002 | 950000 | 1052 | M |
| 3G2A5-II101 | 1112112 | 899 | M |
| 3G2A5-IM111 | 145000 | 6894 | M |
| 3G2A5-IM211 | 288000 | 3462 | M |
| 3G2A5-IM212 | 145000 | 6894 | M |
| 3G2A5-IM213 | 145000 | 6894 | M |
| 3G2A5-IP001 | 276000 | 3621 | M |
| 3G2A5-IP002 | 276000 | 3621 | M |
| 3G2A5-IP004 | 276000 | 3621 | M |
| 3G2A5-IP004M | 276000 | 3621 | R |
| 3G2A5-LDP01 | 521000 | 1917 | R |
| 3G2A5-LK003 | 254000 | 3937 | M |
| 3G2A5-LK005 | 185000 | 5405 | M |
| 3G2A5-LK007 | 185000 | 5405 | M |
| 3G2A5-LK008 | 185000 | 5405 | M |
| 3G2A5-LK009 | 254000 | 3937 | M |
| 3G2A5-LK009-D | 254000 | 3937 | M |

| | | | |
|-----------------|---------|-------|---|
| 3G2A5-LK009-V1 | 611000 | 1636 | M |
| 3G2A5-LK010 | 248000 | 4032 | M |
| 3G2A5-LK010-H | 248000 | 4032 | R |
| 3G2A5-LK010-P | 248000 | 4032 | M |
| 3G2A5-LK012 | 244000 | 4098 | M |
| 3G2A5-LK101 | 244000 | 4098 | M |
| 3G2A5-LK101-PV1 | 244000 | 4098 | M |
| 3G2A5-LK101-V1 | 244000 | 4098 | M |
| 3G2A5-LK103 | 244000 | 4098 | M |
| 3G2A5-LK103-P | 244000 | 4098 | M |
| 3G2A5-LK201 | 185000 | 5405 | M |
| 3G2A5-LK201-V1 | 185000 | 5405 | M |
| 3G2A5-LK203 | 511000 | 1954 | M |
| 3G2A5-MD211 | 298000 | 3353 | R |
| 3G2A5-MD211CN | 298000 | 3353 | M |
| 3G2A5-MGC01 | 241000 | 4144 | M |
| 3G2A5-MP007 | 1167000 | 856 | M |
| 3G2A5-MP008 | 1650000 | 606 | M |
| 3G2A5-MP501-H | 1434000 | 697 | M |
| 3G2A5-MP501-T | 1434000 | 697 | M |
| 3G2A5-MP502-H | 1321000 | 757 | M |
| 3G2A5-MP502-T | 1321000 | 757 | M |
| 3G2A5-MP503-H | 887000 | 1127 | M |
| 3G2A5-MP503-T | 887000 | 1127 | M |
| 3G2A5-MP504-H | 791000 | 1264 | M |
| 3G2A5-MP504-T | 791000 | 1264 | M |
| 3G2A5-MP831 | 904000 | 1106 | M |
| 3G2A5-MR231 | 2020000 | 495 | M |
| 3G2A5-MR431 | 1538000 | 650 | M |
| 3G2A5-MR831 | 1538000 | 650 | M |
| 3G2A5-MSB01 | 180000 | 5550 | M |
| 3G2A5-NC101 | 106000 | 9371 | M |
| 3G2A5-NC103 | 106000 | 9386 | M |
| 3G2A5-NC103-Z | 106000 | 9386 | M |
| 3G2A5-NC111 | 143000 | 6972 | M |
| 3G2A5-NC111-V1 | 114000 | 8755 | M |
| 3G2A5-NC121 | 113000 | 8850 | M |
| 3G2A5-NC221 | 54000 | 18354 | M |
| 3G2A5-NC221-E | 54000 | 18354 | R |
| 3G2A5-NC222 | 47000 | 20953 | R |
| 3G2A5-OA121 | 506000 | 1973 | M |
| 3G2A5-OA121-G | 506000 | 1973 | R |
| 3G2A5-OA221 | 941000 | 1062 | M |
| 3G2A5-OA222 | 506000 | 1973 | M |
| 3G2A5-OA223 | 433000 | 2308 | M |
| 3G2A5-OA223 | 433000 | 2308 | R |
| 3G2A5-OA223-FK | 941000 | 1062 | R |
| 3G2A5-OA223-G | 433000 | 2308 | R |
| 3G2A5-OA225 | 511218 | | M |
| 3G2A5-OC221 | 197000 | 5060 | M |
| 3G2A5-OC223 | 197000 | 5060 | M |
| 3G2A5-OC224 | 100000 | 9993 | M |
| 3G2A5-OC224 | 100000 | 9993 | R |
| 3G2A5-OC224-E | 100000 | 10000 | R |
| 3G2A5-OD211 | 259000 | 3849 | M |
| 3G2A5-OD212 | 192000 | 5185 | M |
| 3G2A5-OD212 | 192000 | 5185 | R |
| 3G2A5-OD212-G | 192000 | 5185 | R |
| 3G2A5-OD213 | 182000 | 5477 | R |
| 3G2A5-OD213-FK | 277000 | 3604 | R |
| 3G2A5-OD215 | 504000 | 1981 | M |
| 3G2A5-OD217 | 206000 | 4852 | M |
| 3G2A5-OD218 | 189000 | 5287 | M |
| 3G2A5-OD218-G | 189000 | 5287 | R |
| 3G2A5-OD219 | 369000 | 2709 | R |

| | | | |
|------------------|---------|-------|---|
| 3G2A5-OD21N | 280000 | 3564 | M |
| 3G2A5-OD411 | 206000 | 4852 | M |
| 3G2A5-OD412 | 189000 | 5287 | M |
| 3G2A5-OD412-G | 189000 | 5287 | R |
| 3G2A5-OD414 | 189000 | 5287 | M |
| 3G2A5-OD415CN | 189000 | 5287 | M |
| 3G2A5-OD501CN | 189000 | 5287 | M |
| 3G2A5-OV001 | 209000 | 4782 | M |
| 3G2A5-PID01 | 181000 | 5501 | M |
| 3G2A5-PRO13 | 451000 | 2213 | M |
| 3G2A5-PRO15 | 463000 | 2159 | M |
| 3G2A5-PRO19 | 497000 | 2008 | M |
| 3G2A5-PRO20 | 506000 | 1973 | M |
| 3G2A5-PRO23 | 451000 | 2213 | M |
| 3G2A5-PRO23-FK | 463000 | 2159 | M |
| 3G2A5-PRT01 | 297000 | 3366 | M |
| 3G2A5-PRW04 | 172000 | 5788 | M |
| 3G2A5-PRW06 | 481000 | 2077 | R |
| 3G2A5-PS103 | 1705000 | 586 | M |
| 3G2A5-PS212 | 159000 | 6268 | M |
| 3G2A5-PS212-E | 159000 | 6268 | M |
| 3G2A5-PS213-E | 16000 | 62500 | R |
| 3G2A5-PS221 | 457618 | | M |
| 3G2A5-PS221-E | 457618 | | M |
| 3G2A5-PS221-FK | 333000 | 3000 | R |
| 3G2A5-PS222 | 131000 | 7621 | M |
| 3G2A5-PS222-E | 131000 | 7621 | M |
| 3G2A5-PS223 | 203000 | 4917 | M |
| 3G2A5-PS223-E | 203000 | 4917 | M |
| 3G2A5-RM001 | 271000 | 3686 | M |
| 3G2A5-RM001-V1 | 271000 | | M |
| 3G2A5-RM201 | 311000 | 3214 | M |
| 3G2A5-RT001 | 276000 | 3622 | R |
| 3G2A5-RT001-EV1 | 294000 | | M |
| 3G2A5-RT001-PEV1 | 294000 | | M |
| 3G2A5-RT001-PV1 | 294000 | | M |
| 3G2A5-RT001-V1 | 294000 | | M |
| 3G2A5-RT001-V1H | 271000 | 3690 | M |
| 3G2A5-RT002 | 276000 | 3621 | M |
| 3G2A5-RT002-EV1 | 276000 | | M |
| 3G2A5-RT002-PEV1 | 276000 | | M |
| 3G2A5-RT002-PV1 | 276000 | | M |
| 3G2A5-RT002-V1 | 276000 | | M |
| 3G2A5-RT002-V1H | 276000 | 3623 | R |
| 3G2A5-RT201 | 332000 | 3012 | M |
| 3G2A5-SNT31-V1 | 55000 | 17950 | M |
| 3G2A5-SNT31-V2 | 55000 | 17950 | M |
| 3G2A5-SNT31-V3 | 55000 | 17950 | M |
| 3G2A5-SNT31-V3MJ | 55000 | 17950 | M |
| 3G2A5-SNT31-V4 | 121000 | 8262 | R |
| 3G2A5-TS101-D | 190000 | 5259 | R |
| 3G2A5-TU001 | 300000 | 3330 | M |
| 3G2A5-ZTL01 | 1801000 | 555 | M |
| 3G2A6-AD001 | 130000 | 7652 | M |
| 3G2A6-AD002 | 130000 | 7652 | M |
| 3G2A6-AD003 | 130000 | 7652 | M |
| 3G2A6-AD004 | 130000 | 7652 | M |
| 3G2A6-AD005 | 130000 | 7652 | M |
| 3G2A6-AD006 | 116000 | 8551 | M |
| 3G2A6-AD007 | 116000 | 8551 | M |
| 3G2A6-CT001 | 170000 | 5855 | M |
| 3G2A6-DA001 | 107000 | 9275 | M |
| 3G2A6-DA002 | 107000 | 9275 | M |
| 3G2A6-DA003 | 107000 | 9275 | M |
| 3G2A6-DA004 | 107000 | 9275 | M |

| | | | |
|-------------------|---------|-------|---|
| 3G2A6-DA005 | 107000 | 9275 | M |
| 3G2A6-DUM01 | 880000 | 1136 | M |
| 3G2A6-IA121 | 418000 | 2392 | M |
| 3G2A6-IA221 | 185000 | 5391 | M |
| 3G2A6-IA222 | 403000 | 2480 | M |
| 3G2A6-ID112 | 352000 | 2835 | M |
| 3G2A6-ID212 | 257000 | 3884 | M |
| 3G2A6-ID213 | 352000 | 2835 | M |
| 3G2A6-ID216 | 332000 | 3004 | M |
| 3G2A6-ID217 | 245000 | 4072 | M |
| 3G2A6-IM111 | 145000 | 6894 | M |
| 3G2A6-IM211 | 288000 | 3462 | M |
| 3G2A6-IM213 | 145000 | 6894 | M |
| 3G2A6-LK010 | 248000 | 4032 | M |
| 3G2A6-LK010-P | 248000 | 4032 | M |
| 3G2A6-LK012 | 274000 | 3650 | M |
| 3G2A6-LK013 | 250000 | 3999 | M |
| 3G2A6-LK014 | 250000 | 3999 | M |
| 3G2A6-LK101 | 274000 | 3650 | M |
| 3G2A6-LK101-PV1 | 274000 | 3650 | M |
| 3G2A6-LK101-V1 | 274000 | 3650 | M |
| 3G2A6-LK201 | 250000 | 3999 | M |
| 3G2A6-LK201-V1 | 250000 | 3999 | M |
| 3G2A6-LK202 | 250000 | 3999 | M |
| 3G2A6-LK202-V1 | 250000 | 3999 | M |
| 3G2A6-OA121 | 506000 | 1973 | M |
| 3G2A6-OA222 | 506000 | 1973 | M |
| 3G2A6-OC221 | 197000 | 5060 | M |
| 3G2A6-OC222 | 121000 | 8250 | M |
| 3G2A6-OD211 | 259000 | 3849 | M |
| 3G2A6-OD411 | 206000 | 4852 | M |
| 3G2A6-OD412 | 189000 | 5287 | M |
| 3G2A6-OV001 | 209000 | 4782 | M |
| 3G2A6-PRO25 | 451000 | 2213 | M |
| 3G2A6-RM001 | 271000 | 3686 | M |
| 3G2A6-RM001-P | 271000 | 3686 | M |
| 3G2A9-AL001 | 3301000 | 303 | M |
| 3G2A9-AL002 | 569000 | 1757 | M |
| 3G2A9-AL003 | 480000 | 2083 | M |
| 3G2A9-AL004 | 610000 | 1638 | M |
| 3G2A9-AL005 | 530000 | 1886 | M |
| 3G2A9-AL006 | 489000 | 2043 | M |
| 3G2C2-SC021-CPUMB | 1988000 | 503 | M |
| 3G2C2-SCA21 | 165000 | 6039 | M |
| 3G2C2-SCK21 | 111000 | 8969 | M |
| 3G2C3-CP131 | 173000 | 5780 | M |
| 3G2C3-CPU01 | 145000 | 6851 | M |
| 3G2C3-CPU11 | 215000 | 4632 | M |
| 3G2C3-CPU11-V1 | 215000 | 4632 | M |
| 3G2C3-CPUA1 | 202000 | 4939 | M |
| 3G2C3-CPUA1-1 | 414000 | 2415 | M |
| 3G2C3-CPUA1-2 | 396000 | 2523 | M |
| 3G2C3-CPUK1 | 215000 | 4632 | M |
| 3G2C4-CPU75 | 40000 | 24551 | M |
| 3G2C4-CPU76 | 54000 | 18273 | M |
| 3G2C4-CPU77 | 46000 | 21587 | M |
| 3G2C4-CPU78 | 40000 | 24551 | M |
| 3G2C4-CPU79 | 54000 | 18273 | M |
| 3G2C4-CPU80 | 46000 | 21587 | M |
| 3G2C4-CPUA1-1 | 387000 | 2578 | M |
| 3G2C4-CPUA1-2 | 415000 | 2404 | M |
| 3G2C4-CPUA1-3 | 568000 | 1759 | M |
| 3G2C4-CPUA4-1 | 374000 | 2668 | M |
| 3G2C4-SC021 | 81000 | 12228 | M |
| 3G2C4-SC022 | 81000 | 12228 | M |

| | | | |
|----------------|---------|-------|---|
| 3G2C4-SC023 | 81000 | 12228 | M |
| 3G2C4-SC023-V1 | 81000 | 12228 | M |
| 3G2C4-SC024 | 81000 | 12228 | M |
| 3G2C4-SC026 | 81000 | 12228 | M |
| 3G2C4-SCA22 | 78000 | 12746 | M |
| 3G2C4-SCK23 | 81000 | 12228 | M |
| 3G2C4-SCK24 | 81000 | 12228 | M |
| 3G2C4-SI021 | 135000 | 7384 | M |
| 3G2C4-SI022 | 135000 | 7384 | M |
| 3G2C4-SI023 | 135000 | 7384 | M |
| 3G2C4-SI024 | 135000 | 7384 | M |
| 3G2C4-SI025 | 135000 | 7384 | M |
| 3G2C4-SI026 | 135000 | 7384 | M |
| 3G2C4-SI027 | 135000 | 7384 | M |
| 3G2C4-SI028 | 135000 | 7384 | M |
| 3G2C4-SI029 | 135000 | 7384 | M |
| 3G2C4-SI031 | 135000 | 7384 | M |
| 3G2C4-SI033 | 135000 | 7384 | M |
| 3G2C4-SI035 | 135000 | 7384 | M |
| 3G2C5-BC001 | 641000 | 1559 | M |
| 3G2C5-BC061 | 450000 | 2218 | M |
| 3G2C5-BI082 | 587000 | 1702 | M |
| 3G2C5-BI083 | 649000 | 1539 | M |
| 3G2C5-CPU01 | 104000 | 9568 | M |
| 3G2C5-CPU01-V1 | 104000 | 9568 | M |
| 3G2C5-DPL01 | 260000 | 3841 | M |
| 3G2C5-DPL01-E | 260000 | 3841 | M |
| 3G2C5-FDI01 | 403000 | 2476 | M |
| 3G2C5-GDI01 | 1007000 | 992 | M |
| 3G2C5-GPC01 | 154000 | 6492 | M |
| 3G2C5-GPC01(1) | 642000 | 1555 | M |
| 3G2C5-GPC01(2) | 447000 | 2237 | M |
| 3G2C5-GPC01(3) | 384000 | 2599 | M |
| 3G2C5-GPC01(4) | 9900000 | 101 | M |
| 3G2C5-GPC03 | 144000 | 6940 | M |
| 3G2C5-GPC03(1) | 733000 | 1363 | M |
| 3G2C5-GPC03(2) | 347000 | 2878 | M |
| 3G2C5-II101 | 1926000 | 519 | M |
| 3G2C5-IOD01 | 1400000 | 714 | M |
| 3G2C5-IOD02 | 1228000 | 814 | M |
| 3G2C5-MP001 | 1319000 | 758 | M |
| 3G2C5-MP302 | 3599000 | 278 | M |
| 3G2C5-MP341 | 1070000 | 934 | M |
| 3G2C5-MR141 | 1070000 | 934 | M |
| 3G2C5-MR141-V1 | 1070000 | 934 | M |
| 3G2C5-MR141-V2 | 1070000 | 934 | R |
| 3G2C5-MR241 | 1070000 | 934 | M |
| 3G2C5-MR241-V1 | 1070000 | 934 | M |
| 3G2C5-MR341 | 1070000 | 934 | M |
| 3G2C5-MR341-V1 | 1070000 | 934 | M |
| 3G2C5-MR341-V1 | 1070000 | 934 | R |
| 3G2C5-MR831 | 1070000 | 934 | M |
| 3G2C5-MR831-V1 | 1070000 | 934 | M |
| 3G2C7-CPU11 | 130000 | 7656 | M |
| 3G2C7-CPU11-H | 130000 | 7656 | M |
| 3G2C7-CPU12 | 130000 | 7656 | M |
| 3G2C7-CPU12 | 130000 | 7656 | R |
| 3G2C7-CPU12-N | 130000 | 7656 | M |
| 3G2C7-CPU13-E | 130000 | 7656 | M |
| 3G2C7-CPU14-E | 130000 | 7656 | M |
| 3G2C7-CPU32 | 123000 | 8125 | M |
| 3G2C7-CPU32-J | 123000 | 8125 | M |
| 3G2C7-CPU34-E | 123000 | 8125 | M |
| 3G2C7-CPU38 | 123000 | 8125 | M |
| 3G2C7-CPU38-E | 130000 | 7656 | M |

| | | | |
|-------------------|---------|-------|---|
| 3G2C7-CPU41 | 130000 | 7656 | M |
| 3G2C7-CPU42 | 130000 | 7656 | M |
| 3G2C7-CPU43-E | 130000 | 7656 | M |
| 3G2C7-CPU44-E | 130000 | 7656 | M |
| 3G2C7-CPU53-E | 130000 | 7656 | M |
| 3G2C7-CPU54-E | 130000 | 7656 | M |
| 3G2C7-CPU71 | 130000 | 7656 | M |
| 3G2C7-CPU71-H | 130000 | 7656 | M |
| 3G2C7-CPU72 | 130000 | 7656 | M |
| 3G2C7-CPU72-IS | 120000 | 8333 | M |
| 3G2C7-CPU72-N | 130000 | 7656 | M |
| 3G2C7-CPU73-E | 130000 | 7656 | M |
| 3G2C7-CPU74-E | 130000 | 7656 | M |
| 3G2C7-CPU76 | 130000 | 7656 | M |
| 3G2C7-CPU76-E | 130000 | 7656 | M |
| 3G2C7-CPU83-E | 130000 | 7656 | M |
| 3G2C7-CPU84-E | 130000 | 7656 | M |
| 3G2C7-CPUM2 | 130000 | 7656 | M |
| 3G2C7-IP002 | 451000 | 2213 | M |
| 3G2C7-IP002 | 451000 | 2213 | R |
| 3G2C7-IP002-V1 | 451000 | 2213 | R |
| 3G2C7-LK011 | 130000 | 7656 | M |
| 3G2C7-LK201 | 451000 | 2213 | M |
| 3G2C7-LK201-V1 | 451000 | 2213 | M |
| 3G2C7-LK202 | 451000 | 2213 | M |
| 3G2C7-LK202-V1 | 451000 | 2213 | M |
| 3G2C7-MA221 | 191000 | 5223 | M |
| 3G2C7-MA222 | 98000 | 10137 | M |
| 3G2C7-MC221 | 214000 | 4671 | M |
| 3G2C7-MC222 | 110000 | 9058 | M |
| 3G2C7-MC223 | 214000 | 4671 | M |
| 3G2C7-MC224 | 110000 | 9059 | M |
| 3G2C7-MC227 | 214000 | 4671 | M |
| 3G2C7-MC228 | 110000 | 9059 | M |
| 3G2C7-MC229 | 191000 | 5223 | M |
| 3G2C7-MC22A | 98000 | 10137 | M |
| 3G2C7-MC22B | 191000 | 5223 | M |
| 3G2C7-MC22C | 98000 | 10137 | M |
| 3G2C7-MC22E | 110000 | 9059 | M |
| 3G2C7-MC22EA | 110000 | 9059 | M |
| 3G2C7-MD211 | 214000 | 4671 | M |
| 3G2C7-MD212 | 110000 | 9059 | M |
| 3G2C7-MD222 | 110000 | 9059 | M |
| 3G2C7-MP009 | 1000000 | 1000 | M |
| 3G2C7-MP009-V1 | 1000000 | 1000 | M |
| 3G2NK-CPU31 | 225000 | 4440 | M |
| 3G2T4-ID21N | 331000 | 3017 | M |
| 3G2T4-IP001(PCB1) | 440000 | 2272 | M |
| 3G2T4-OD21N | 280000 | 3564 | M |
| 3G2T4-PS121 | 556000 | 1796 | M |
| 3G2T5-PS121 | 932000 | 1072 | M |
| 3G2T5-SC011 | 120000 | 8314 | M |
| 3G2T5-SC012 | 111000 | 8995 | M |
| 3G2T5-SI011 | 160000 | 6222 | M |
| 3G2T5-SI013 | 293000 | 3402 | M |
| 3G2T8-IP001 | 234000 | 4263 | M |
| 3G2T8-IP001(PCB2) | 502000 | 1991 | M |
| 3G2T8-MP001 | 1745000 | 573 | M |
| 3G2T8-MP002 | 1485000 | 673 | M |
| 3G2T8-MP003 | 1293000 | 773 | M |
| 3G2T8-MP004 | 1293000 | 773 | M |
| 3G2T8-PCM11 | 62000 | 15929 | M |
| 3G2T8-PCM12 | 64000 | 15400 | M |
| 3G2T8-PRO18 | 35000 | 28156 | M |
| 3G2T8-PRO18(PCB1) | 41000 | 24378 | M |

| | | | |
|-------------------|---------|------|---|
| 3G2T8-PRO18(PCB2) | 264000 | 3779 | M |
| 3G2T8-SC081 | 101000 | 9870 | M |
| 3G2T8-SC081(MPU) | 118000 | 8435 | M |
| 3G2T8-SC082 | 107000 | 9341 | M |
| 3G2T8-SC082(MPU) | 120000 | 8306 | M |
| 3G2T9-IP005-V2 | 421000 | 2375 | M |
| 3G2V8-CPU11 | 258000 | 3864 | M |
| 3G2V8-CPU14 | 258000 | 3864 | M |
| 3G3EV | 2000000 | | R |
| 3G3FV 200V | 2330000 | | R |
| 3G3FV 400V | 1410000 | | R |
| 3G3HV 200V | 2330000 | | R |
| 3G3HV 400V | 1410000 | | R |
| 3G3IV-A2004 | 1000000 | 1000 | M |
| 3G3IV-A2007 | 1000000 | 1000 | M |
| 3G3IV-A2015 | 1000000 | 1000 | M |
| 3G3IV-A2022 | 1000000 | 1000 | M |
| 3G3IV-A2037 | 1000000 | 1000 | M |
| 3G3IV-A2055 | 1000000 | 1000 | M |
| 3G3IV-A2075 | 1000000 | 1000 | M |
| 3G3IV-A4004 | 1000000 | 1000 | M |
| 3G3IV-A4007 | 1000000 | 1000 | M |
| 3G3IV-A4015 | 1000000 | 1000 | M |
| 3G3IV-A4022 | 1000000 | 1000 | M |
| 3G3IV-A4037 | 1000000 | 1000 | M |
| 3G3IV-A4055 | 1000000 | 1000 | M |
| 3G3IV-A4075 | 1000000 | 1000 | M |
| 3G3IV-A4110 | 1000000 | 1000 | M |
| 3G3IV-A4150 | 1000000 | 1000 | M |
| 3G3IV-A4185 | 1000000 | 1000 | M |
| 3G3IV-A4220 | 1000000 | 1000 | M |
| 3G3IV-A4300 | 1000000 | 1000 | M |
| 3G3IV-A4370 | 1000000 | 1000 | M |
| 3G3IV-A4450 | 1000000 | 1000 | M |
| 3G3IV-B2110 | 1000000 | 1000 | M |
| 3G3IV-B2150 | 1000000 | 1000 | M |
| 3G3IV-B2185 | 1000000 | 1000 | M |
| 3G3IV-B2220 | 1000000 | 1000 | M |
| 3G3IV-PSIF | 624000 | 1603 | M |
| 3G3IV-PSIG | 624000 | 1603 | M |
| 3G3SV-BB002-E | 1000000 | 1000 | M |
| 3G3SV-BB004-E | 1000000 | 1000 | M |
| 3G3SV-BB007-E | 1000000 | 1000 | M |
| 3G3SV-BB015-E | 1000000 | 1000 | M |
| 3G3SV-BB022-E | 1000000 | 1000 | M |
| 3G3SV-BB037-E | 1000000 | 1000 | M |
| 3G5A2-IA121 | 186000 | 5365 | M |
| 3G5A2-IA221 | 185000 | 5391 | M |
| 3G5A2-ID001 | 211000 | 4730 | M |
| 3G5A2-IM211 | 192000 | 5196 | M |
| 3G5A2-OA121 | 224000 | 4460 | M |
| 3G5A2-OA221 | 224000 | 4460 | M |
| 3G5A2-OC221 | 150000 | 6624 | M |
| 3G5A2-OD411 | 216000 | 4610 | M |
| 3G5B2-CPU01 | 145000 | 6851 | M |
| 3G5B2-IA121 | 186000 | 5365 | M |
| 3G5B2-IA221 | 185000 | 5391 | M |
| 3G5B2-ID001 | 211000 | 4730 | M |
| 3G5B2-IM211 | 192000 | 5196 | M |
| 3G5B2-MD001 | 594000 | 1683 | M |
| 3G5B2-OA121 | 224000 | 4460 | M |
| 3G5B2-OA221 | 224000 | 4460 | M |
| 3G5B2-OC221 | 150000 | 6624 | M |
| 3G5B2-OD411 | 216000 | 4610 | M |
| 3G8B2-AB000 | 800000 | 1249 | M |

| | | | |
|----------------|---------|-------|---|
| 3G8B2-AB001 | 600000 | 1667 | M |
| 3G8B2-AB010 | 1000000 | 1000 | M |
| 3G8B2-AE000 | 2000000 | 500 | M |
| 3G8B2-AP000 | 900000 | 1111 | M |
| 3G8B2-AP001 | 900000 | 1111 | M |
| 3G8B2-AX000 | 800000 | 1249 | M |
| 3G8B2-AX001 | 600000 | 1667 | M |
| 3G8B2-AX002 | 800000 | 1249 | M |
| 3G8B2-AX003 | 600000 | 1667 | M |
| 3G8B2-AX010 | 42000 | 23809 | M |
| 3G8B2-AX020 | 11000 | 90909 | M |
| 3G8B2-BG000 | 450000 | 2222 | M |
| 3G8B2-BI000 | 600000 | 1667 | M |
| 3G8B2-BI010 | 1244648 | | M |
| 3G8B2-BI012 | 600000 | 1667 | M |
| 3G8B2-BP000 | 650000 | 1538 | M |
| 3G8B2-CS000 | 200000 | 5000 | M |
| 3G8B2-CS001 | 200000 | 5000 | M |
| 3G8B2-CS010-KB | 20000 | 50000 | M |
| 3G8B2-DB000 | 350000 | 2857 | M |
| 3G8B2-DB001 | 350000 | 2857 | M |
| 3G8B2-EF000 | 200000 | 5000 | M |
| 3G8B2-EW000 | 200000 | 5000 | M |
| 3G8B2-FP000 | 400000 | 2500 | M |
| 3G8B2-IG000 | 200000 | 5000 | M |
| 3G8B2-IG001 | 200000 | 5000 | M |
| 3G8B2-IG010 | 200000 | 5000 | M |
| 3G8B2-IG020 | 200000 | 5000 | M |
| 3G8B2-IK000 | 450000 | 2222 | M |
| 3G8B2-IP000 | 350000 | 2857 | M |
| 3G8B2-IW000 | 180000 | 5555 | M |
| 3G8B2-IW010 | 180000 | 5555 | M |
| 3G8B2-M0000 | 350000 | 2857 | M |
| 3G8B2-M0002 | 180000 | 5555 | M |
| 3G8B2-M8910 | 200000 | 5000 | M |
| 3G8B2-M8912 | 200000 | 5000 | M |
| 3G8B2-M8913 | 200000 | 5000 | M |
| 3G8B2-M8920 | 751000 | 1331 | M |
| 3G8B2-MA000 | 220000 | 4545 | M |
| 3G8B2-MA001 | 220000 | 4545 | M |
| 3G8B2-MA002 | 220000 | 4545 | M |
| 3G8B2-MA010 | 961000 | 1040 | M |
| 3G8B2-MA011 | 961000 | 1040 | M |
| 3G8B2-MA012 | 961000 | 1040 | M |
| 3G8B2-MD000 | 170000 | 5882 | M |
| 3G8B2-MD001 | 170000 | 5882 | M |
| 3G8B2-MD010 | 537000 | 1859 | M |
| 3G8B2-MD011 | 537000 | 1859 | M |
| 3G8B2-MO000 | 350000 | 2857 | R |
| 3G8B2-NA000 | 330000 | 3030 | M |
| 3G8B2-NA001 | 322000 | 3100 | M |
| 3G8B2-NC000 | 200000 | 5000 | M |
| 3G8B2-ND000 | 180000 | 5555 | M |
| 3G8B2-ND001 | 180000 | 5555 | M |
| 3G8B2-NF000 | 300000 | 3333 | M |
| 3G8B2-NI000 | 200000 | 5000 | M |
| 3G8B2-NI001 | 200000 | 5000 | M |
| 3G8B2-NI002 | 200000 | 5000 | M |
| 3G8B2-NI003 | 200000 | 5000 | M |
| 3G8B2-NI010 | 200000 | 5000 | M |
| 3G8B2-NI011 | 200000 | 5000 | M |
| 3G8B2-NI012 | 200000 | 5000 | M |
| 3G8B2-NI013 | 200000 | 5000 | M |
| 3G8B2-NI020 | 170000 | 5882 | M |
| 3G8B2-NI021 | 170000 | 5882 | M |

| | | | | |
|----------------|---------|--------|---|----------------------------------|
| 3G8B2-NM000 | 200000 | 5000 | M | |
| 3G8B2-NM001 | 200000 | 5000 | M | |
| 3G8B2-NM010 | 200000 | 5000 | M | |
| 3G8B2-NM011 | 200000 | 5000 | M | |
| 3G8B2-NO000 | 200000 | 5000 | M | |
| 3G8B2-NO001 | 200000 | 5000 | M | |
| 3G8B2-NO020 | 170000 | 5882 | M | |
| 3G8B2-NS000 | 265000 | 3771 | M | |
| 3G8B2-NS000-V1 | 265000 | 3771 | M | |
| 3G8B2-NS001 | 258000 | 3871 | M | |
| 3G8B2-NS001-V1 | 258000 | 3871 | M | |
| 3G8B2-PS000 | 30000 | 33333 | M | |
| 3G8B2-Z8010 | 200000 | 5000 | M | |
| 3G8B2-Z8011 | 200000 | 5000 | M | |
| 3G8B2-Z8020 | 200000 | 5000 | M | |
| 3G8B2-Z8030 | 652000 | 1533 | M | |
| 3G8B2-Z8031 | 383000 | 2610 | M | |
| 3G8B2-Z8040 | 668000 | 1497 | M | |
| 3G8B3-AB000 | 1000000 | 1000 | M | |
| 3G8B3-AB001 | 1400000 | 714 | M | |
| 3G8B3-AB030 | 1300000 | 769 | M | |
| 3G8B3-AB040 | 2906000 | 344 | M | |
| 3G8B3-AB050 | 3140000 | 318 | M | |
| 3G8B3-AE000 | 2000000 | 500 | M | |
| 3G8B3-APS01 | 2383000 | 420 | M | |
| 3G8B3-AT000 | 900000 | 1111 | M | |
| 3G8B3-AX000 | 400000 | 2500 | M | |
| 3G8B3-AX010 | 42000 | 23810 | M | |
| 3G8B3-AX020 | 11000 | 90909 | M | |
| 3G8B3-AX030 | 4000 | 208333 | M | |
| 3G8B3-AX031 | 53000 | 18832 | M | |
| 3G8B3-AX040 | 4000 | 208333 | M | |
| 3G8B3-AX041 | 53000 | 18727 | M | |
| 3G8B3-BE000 | 3573000 | 280 | M | |
| 3G8B3-BG010 | 165000 | 6044 | M | |
| 3G8B3-CL000-1 | 67000 | 14815 | M | |
| 3G8B3-CL001 | 67000 | 14815 | M | |
| 3G8B3-CS001 | 530000 | 1887 | M | |
| 3G8B3-CS010 | 112000 | 8928 | M | |
| 3G8B3-CS011 | 112000 | 8928 | M | |
| 3G8B3-CS012 | 112000 | 8928 | M | |
| 3G8B3-DRM21 | | | A | Not available from SS technology |
| 3G8B3-ED000 | 230000 | 4348 | M | |
| 3G8B3-IG000 | 380000 | 2632 | M | |
| 3G8B3-M0000 | 150000 | 6667 | M | |
| 3G8B3-M0000-1 | 150000 | 6667 | M | |
| 3G8B3-M0001 | 150000 | 6667 | M | |
| 3G8B3-M0002 | 150000 | 6667 | M | |
| 3G8B3-M0003 | 150000 | 6667 | M | |
| 3G8B3-M0003-1 | 150000 | 6667 | M | |
| 3G8B3-M0010 | 178000 | 5618 | M | |
| 3G8B3-M0011 | 178000 | 5618 | M | |
| 3G8B3-M0020 | 249000 | 4016 | M | |
| 3G8B3-M0021 | 213000 | 4695 | M | |
| 3G8B3-M0022 | 200000 | 5000 | M | |
| 3G8B3-M0023 | 178000 | 5618 | M | |
| 3G8B3-M1010 | 178000 | 5614 | M | |
| 3G8B3-M1011 | 178000 | 5614 | M | |
| 3G8B3-M1020 | 249000 | 4016 | M | |
| 3G8B3-M1021 | 213000 | 4695 | M | |
| 3G8B3-M1022 | 200000 | 5000 | M | |
| 3G8B3-M1023 | 178000 | 5618 | M | |
| 3G8B3-M2000 | 181000 | 5497 | M | |
| 3G8B3-M2001 | 243000 | 4099 | M | |
| 3G8B3-M2003 | 181000 | 5497 | M | |

| | | | | |
|-------------|----------|--------|---|----------------------------------|
| 3G8B3-M2005 | 181000 | 5497 | M | |
| 3G8B3-M200X | 181000 | 5497 | M | |
| 3G8B3-M2010 | 199000 | 5025 | M | |
| 3G8B3-M2011 | 125000 | 8000 | M | |
| 3G8B3-M2012 | 135000 | 7407 | M | |
| 3G8B3-M2013 | 110000 | 9091 | M | |
| 3G8B3-MA000 | 180000 | 5556 | M | |
| 3G8B3-MA001 | 180000 | 5556 | M | |
| 3G8B3-MA002 | 180000 | 5556 | M | |
| 3G8B3-MA010 | 459000 | 2179 | M | |
| 3G8B3-MA011 | 420000 | 2381 | M | |
| 3G8B3-MA012 | 420000 | 2381 | M | |
| 3G8B3-MD000 | 110000 | 9091 | M | |
| 3G8B3-MD001 | 110000 | 9091 | M | |
| 3G8B3-MD002 | 110000 | 9091 | M | |
| 3G8B3-MD003 | 110000 | 9091 | M | |
| 3G8B3-MD010 | 240000 | 4156 | M | |
| 3G8B3-MD011 | 196000 | 5081 | M | |
| 3G8B3-MD012 | 183000 | 5436 | M | |
| 3G8B3-MD013 | 157000 | 6361 | M | |
| 3G8B3-MP000 | 859000 | 1164 | M | |
| 3G8B3-MP002 | 859000 | 1164 | M | |
| 3G8B3-MP021 | 1033000 | 968 | M | |
| 3G8B3-MP022 | 633000 | 1579 | M | |
| 3G8B3-MP030 | 95000 | 10526 | M | |
| 3G8B3-MP031 | 88000 | 11364 | M | |
| 3G8B3-N0000 | 310000 | 3226 | M | |
| 3G8B3-N0001 | 310000 | 3226 | M | |
| 3G8B3-NI001 | 310000 | 3226 | M | |
| 3G8B3-NI010 | 144000 | 6903 | M | |
| 3G8B3-NM010 | 138000 | 7204 | M | |
| 3G8B3-NO000 | 190470 | | M | |
| 3G8B3-NO010 | 142000 | 7011 | M | |
| 3G8B3-NS010 | 152000 | 6575 | M | |
| 3G8B3-NS011 | 138000 | 7206 | M | |
| 3G8B3-PS000 | 30000 | 33333 | M | |
| 3G8B3-PS001 | 30000 | 33333 | M | |
| 3G8B3-SRM00 | 256673.5 | | M | |
| 3G8B3-SRM01 | 138011 | | M | |
| 3G8B3-TM031 | 112000 | 8928 | M | |
| 3G8B3-TM041 | 112000 | 8928 | M | |
| 3G8B3-TM051 | 112000 | 8928 | M | |
| 3G8E2-DRM21 | | | A | Not available from SS technology |
| 3G8F2-9801E | 69000 | 14306 | M | |
| 3G8F2-CPU01 | 21000 | 47619 | M | |
| 3G8F2-FD501 | 12000 | 83333 | M | |
| 3G8F2-FU001 | 180000 | 5555 | M | |
| 3G8F2-HD511 | 18000 | 55555 | M | |
| 3G8F2-HD520 | 11000 | 90909 | M | |
| 3G8F2-HD521 | 18000 | 55555 | M | |
| 3G8F2-O1021 | 124000 | 8051 | M | |
| 3G8F2-O1070 | 438000 | 2283 | M | |
| 3G8F2-O1090 | 346000 | 2890 | M | |
| 3G8F2-O1150 | 316000 | 3164 | M | |
| 3G8F3-CD141 | 280000 | 3571 | M | |
| 3G8F3-CPU02 | 20000 | 50000 | M | |
| 3G8F3-CPU03 | 12000 | 83333 | M | |
| 3G8F3-FD501 | 12000 | 83333 | M | |
| 3G8F3-KB002 | 58000 | 17241 | M | |
| 3G8F4-CD141 | 280000 | 3571 | M | |
| 3G8F4-CPU01 | 24000 | 41667 | M | |
| 3G8F4-KB001 | 6000 | 156250 | M | |
| 3G8F4-SLK21 | 312000 | 3203 | M | |
| 3G8F5-CD131 | 35000 | 28571 | M | |
| 3G8F5-CLK21 | 635000 | | M | |

| | | | | |
|----------------|---------|--------|---|----------------------------------|
| 3G8F5-CPU11 | 32000 | 31250 | M | Not available from SS technology |
| 3G8F5-DRM21 | | | A | |
| 3G8F5-KB001 | 100000 | 10000 | M | |
| 3G8F5-KB011 | 500000 | 2000 | M | |
| 3G8F5-SLK21 | 224000 | 4462 | M | |
| 3G8F5-SNT31 | 78000 | 12820 | M | |
| 3G8F6-CPU01 | 6000 | 154000 | M | |
| 3G8F6-KB001 | 20000 | 50000 | M | |
| 3G8FX-9200H-21 | 8000 | 125000 | M | |
| 3G8FX-9200H-22 | 8000 | 125000 | M | |
| 3G8FX-9200R-21 | 8000 | 125000 | M | |
| 3G8FX-AP000 | 29000 | 33400 | M | |
| 3G8FX-CD140-10 | 30000 | 33333 | M | |
| 3G8FX-CPU00-10 | 12000 | 83333 | M | |
| 3G8FX-CPU00-1B | 16000 | 62500 | M | |
| 3G8FX-CPU00-1E | 16000 | 62500 | M | |
| 3G8FX-CPU00-1H | 16000 | 62500 | M | |
| 3G8FX-CPU00-20 | 12000 | 83333 | M | |
| 3G8FX-FU200-11 | 8000 | 125000 | M | |
| 3G8FX-FU210-11 | 8000 | 125000 | M | |
| 3G8FX-FU210-13 | 8000 | 125000 | M | |
| 3G8FX-FU300-10 | 6000 | 166667 | M | |
| 3G8FX-FU300-11 | 6000 | 166667 | M | |
| 3G8FX-FU300-12 | 6000 | 166667 | M | |
| 3G8FX-FU300-13 | 6000 | 166667 | M | |
| 3G8FX-FU300-20 | 6000 | 166667 | M | |
| 3G8FX-FU301-10 | 8000 | 125000 | M | |
| 3G8FX-FU302-10 | 8000 | 125000 | M | |
| 3G8FX-FU400 | 9000 | 111111 | M | |
| 3G8FX-FU500-10 | 8000 | 125000 | M | |
| 3G8FX-KB000 | 100000 | 10000 | M | |
| 3G8FX-MA000 | 144000 | 6903 | M | |
| 3G8FX-MA000-1 | 270000 | 3703 | M | |
| 3G8FX-MD000 | 209000 | 4785 | M | |
| 3G8FX-MD000-1 | 648000 | 1543 | M | |
| 3G8FX-TM101 | 30000 | 33333 | M | |
| 3G8FX-TM111 | 67000 | 14815 | M | |
| 3G8FX-TM121 | 112000 | 8928 | M | |
| 3G8FX-TM131 | 112000 | 8928 | M | |
| 3G8FX-TM141 | 112000 | 8928 | M | |
| 3G8FX-TM151 | 283000 | 3532 | M | |
| 3G8FX-TM171 | 184000 | 5429 | M | |
| 3G8SX-CD170 | 20000 | 50000 | M | |
| 3G8SX-CD200 | 20000 | 50000 | M | |
| 3G8SX-CPU00 | 24000 | 40160 | M | |
| 3G8SX-CPU01 | 24000 | 40160 | M | |
| 3G8SX-FU601 | 47000 | 21000 | M | |
| 3G8SX-FU602 | 47000 | 21000 | M | |
| 3G8SX-FU603 | 166000 | 6000 | M | |
| 3G8SX-FU605 | 166000 | 6000 | M | |
| 3J4FZ | 122000 | 8197 | M | |
| 3S4YR-MAW2C-04 | 20000 | 49557 | M | |
| 3S4YR-MAW2C-07 | 20000 | 49557 | M | |
| 9200H-21 | 8000 | 125000 | M | |
| 9200H-22 | 8000 | 125000 | M | |
| 9200R-21 | 8000 | 125000 | M | |
| 95F3567 | 500000 | 2000 | M | |
| B500-AL007-P | 871000 | 1147 | M | |
| B500-CPU01 | 145000 | 6851 | M | |
| B500-MD001 | 594000 | 1683 | M | |
| B500-RPT01 | 429000 | 2329 | M | |
| B600-RT201 | 402000 | 2486 | M | |
| B700-AL001 | 101000 | 9828 | M | |
| B7A01 | 573000 | 1744 | M | |
| BC031-V2 | 2704000 | 370 | M | |

| | | | |
|-------------------|---------|-------|---|
| BC051-V2 | 2543000 | 393 | M |
| BC081-V2 | 1887000 | 530 | M |
| BC101-V2 | 1802000 | 555 | M |
| C1000H-APS01 | 1286000 | 777 | M |
| C1000H-CPU01-E2V1 | 92000 | 10870 | M |
| C1000H-CPU01-EV1 | 92000 | 10870 | M |
| C1000H-CPU01-FK | 92000 | 10814 | M |
| C1000H-CPU01-R | 92000 | 10814 | M |
| C1000H-CPU01-V1 | 92000 | 10814 | M |
| C1000HF-CPUA1 | 92000 | 10814 | M |
| C1000H-FMR11 | 363000 | 2750 | M |
| C1000H-FMR21 | 272000 | 3676 | M |
| C1000H-MAP01 | 30000 | 33333 | M |
| C1000H-SLK11 | 167000 | 5975 | M |
| C1000H-SLK21 | 179000 | 5571 | M |
| C1000H-SLK21-V1 | 179000 | 5571 | M |
| C1000H-TER01 | 500000 | 2000 | M |
| C120-LK201-V2 | 2868000 | 349 | M |
| C16P-IA | 253000 | 3937 | M |
| C16P-ID | 280000 | 3571 | M |
| C16P-ID-A | 211000 | 4728 | M |
| C16P-O-A | 130000 | 7675 | M |
| C16P-OR-A | 130000 | 7675 | M |
| C16P-OR-D | 160000 | 6250 | M |
| C16P-OS1-A | 130000 | 7675 | M |
| C16P-OT1-A | 130000 | 7675 | M |
| C16P-OT1-D | 160000 | 6250 | M |
| C1K-AD | 186000 | 5354 | M |
| C1K-DA | 196000 | 5081 | M |
| C2000H-CPU01 | 80000 | 12462 | M |
| C2000H-CPU01-E | 80000 | 12462 | M |
| C2000H-CPU01-E2V1 | 80000 | 12500 | M |
| C2000H-CPU01-EV1 | 80000 | 12500 | M |
| C2000H-CPU01-R | 80000 | 12462 | M |
| C2000H-CPU01-V1 | 80000 | 12462 | M |
| C2000-MP341-V1 | 1070000 | | M |
| C2000-MR141-V2 | 1070000 | 934 | M |
| C2000-MR241-V2 | 1070000 | | M |
| C2000-MR341-V2 | 1070000 | 934 | M |
| C2000-MR831-V2 | 1070000 | | M |
| C200H-AD001 | 122000 | 8150 | M |
| C200H-AD001-OD | 122000 | 8150 | M |
| C200H-AD002 | 390000 | 2561 | M |
| C200H-AD003 | 191600 | 5218 | M |
| C200H-APS01 | 262000 | 3810 | M |
| C200H-APS02 | 94000 | 10600 | M |
| C200H-APS03 | 1472000 | 679 | M |
| C200H-ASC01 | 803000 | 1244 | M |
| C200H-ASC02 | 700000 | 1429 | M |
| C200H-ASC11 | 512000 | 1952 | M |
| C200H-ASC21 | 486000 | 2057 | M |
| C200H-ASC31 | 451000 | 2217 | M |
| C200H-ATT02 | #DIV/0! | | R |
| C200H-ATT81 | #DIV/0! | | R |
| C200H-ATT83 | #DIV/0! | | R |
| C200H-B7A01 | 1929000 | 518 | M |
| C200H-B7A02 | 413000 | 2418 | M |
| C200H-B7A12 | 326000 | 3066 | M |
| C200H-B7A21 | 342000 | 2919 | M |
| C200H-B7A22 | 203000 | 4921 | M |
| C200H-B7AI1 | 1736000 | 576 | M |
| C200H-B7AO1 | 1929000 | | M |
| C200H-B7AO2 | 413427 | | M |
| C200H-BC031 | 7680000 | 130 | M |
| C200H-BC031-V1 | 7680000 | 130 | M |

| | | | |
|----------------|----------|-------|---|
| C200H-BC031-V2 | 7680000 | 130 | M |
| C200H-BC051 | 10416000 | 96 | R |
| C200H-BC051-V1 | 10395000 | 96 | R |
| C200H-BC051-V2 | 7680000 | 130 | M |
| C200H-BC081 | 7874000 | 127 | M |
| C200H-BC081-V1 | 7874000 | 127 | M |
| C200H-BC081-V2 | 7874000 | | M |
| C200H-BC101 | 7082000 | 141 | M |
| C200H-BC101-V1 | 7077000 | 141 | M |
| C200H-BC101-V2 | 7077000 | 141 | M |
| C200H-CP114 | 143000 | 6973 | M |
| C200H-CPU01 | 186000 | 5358 | M |
| C200H-CPU01-R | 80000 | 12462 | M |
| C200H-CPU01-SD | 186000 | 5358 | M |
| C200H-CPU02 | 1929000 | 518 | M |
| C200H-CPU02-SD | 1929000 | 518 | M |
| C200H-CPU03 | 158000 | 6298 | M |
| C200H-CPU11 | 570000 | 1754 | M |
| C200H-CPU11-E | 570000 | 1754 | M |
| C200H-CPU11-E2 | 570000 | 1754 | M |
| C200H-CPU21 | 132000 | 7576 | M |
| C200H-CPU22 | 132000 | 7576 | M |
| C200H-CPU23 | 110000 | 9091 | M |
| C200H-CPU31 | 109000 | 9174 | M |
| C200H-CT001 | 666000 | 1499 | M |
| C200H-CT001-V1 | 666000 | 1502 | M |
| C200H-CT002 | 320000 | 3125 | M |
| C200H-CT021 | 385000 | 2595 | M |
| C200H-DA001 | 124000 | 8021 | M |
| C200H-DA002 | 592000 | 1688 | M |
| C200H-DA003 | 184700 | 5413 | M |
| C200H-DA004 | 161000 | 6210 | M |
| C200H-DAC01 | 303000 | 3296 | M |
| C200H-DSC01 | 303000 | | M |
| C200HE-CPU11 | 507000 | 1970 | R |
| C200HE-CPU11-Z | 507000 | 1970 | M |
| C200HE-CPU32 | 467000 | 2139 | M |
| C200HE-CPU32 | 467000 | 2139 | R |
| C200HE-CPU32-Z | 467591 | | M |
| C200HE-CPU42 | 434000 | 2304 | M |
| C200HE-CPU42-Z | 434000 | 2304 | M |
| C200H-FZ001 | 176766 | | M |
| C200HG-CPU33 | 696000 | 1437 | M |
| C200HG-CPU33-Z | 696000 | 1437 | M |
| C200HG-CPU43 | 624000 | 1602 | M |
| C200HG-CPU43-Z | 624000 | 1602 | M |
| C200HG-CPU53 | 696000 | 1437 | M |
| C200HG-CPU53-Z | 696000 | 1437 | M |
| C200HG-CPU63 | 610000 | 1638 | M |
| C200HG-CPU63-Z | 610000 | 1638 | M |
| C200H-IA121 | 2403000 | 416 | M |
| C200H-IA122 | 1293000 | 773 | M |
| C200H-IA122V | 1293000 | 773 | M |
| C200H-IA221 | 2403000 | 416 | M |
| C200H-IA222 | 1298000 | 770 | M |
| C200H-IA222V | 1298000 | 770 | M |
| C200H-ID001 | 2309000 | 433 | M |
| C200H-ID002 | 2309000 | 433 | M |
| C200H-ID111 | 1374000 | 728 | M |
| C200H-ID211 | 2415000 | 414 | M |
| C200H-ID212 | 1782000 | 561 | M |
| C200H-ID215 | 676000 | 1479 | M |
| C200H-ID216 | 287000 | 3477 | M |
| C200H-ID217 | 242000 | 4131 | M |
| C200H-ID218 | 233000 | 4287 | M |

| | | | |
|-----------------|----------|-------|---|
| C200H-ID219 | 106000 | 9429 | M |
| C200H-ID501 | 679000 | 1471 | M |
| C200H-IDS01 | 596000 | 1676 | M |
| C200H-IDS01-V1 | 596000 | 1676 | M |
| C200H-IDS21 | 596000 | 1676 | M |
| C200H-IM211 | 2415000 | 414 | M |
| C200H-IM212 | 2127000 | 470 | M |
| C200H-IP006 | 1074000 | 931 | M |
| C200H-LK101 | 1555000 | 643 | M |
| C200H-LK101-PV1 | 1555000 | | M |
| C200H-LK201 | 1638000 | 611 | M |
| C200H-LK201-V1 | 1638000 | | M |
| C200H-LK202 | 1689000 | 592 | M |
| C200H-LK202-V1 | 1689000 | | M |
| C200H-LK401 | 723000 | 1382 | M |
| C200H-LS101 | 140000 | 7104 | M |
| C200H-MC221 | 237000 | | R |
| C200H-MD115 | 366000 | 2732 | M |
| C200H-MD215 | 366000 | 2732 | M |
| C200H-MD501 | 415000 | 2410 | M |
| C200H-ME431 | 14992000 | 67 | M |
| C200H-ME432 | 2803000 | 357 | M |
| C200H-ME831 | 2238000 | 447 | M |
| C200H-ME832 | 2654000 | 377 | M |
| C200H-MP831 | 27173000 | 37 | M |
| C200H-MR431 | 12135000 | 82 | M |
| C200H-MR432 | 2803000 | 357 | M |
| C200H-MR433 | 2803000 | 357 | M |
| C200H-MR831 | 3900000 | 256 | M |
| C200H-MR832 | 2653000 | 377 | M |
| C200H-MR833 | 2654000 | 377 | M |
| C200H-NC111 | 765000 | 1307 | M |
| C200H-NC112 | 779000 | 1284 | M |
| C200H-NC112-HD | 779000 | 1282 | M |
| C200H-NC211 | 40000 | 25000 | M |
| C200H-OA121-E | 2227000 | 449 | M |
| C200H-OA122-E | 746000 | 1340 | M |
| C200H-OA221 | 2227000 | 449 | M |
| C200H-OA222 | 2123000 | 471 | M |
| C200H-OA222V | 836000 | 1196 | M |
| C200H-OA223 | 746000 | 1340 | M |
| C200H-OA224 | 674000 | 1482 | M |
| C200H-OC221 | 1715000 | 583 | M |
| C200H-OC222 | 1157000 | 864 | M |
| C200H-OC222V | 484000 | | M |
| C200H-OC223 | 6134000 | 163 | M |
| C200H-OC224 | 1715000 | 583 | M |
| C200H-OC224V | 1038000 | | M |
| C200H-OC225 | 850000 | 1176 | M |
| C200H-OC226 | 360000 | | M |
| C200H-OD211 | 2994000 | 334 | M |
| C200H-OD212 | 1260000 | 794 | M |
| C200H-OD213 | 1850000 | 541 | M |
| C200H-OD214 | 1676000 | 597 | M |
| C200H-OD215 | 251000 | 3984 | M |
| C200H-OD215-MA | 251000 | 3984 | M |
| C200H-OD216 | 337000 | 2967 | M |
| C200H-OD217 | 225000 | 4444 | M |
| C200H-OD218 | 234000 | 4270 | M |
| C200H-OD219 | 167000 | 5968 | M |
| C200H-OD21A | 184000 | 5435 | M |
| C200H-OD411 | 2631000 | 380 | M |
| C200H-OD501 | 300000 | 3333 | M |
| C200H-OV001 | 230000 | 4333 | M |
| C200H-PID01 | 177000 | | M |

| | | | |
|-----------------|---------|-------|---|
| C200H-PID02 | 177000 | | M |
| C200H-PID03 | 177000 | | M |
| C200H-PRO27 | 823000 | 1215 | M |
| C200H-PS211 | 173000 | 5780 | M |
| C200H-PS221 | 206000 | 4840 | M |
| C200H-PS221-C | 200000 | 4995 | M |
| C200H-RM001-P | 2175000 | 460 | M |
| C200H-RM001-PV1 | 2175000 | 460 | M |
| C200H-RM201 | 727000 | 1375 | M |
| C200H-RT001-P | 1705000 | 586 | M |
| C200H-RT002-P | 157000 | 6366 | M |
| C200H-RT201 | 746000 | 1339 | M |
| C200H-RT202 | 140000 | 7120 | M |
| C200HS-CPU01 | 297000 | 3357 | M |
| C200HS-CPU01-C | 284000 | 3511 | M |
| C200HS-CPU01-E | 297000 | 3357 | R |
| C200HS-CPU03 | 103000 | 9645 | M |
| C200HS-CPU03-E | 103000 | 9645 | M |
| C200HS-CPU21 | 220000 | 4545 | M |
| C200HS-CPU21-C | 212000 | 4700 | M |
| C200HS-CPU21-E | 220000 | 4545 | M |
| C200HS-CPU21-EC | 212000 | 4700 | M |
| C200HS-CPU23 | 93000 | 10729 | M |
| C200HS-CPU23-C | 97000 | 10241 | M |
| C200HS-CPU23-E | 93000 | 10729 | M |
| C200HS-CPU23-EC | 97000 | 10241 | M |
| C200HS-CPU31 | 225000 | 4440 | M |
| C200HS-CPU31-E | 225000 | 4440 | M |
| C200HS-CPU31-HT | 225000 | 4440 | M |
| C200HS-CPU33 | 90000 | 11111 | M |
| C200HS-CPU33-E | 90000 | 11111 | M |
| C200HS-INT01 | 1599000 | 625 | M |
| C200H-SLK11 | 187000 | 5337 | M |
| C200H-SLK21 | 197000 | 5063 | M |
| C200H-SLK21-V1 | 197000 | 5063 | M |
| C200HS-ME16K | 3225000 | 310 | M |
| C200HS-MP16K | 153000 | 6520 | M |
| C200HS-MP16K | 9057000 | 110 | M |
| C200H-SNT31 | 153000 | 6520 | M |
| C200HS-SLK12 | 187000 | 5348 | M |
| C200HS-SLK22 | 198000 | 5051 | M |
| C200HS-SNT32 | 211000 | 4733 | M |
| C200HS-TLK01 | 415000 | 2409 | M |
| C200H-TC001 | 168000 | | M |
| C200H-TC002 | 168000 | | M |
| C200H-TC003 | 168000 | | M |
| C200H-TC101 | 168000 | | M |
| C200H-TC102 | 168000 | | M |
| C200H-TC103 | 168000 | | M |
| C200H-TM001 | 1114000 | 898 | M |
| C200H-TS001 | 607000 | 1647 | M |
| C200H-TS002 | 610000 | 1639 | M |
| C200H-TS101 | 869000 | 1151 | M |
| C200H-TS102 | 870000 | 1149 | M |
| C200H-TV001 | 125000 | | M |
| C200H-TV002 | 125000 | | M |
| C200H-TV003 | 125000 | | M |
| C200H-TV101 | 125000 | | M |
| C200H-TV102 | 125000 | | M |
| C200H-TV103 | 125000 | | M |
| C200HW-BC022 | 270000 | | M |
| C200HW-BC031 | 256000 | 3905 | M |
| C200HW-BC051 | 235000 | 4239 | M |
| C200HW-BC081 | 165000 | 6031 | M |
| C200HW-BC101 | 158000 | 6305 | M |

| | | | |
|-----------------|---------|------|---|
| C200HW-BI031 | 274000 | 3650 | M |
| C200HW-BI051 | 254000 | 3923 | M |
| C200HW-BI081 | 173000 | 5774 | M |
| C200HW-BI101 | 165000 | 6050 | M |
| C200HW-CLK21 | 715000 | | M |
| C200HW-COM01 | 1795000 | 557 | M |
| C200HW-COM02 | 1297000 | 771 | M |
| C200HW-COM02-V1 | 1297000 | 771 | M |
| C200HW-COM03 | 712000 | 1404 | M |
| C200HW-COM03-V1 | 712000 | 1404 | M |
| C200HW-COM04 | 902000 | 1108 | M |
| C200HW-COM04-V1 | 902369 | | M |
| C200HW-COM05 | 1123000 | 890 | M |
| C200HW-COM05-V1 | 1123000 | 890 | M |
| C200HW-COM06 | 636000 | 1570 | M |
| C200HW-COM06-V1 | 636000 | 1570 | M |
| C200HW-DRM21 | 745000 | 1342 | M |
| C200HW-DRM21-V1 | 743887 | | M |
| C200HW-ME04K | 3181000 | 314 | M |
| C200HW-ME08K | 1987000 | 503 | M |
| C200HW-ME16K | 1948000 | 513 | M |
| C200HW-ME32K | 1948000 | 513 | M |
| C200HW-ME64K | 1948000 | 513 | M |
| C200HW-NC113 | 560728 | | M |
| C200HW-NC213 | 409781 | | M |
| C200HW-NC413 | 295279 | | M |
| C200HW-PA204 | 238000 | 4195 | M |
| C200HW-PA204R | 238000 | | M |
| C200HW-PA204S | 204000 | 4902 | M |
| C200HW-PA209R | 794000 | | R |
| C200HW-PCS01 | 477304 | | M |
| C200HW-PCS01-V1 | 477,304 | | R |
| C200HW-PCU01 | 477304 | | M |
| C200HW-PD024 | 1172000 | 853 | M |
| C200HW-SLK13 | 187000 | | M |
| C200HW-SLK14 | 187000 | | M |
| C200HW-SLK23 | 179000 | 5571 | M |
| C200HW-SLK24 | 179000 | 5571 | M |
| C200HW-SRM21 | 1801000 | 555 | M |
| C200HX-CPU34 | 692000 | 1445 | M |
| C200HX-CPU34D | 692000 | 1445 | M |
| C200HX-CPU34-E | 692000 | 1445 | M |
| C200HX-CPU34-Z | 692000 | 1445 | M |
| C200HX-CPU34-ZE | 692000 | 1445 | M |
| C200HX-CPU44 | 621000 | 1610 | M |
| C200HX-CPU44-E | 621000 | 1610 | M |
| C200HX-CPU44-Z | 621000 | 1610 | M |
| C200HX-CPU44-ZE | 621000 | 1610 | M |
| C200HX-CPU54 | 692000 | 1444 | M |
| C200HX-CPU54-E | 692000 | 1444 | M |
| C200HX-CPU54-Z | 692000 | 1444 | M |
| C200HX-CPU54-ZE | 692000 | 1444 | M |
| C200HX-CPU64 | 622000 | 1607 | M |
| C200HX-CPU64D | 622000 | 1607 | M |
| C200HX-CPU64-E | 622000 | 1607 | M |
| C200HX-CPU64-Z | 622000 | 1607 | M |
| C200HX-CPU64-ZE | 622000 | 1607 | M |
| C200HX-CPU65-Z | 622000 | 1607 | M |
| C200HX-CPU65-ZE | 622000 | 1607 | M |
| C200HX-CPU85-Z | 622000 | 1607 | M |
| C200HX-CPU85-ZE | 622000 | 1607 | M |
| C20-CPU72-IS | 120000 | 8333 | M |
| C20-CPU76-IS | 130000 | 7692 | M |
| C20HB-B7AK1 | 715000 | 1397 | R |
| C20HB-B7AM1 | 715000 | 1397 | M |

| | | | |
|-----------------|---------|-------|---|
| C20HB-CPU01 | 613000 | 1631 | M |
| C20HB-II001 | 8203000 | 122 | M |
| C20HB-LK201 | 2499000 | 400 | M |
| C20HB-LK202 | 264000 | 3787 | M |
| C20HB-LK501 | 251000 | 3978 | M |
| C20HB-MD211 | 1984000 | 504 | M |
| C20HB-MD212 | 1133000 | 882 | M |
| C20H-C1DR-D | 169000 | 5887 | M |
| C20H-C1DR-DE-V1 | 169000 | 5887 | M |
| C20H-C1DR-D-V1 | 169000 | 5887 | M |
| C20H-C1DT-DE-V1 | 169000 | 5887 | M |
| C20H-C2DR-D | 171000 | 5843 | M |
| C20H-C2DR-DE-V1 | 171000 | 5843 | M |
| C20H-C2DR-D-V1 | 171000 | 5843 | M |
| C20H-C2DT-DE-V1 | 171000 | 5843 | M |
| C20H-C3DR-D | 165000 | 6027 | M |
| C20H-C3DR-DE-V1 | 165000 | 6027 | M |
| C20H-C3DR-D-V1 | 165000 | 6027 | M |
| C20H-C3DT-DE-V1 | 165000 | 6027 | M |
| C20H-C5DR-D | 164000 | 6087 | M |
| C20H-C5DR-DE-V1 | 164000 | 6087 | M |
| C20H-C5DR-D-V1 | 164000 | 6087 | M |
| C20H-C5DT-DE-V1 | 164000 | 6087 | M |
| C20H-C6DR-D | 165000 | 6043 | M |
| C20H-C6DR-DE-V1 | 165000 | 6043 | M |
| C20H-C6DT-DE-V1 | 165000 | 6043 | M |
| C20H-C7DR-D | 160000 | 6227 | M |
| C20H-C7DR-DE-V1 | 160000 | 6227 | M |
| C20H-C7DR-D-V1 | 160000 | 6227 | M |
| C20H-C7DT-DE-V1 | 160000 | 6227 | M |
| C20H-EDR-D | 223000 | 4465 | M |
| C20-IP002-V1 | 451000 | 2213 | M |
| C20K-CAR-A | 135000 | 7375 | M |
| C20K-CAS1-A | 135000 | 7375 | M |
| C20K-CDR-A | 136000 | 7341 | M |
| C20K-CDR-D | 134000 | 7432 | M |
| C20K-CDS1-A | 136000 | 7341 | M |
| C20K-CDT1-A | 136000 | 7341 | M |
| C20K-CDT1-D | 134000 | 7432 | M |
| C20-LK201 | 451000 | 2213 | M |
| C20-LK201-V1 | 451000 | 2213 | M |
| C20-LK202 | 451000 | 2213 | M |
| C20-LK202-V1 | 451000 | 2213 | M |
| C20P-C1DR1-A | 136000 | 7341 | M |
| C20P-CA-A | 94000 | 10582 | M |
| C20P-CAR-A | 135000 | 7375 | M |
| C20P-CAS1-A | 135000 | 7375 | M |
| C20P-CD-A | 136000 | 7341 | M |
| C20P-CD-D | 134000 | 7432 | M |
| C20P-CDR-A | 136000 | 7341 | M |
| C20P-CDR-AE | 136000 | 7341 | M |
| C20P-CDR-D | 134000 | 7432 | M |
| C20P-CDS1-A | 136000 | 7341 | M |
| C20P-CDS-A | 136000 | 7341 | M |
| C20P-CDT1-A | 136000 | 7341 | M |
| C20P-CDT1-D | 134000 | 7432 | M |
| C20P-CDT-A | 136000 | 7341 | M |
| C20P-CDT-D | 134000 | 7432 | M |
| C20P-EA-A | 103000 | 9684 | M |
| C20P-EAR-A | 154000 | 6477 | M |
| C20P-EAS1-A | 154000 | 6477 | M |
| C20P-ED-A | 155000 | 6444 | M |
| C20P-ED-D | 153000 | 6536 | M |
| C20P-EDR1-A | 155000 | 6444 | M |
| C20P-EDR-A | 155000 | 6444 | M |

| | | | |
|-----------------|---------|-------|---|
| C20P-EDR-D | 153000 | 6536 | M |
| C20P-EDS1-A | 155000 | 6444 | M |
| C20P-EDS-A | 155000 | 6444 | M |
| C20P-EDT1-A | 155000 | 6444 | M |
| C20P-EDT1-D | 153000 | 6536 | M |
| C20P-EDT-A | 155000 | 6444 | M |
| C20P-EDT-D | 153000 | 6536 | M |
| C20PF-CDR-A | 136000 | 7341 | M |
| C20PF-CDS1-A | 136000 | 7341 | M |
| C20PF-CDT1-A | 136000 | 7341 | M |
| C20PF-MP104 | 1000000 | 1000 | M |
| C28H-C1DR-D | 157000 | 6338 | M |
| C28H-C1DR-DE-V1 | 157000 | 6338 | M |
| C28H-C1DR-D-V1 | 157000 | 6338 | M |
| C28H-C1DT-DE-V1 | 157000 | 6338 | M |
| C28H-C2DR-D | 158000 | 6294 | M |
| C28H-C2DR-DE-V1 | 158000 | 6294 | M |
| C28H-C2DR-D-V1 | 158000 | 6294 | M |
| C28H-C2DT-DE-V1 | 158000 | 6294 | M |
| C28H-C3DR-D | 154000 | 6478 | M |
| C28H-C3DR-DE-V1 | 154000 | 6478 | M |
| C28H-C3DR-D-V1 | 154000 | 6478 | M |
| C28H-C3DT-DE-V1 | 154000 | 6478 | M |
| C28H-C5DR-D | 152000 | 6538 | M |
| C28H-C5DR-DE-V1 | 152000 | 6538 | M |
| C28H-C5DR-D-V1 | 152000 | 6538 | M |
| C28H-C5DT-DE-V1 | 152000 | 6538 | M |
| C28H-C6DR-D | 154000 | 6494 | M |
| C28H-C6DR-DE-V1 | 154000 | 6494 | M |
| C28H-C6DR-D-V1 | 154000 | 6494 | M |
| C28H-C6DT-DE-V1 | 154000 | 6494 | M |
| C28H-C7DR-D | 149000 | 6678 | M |
| C28H-C7DR-DE-V1 | 149000 | 6678 | M |
| C28H-C7DR-D-V1 | 149000 | 6678 | M |
| C28H-C7DT-DE-V1 | 149000 | 6678 | M |
| C28H-EDR-D | 203000 | 4916 | M |
| C28K-CAR-A | 119000 | 8384 | M |
| C28K-CAS1-A | 119000 | 8384 | M |
| C28K-CDR-A | 119000 | 8353 | M |
| C28K-CDR-D | 118000 | 8445 | M |
| C28K-CDS1-A | 119000 | 8353 | M |
| C28K-CDT1-A | 119000 | 8353 | M |
| C28K-CDT1-D | 118000 | 8445 | M |
| C28P-C1DR1-A | 119000 | 8353 | M |
| C28P-CA-A | 86000 | 11591 | M |
| C28P-CAR-A | 119000 | 8384 | M |
| C28P-CAR-AE | 119000 | 8384 | M |
| C28P-CAS1-A | 119000 | 8384 | M |
| C28P-CD-A | 119000 | 8353 | M |
| C28P-CD-D | 118000 | 8445 | M |
| C28P-CDR-A | 119000 | 8353 | M |
| C28P-CDR-AE | 119000 | 8353 | M |
| C28P-CDR-D | 118000 | 8445 | M |
| C28P-CDR-DE | 118000 | 8445 | M |
| C28P-CDS1-A | 119000 | 8353 | M |
| C28P-CDS1-AK | 119000 | 8353 | M |
| C28P-CDS-A | 119000 | 8353 | M |
| C28P-CDT1-A | 119000 | 8353 | M |
| C28P-CDT1-D | 118000 | 8445 | M |
| C28P-CDT-A | 119000 | 8353 | M |
| C28P-CDT-AE | 119000 | 8353 | M |
| C28P-CDT-D | 118000 | 8445 | M |
| C28P-CDT-DE | 118000 | 8445 | M |
| C28P-EA-A | 93000 | 10694 | M |
| C28P-EAR-A | 133000 | 7487 | M |

| | | | |
|-----------------|--------|-------|---|
| C28P-EAS1-A | 133000 | 7487 | M |
| C28P-ED-A | 134000 | 7457 | M |
| C28P-ED-D | 132000 | 7548 | M |
| C28P-EDR1-A | 134000 | 7457 | M |
| C28P-EDR-A | 134000 | 7457 | M |
| C28P-EDR-D | 132000 | 7548 | M |
| C28P-EDS1-A | 134000 | 7457 | M |
| C28P-EDS-A | 134000 | 7457 | M |
| C28P-EDT1-A | 134000 | 7457 | M |
| C28P-EDT1-D | 132000 | 7548 | M |
| C28P-EDT-A | 134000 | 7457 | M |
| C28P-EDT-D | 132000 | 7548 | M |
| C28PF-CDR-A | 119000 | 8353 | M |
| C28PF-CDR-D | 118000 | 8445 | M |
| C28PF-CDS1-A | 119000 | 8353 | M |
| C28PF-CDT1-A | 119000 | 8353 | M |
| C40H-C1DR-D | 146000 | 6848 | M |
| C40H-C1DR-DE-V1 | 146000 | 6848 | M |
| C40H-C1DR-D-V1 | 146000 | 6848 | M |
| C40H-C1DT-DE-V1 | 146000 | 6848 | R |
| C40H-C2DR-D | 146000 | 6804 | M |
| C40H-C2DR-DE-V1 | 146000 | 6804 | M |
| C40H-C2DR-D-V1 | 146000 | 6804 | M |
| C40H-C2DT-DE-V1 | 146000 | 6804 | M |
| C40H-C3DR-D | 143000 | 6988 | M |
| C40H-C3DR-DE-V1 | 143000 | 6988 | M |
| C40H-C3DR-D-V1 | 143000 | 6988 | M |
| C40H-C3DT-DE-V1 | 143000 | 6988 | M |
| C40H-C3DT-D-V1 | 143000 | 6988 | M |
| C40H-C5DR-D | 141000 | 7048 | M |
| C40H-C5DR-DE-V1 | 141000 | 7048 | M |
| C40H-C5DR-D-V1 | 141000 | 7048 | M |
| C40H-C5DT-DE-V1 | 141000 | 7048 | M |
| C40H-C5DT-D-V1 | 141000 | 7048 | M |
| C40H-C6DR-D | 142000 | 7004 | M |
| C40H-C6DR-DE-V1 | 142000 | 7004 | M |
| C40H-C6DR-D-V1 | 142000 | 7004 | M |
| C40H-C6DT-DE-V1 | 142000 | 7004 | M |
| C40H-C7DR-D | 139000 | 7188 | M |
| C40H-C7DR-DE-V1 | 139000 | 7188 | M |
| C40H-C7DR-D-V1 | 139000 | 7188 | M |
| C40H-C7DT-DE-V1 | 139000 | 7188 | M |
| C40H-EDR-D | 184000 | 5426 | M |
| C40K-CAR-A | 98000 | 10175 | M |
| C40K-CAS1-A | 98000 | 10175 | M |
| C40K-CDR-A | 98000 | 10129 | M |
| C40K-CDR-D | 97000 | 10220 | M |
| C40K-CDS1-A | 98000 | 10129 | M |
| C40K-CDT1-A | 98000 | 10129 | M |
| C40K-CDT1-D | 97000 | 10220 | M |
| C40P-C1DR1-A | 98000 | 10129 | M |
| C40P-CA-A | 74000 | 13382 | M |
| C40P-CAR-A | 98000 | 10175 | M |
| C40P-CAS1-A | 98000 | 10175 | M |
| C40P-CD-A | 98000 | 10129 | M |
| C40P-CD-D | 97000 | 10220 | M |
| C40P-CDR-A | 98000 | 10129 | M |
| C40P-CDR-AE | 98000 | 10129 | M |
| C40P-CDR-D | 97000 | 10220 | M |
| C40P-CDR-DE | 97000 | 10220 | M |
| C40P-CDS1-A | 98000 | 10129 | M |
| C40P-CDS-A | 98000 | 10129 | M |
| C40P-CDT1-A | 98000 | 10129 | M |
| C40P-CDT1-D | 97000 | 10220 | M |
| C40P-CDT-A | 98000 | 10129 | M |

| | | | |
|---------------|---------|-------|---|
| C40P-CDT-AE | 98000 | 10129 | M |
| C40P-CDT-D | 97000 | 10220 | M |
| C40P-EA-A | 79000 | 12570 | M |
| C40P-EAR-A | 106000 | 9363 | M |
| C40P-EAS1-A | 106000 | 9363 | M |
| C40P-ED-A | 107000 | 9317 | M |
| C40P-ED-D | 106000 | 9409 | M |
| C40P-EDR1-A | 107000 | 9317 | M |
| C40P-EDR-A | 107000 | 9317 | M |
| C40P-EDR-D | 106000 | 9409 | M |
| C40P-EDS1-A | 107000 | 9317 | M |
| C40P-EDS-A | 107000 | 9317 | M |
| C40P-EDT1-A | 107000 | 9317 | M |
| C40P-EDT1-D | 106000 | 9409 | M |
| C40P-EDT-A | 107000 | 9317 | M |
| C40P-EDT-D | 106000 | 9409 | M |
| C40PF-CDR-A | 98000 | 10129 | M |
| C40PF-CDR-D | 97000 | 10220 | M |
| C40PF-CDS1-A | 98000 | 10129 | M |
| C40PF-CDT1-A | 98000 | 10129 | M |
| C4K-AD | 148000 | 6733 | M |
| C4K-AD | 200000 | 5000 | M |
| C4K-IA | 558000 | 1790 | M |
| C4K-ID | 585000 | 1709 | M |
| C4K-OR2 | 470000 | 2126 | M |
| C4K-OS2 | 470000 | 2126 | M |
| C4K-OT2 | 470000 | 2126 | M |
| C4K-TM | 387000 | 2583 | M |
| C500-AD101 | 98000 | 10146 | M |
| C500-AD501 | 43848 | | M |
| C500-ASC03 | 467000 | 2140 | M |
| C500-ASC03-G | 467000 | 2140 | M |
| C500-ASC04 | 467000 | 2140 | M |
| C500-ASC04-G | 467000 | 2140 | M |
| C500-ASP01 | 521000 | 1917 | M |
| C500-ASP02 | 675000 | 1480 | M |
| C500-BC031 | 4003000 | 250 | M |
| C500-BC061 | 3389000 | 295 | M |
| C500-BC091 | 3003000 | 333 | M |
| C500-CN312N | 1204000 | 830 | M |
| C500-CP131 | 173000 | 5780 | M |
| C500-CT021 | 398000 | 2511 | M |
| C500-CT041 | 175000 | 5695 | M |
| C500-DA101 | 78000 | 12807 | M |
| C500-DA101-T | 100000 | 10000 | M |
| C500-DA103 | 124000 | 8020 | M |
| C500-DT021 | 47000 | 21172 | M |
| C500-DT022 | 47000 | 21172 | M |
| C500-FZ001 | 108000 | 9182 | M |
| C500-GDI11 | 220000 | 4534 | M |
| C500-GDI12 | 187000 | 5327 | M |
| C500-GPI01 | 261000 | 3830 | M |
| C500-IA122-G | 190000 | 5241 | M |
| C500-IA123 | 418000 | 2392 | M |
| C500-ID215-G | 245000 | 4072 | M |
| C500-ID218-FK | 245000 | 4072 | M |
| C500-ID219 | 122000 | 8145 | M |
| C500-ID219-FK | 280000 | 3565 | M |
| C500-IDA02 | 517000 | 1931 | M |
| C500-IDA22 | 517000 | 1931 | M |
| C500-IDS01 | 673000 | 1485 | M |
| C500-IDS01-V1 | 580000 | 1722 | M |
| C500-IDS02 | 444000 | 2248 | M |
| C500-IDS21 | 580000 | 1722 | M |
| C500-IDS22 | 444000 | 2248 | M |

| | | | |
|-----------------|---------|-------|---|
| C500-LDP01 | 521000 | 1917 | M |
| C500-LDP01-V1 | 521000 | | M |
| C500-LK010-H | 248000 | 4032 | M |
| C500-NC112 | 113000 | | M |
| C500-NC113 | 650559 | | M |
| C500-NC211 | 55591.4 | | M |
| C500-NC221-E | 54000 | 18354 | M |
| C500-NC222 | 47000 | 20953 | M |
| C500-NC222-E | 47000 | 20953 | M |
| C500-OA121-G | 506000 | 1973 | M |
| C500-OA223-FK | 941000 | 1062 | M |
| C500-OA223-G | 433000 | 2308 | M |
| C500-OA226 | 5112181 | | M |
| C500-OC224-E | 100000 | 10000 | M |
| C500-OD212-G | 192000 | 5185 | M |
| C500-OD213 | 182000 | 5477 | M |
| C500-OD213-FK | 277000 | 3604 | M |
| C500-OD218-G | 189000 | 5287 | M |
| C500-OD219 | 369000 | 2709 | M |
| C500-OD412-G | 189000 | 5287 | M |
| C500-PRW06 | 481000 | 2077 | M |
| C500-PS213 | 160000 | 6250 | M |
| C500-PS213-E | 160000 | 6250 | M |
| C500-PS221-FK | 333000 | 3000 | M |
| C500-RT002-V1H | 276000 | 3623 | M |
| C500-SNT31-V4 | 121000 | 8262 | M |
| C500-TS101-D | 190000 | 5259 | M |
| C500-TS501 | 47415 | | M |
| C500-TS502 | 42408 | | M |
| C60H-C1DR-DE-V1 | 104000 | 9552 | M |
| C60H-C1DR-D-V1 | 104000 | 9552 | M |
| C60H-C1DT-DE-V1 | 104000 | 9552 | M |
| C60H-C1DT-D-V1 | 104000 | 9552 | M |
| C60H-C2DR-DE-V1 | 105000 | 9508 | M |
| C60H-C2DR-D-V1 | 105000 | 9508 | M |
| C60H-C2DT-DE-V1 | 105000 | 9508 | M |
| C60H-C2DT-D-V1 | 105000 | 9508 | M |
| C60H-C3DR-DE-V1 | 103000 | 9692 | M |
| C60H-C3DR-D-V1 | 103000 | 9692 | M |
| C60H-C3DT-DE-V1 | 103000 | 9692 | M |
| C60H-C3DT-D-V1 | 103000 | 9692 | M |
| C60H-C5DR-DE-V1 | 102000 | 9752 | M |
| C60H-C5DR-D-V1 | 102000 | 9752 | M |
| C60H-C5DT-DE-V1 | 102000 | 9752 | M |
| C60H-C5DT-D-V1 | 102000 | 9752 | M |
| C60H-C6DR-DE-V1 | 103000 | 9708 | M |
| C60H-C6DR-D-V1 | 103000 | 9708 | M |
| C60H-C6DT-DE-V1 | 103000 | 9708 | M |
| C60H-C6DT-D-V1 | 103000 | 9708 | M |
| C60H-C7DR-DE-V1 | 101000 | 9892 | M |
| C60H-C7DR-D-V1 | 101000 | 9892 | M |
| C60H-C7DT-DE-V1 | 101000 | 9892 | M |
| C60H-C7DT-D-V1 | 101000 | 9892 | M |
| C60H-EDR-D | 168000 | 5937 | M |
| C60H-EDT-D | 168000 | 5937 | M |
| C60P-CAR-A | 53000 | 18733 | M |
| C60P-CAS1-A | 53000 | 18733 | M |
| C60P-CD-A | 54000 | 18282 | M |
| C60P-CDR-A | 54000 | 18282 | M |
| C60P-CDR-D | 54000 | 18373 | M |
| C60P-CDS1-A | 54000 | 18282 | M |
| C60P-CDS1-AK | 54000 | 18282 | M |
| C60P-CDT1-A | 54000 | 18282 | M |
| C60P-CDT1-D | 54000 | 18373 | M |
| C60P-EAR-A | 63000 | 15647 | M |

| | | | |
|-----------------|---------|-------|---|
| C60P-EAS1-A | 63000 | 15647 | M |
| C60P-ED-A | 65000 | 15361 | M |
| C60P-EDR-A | 65000 | 15361 | M |
| C60P-EDR-D | 64000 | 15453 | M |
| C60P-EDS1-A | 65000 | 15361 | M |
| C60P-EDT1-A | 65000 | 15361 | M |
| C60P-EDT1-D | 64000 | 15453 | M |
| C60PF-CDR-A | 54000 | 18282 | M |
| C60PF-CDR-D | 54000 | 18373 | M |
| C60PF-CDS1-A | 54000 | 18282 | M |
| C60PF-CDT1-A | 54000 | 18282 | M |
| CPM1-10CDR-A | 290000 | 3444 | M |
| CPM1-10CDR-D | 567000 | 1762 | M |
| CPM1-20CDR-A | 251000 | 3983 | M |
| CPM1-20CDR-D | 434000 | 2301 | M |
| CPM1-20EDR | 842000 | 1186 | M |
| CPM1-30CDR-A | 219000 | 4562 | M |
| CPM1-30CDR-D | 347000 | 2880 | M |
| CPM1A-10CDR-A | 646000 | 1548 | M |
| CPM1A-10CDR-D | 878000 | 1140 | M |
| CPM1A-10CDT1-D | 650618 | 1537 | M |
| CPM1A-10CDT-D | 650618 | 1537 | M |
| CPM1A-20CDR-A | 584000 | 1711 | M |
| CPM1A-20CDR-D | 767000 | 1303 | M |
| CPM1A-20CDT1-D | 514933 | 1942 | M |
| CPM1A-20CDT-D | 514933 | 1942 | M |
| CPM1A-20EDR | 2010000 | 498 | M |
| CPM1A-20EDT | 1061571 | 942 | M |
| CPM1A-20EDT1 | 1061571 | 942 | M |
| CPM1A-30CDR-A | 290000 | 3445 | M |
| CPM1A-30CDR-D | 638000 | 1568 | M |
| CPM1A-30CDT1-D | 414079 | 2415 | M |
| CPM1A-30CDT-D | 414079 | 2415 | M |
| CPM1A-40CDR-A | 279000 | 3590 | M |
| CPM1A-40CDR-D | 584000 | 1711 | M |
| CPM1A-40CDT1-D | 362056 | 2762 | M |
| CPM1A-40CDT-D | 362056 | 2762 | M |
| CPM1A-MAD01 | 139000 | | A |
| CPM1-CIF01 | 1553000 | 644 | M |
| CPM1-CIF11 | 1470000 | 680 | M |
| CQM1-AD041 | 526000 | 1900 | M |
| CQM1-B7A01 | 573000 | 1744 | M |
| CQM1-B7A02 | 830000 | 1204 | M |
| CQM1-B7A03 | 461000 | 2169 | M |
| CQM1-B7A12 | 806000 | 1240 | M |
| CQM1-B7A13 | 450000 | 2222 | M |
| CQM1-B7A21 | 453000 | 2205 | M |
| CQM1-CIF01 | 6578000 | 152 | M |
| CQM1-CIF02 | 6535000 | 153 | M |
| CQM1-CIF11 | 1303000 | 767 | M |
| CQM1-CPU11 | 418000 | 2391 | M |
| CQM1-CPU21 | 409000 | 2443 | M |
| CQM1-CPU41 | 445000 | 2247 | M |
| CQM1-CPU41-E | 445000 | 2247 | M |
| CQM1-CPU41-EV1 | 445000 | 2247 | M |
| CQM1-CPU41-V1 | 445000 | 2247 | M |
| CQM1-CPU42 | 404000 | 2473 | M |
| CQM1-CPU42-E | 404000 | 2473 | M |
| CQM1-CPU42-EV1 | 404000 | 2473 | M |
| CQM1-CPU42-V1 | 404000 | 2473 | M |
| CQM1-CPU43 | 307000 | 3247 | M |
| CQM1-CPU43-E | 307000 | 3247 | M |
| CQM1-CPU43-E-IT | 307000 | 3247 | M |
| CQM1-CPU43-EV1 | 307000 | 3247 | M |
| CQM1-CPU43-V1 | 307000 | 3247 | M |

| | | | |
|----------------|-----------|------|---|
| CQM1-CPU44 | 313000 | 3187 | M |
| CQM1-CPU44-E | 313000 | 3187 | M |
| CQM1-CPU44-EV1 | 313000 | 3187 | M |
| CQM1-CPU44-V1 | 313000 | 3187 | M |
| CQM1-CPU45-EV1 | 115000 | | R |
| CQM1-DA021 | 495000 | 2020 | M |
| CQM1-DRT21 | 640000 | 1561 | M |
| CQM1-G7M21 | 656000 | 1524 | M |
| CQM1-G7N01 | 1949000 | 513 | M |
| CQM1-G7N11 | 1941000 | 515 | M |
| CQM1H-ABB21 | 210000 | 4740 | A |
| CQM1H-AVB41 | 4668000 | 214 | A |
| CQM1H-CPU11 | 356000 | 2804 | A |
| CQM1H-CPU21 | 326000 | 3058 | A |
| CQM1H-CPU51/61 | 305000 | 3272 | A |
| CQM1H-CTB41 | 120000 | 8276 | A |
| CQM1H-ME16K | 3418000 | 292 | A |
| CQM1H-ME16R | 3273000 | 305 | A |
| CQM1H-PLB21 | 302000 | 3307 | A |
| CQM1H-SCB41 | 388000 | 2575 | A |
| CQM1-IA121 | 434000 | 2304 | M |
| CQM1-IA221 | 433000 | 2305 | M |
| CQM1-ID111 | 1041000 | 960 | M |
| CQM1-ID112 | 798000 | 1252 | M |
| CQM1-ID211 | 1713000 | 584 | M |
| CQM1-ID212 | 1041000 | 960 | M |
| CQM1-ID213 | 798000 | 1252 | M |
| CQM1-IPS01 | 1250000 | 800 | M |
| CQM1-IPS02 | 666000 | 1500 | M |
| CQM1-LK501 | 903000 | 1106 | M |
| CQM1-LSE01 | 150000 | 6623 | M |
| CQM1-LSE02 | 150000 | 6623 | M |
| CQM1-ME04K | 8316000 | 120 | M |
| CQM1-ME04R | 6163000 | 162 | M |
| CQM1-ME08K | 4240000 | 236 | M |
| CQM1-ME08R | 3538000 | 283 | M |
| CQM1-MP08K | 123915000 | 8 | M |
| CQM1-MP08R | 20325000 | 49 | M |
| CQM1-OA221 | 493000 | 2028 | M |
| CQM1-OA222 | 450000 | 2222 | M |
| CQM1-OC221 | 1294000 | 773 | M |
| CQM1-OC222 | 743000 | 1346 | M |
| CQM1-OD211 | 762000 | 1312 | M |
| CQM1-OD212 | 937000 | 1067 | M |
| CQM1-OD213 | 1042000 | 959 | M |
| CQM1-OD214 | 1720000 | 581 | M |
| CQM1-OD215 | 1579000 | 633 | M |
| CQM1-PA203 | 1312000 | 762 | M |
| CQM1-PA206 | 694000 | 1440 | M |
| CQM1-PA216 | 566000 | 1766 | M |
| CQM1-PD026 | 697000 | 1434 | M |
| CQM1-PRO01 | 823000 | 1215 | M |
| CQM1-SRM21 | 2083000 | 480 | M |
| CQM1-TC001 | 250000 | 4000 | M |
| CQM1-TC002 | 250000 | 4000 | M |
| CQM1-TC101 | 250000 | 4000 | M |
| CQM1-TC102 | 250000 | 4000 | M |
| CS1G-CPU42-E | 185000 | 5381 | R |
| CS1G-CPU43 | 185000 | 5405 | M |
| CS1G-CPU43-E | 185000 | 5381 | R |
| CS1G-CPU44 | 185000 | 5405 | M |
| CS1G-CPU44-E | 185000 | 5381 | R |
| CS1G-CPU45 | 185000 | 5405 | M |
| CS1G-CPU45-E | 185000 | 5381 | R |
| CS1H-CPU63 | 184000 | 5434 | M |

| | | | |
|------------------|---------|-------|---|
| CS1H-CPU63-E | 184000 | 5413 | R |
| CS1H-CPU64 | 184000 | 5434 | M |
| CS1H-CPU64-E | 184000 | 5413 | R |
| CS1H-CPU65 | 183000 | 5464 | M |
| CS1H-CPU65-E | 183000 | 5452 | R |
| CS1H-CPU66 | 183000 | 5464 | M |
| CS1H-CPU66-E | 183000 | 5452 | R |
| CS1H-CPU67-E | 194000 | 5145 | R |
| CS1W-AD041 | 246000 | | M |
| CS1W-AD081 | 241000 | | M |
| CS1W-BC023 | 1373000 | 728 | M |
| CS1W-BC033 | 939000 | 1064 | M |
| CS1W-BC053 | 905000 | 1104 | M |
| CS1W-BC083 | 728000 | 1373 | M |
| CS1W-BC103 | 741000 | 1349 | M |
| CS1W-BI033 | 975000 | 1025 | M |
| CS1W-BI053 | 939000 | 1064 | M |
| CS1W-BI083 | 787000 | 1270 | M |
| CS1W-BI103 | 763000 | 1310 | M |
| CS1W-CLK11 | 191000 | 5228 | M |
| CS1W-CLK21 | 565000 | 1769 | M |
| CS1W-DA041 | 199000 | | M |
| CS1W-DA08C | 170000 | | M |
| CS1W-DA08V | 198000 | | M |
| CS1W-ETN01 | 155000 | | M |
| CS1W-ID291 | 94000 | 10626 | M |
| CS1W-MAD44 | 111000 | 8969 | M |
| CS1W-MD291 | 102000 | 9794 | M |
| CS1W-MD292 | 102000 | 9794 | M |
| CS1W-OD291 | 111000 | 8014 | R |
| CS1W-OD292 | 111000 | 8014 | R |
| CS1W-SCB21 | 408000 | 2449 | R |
| CS1W-SCB41 | 256000 | 3898 | R |
| CS1W-SCU21 | 263000 | 3801 | R |
| CV1000-CPU01 | 157000 | 6335 | M |
| CV1000-CPU01-E | 157000 | 6335 | M |
| CV1000-CPU01-EV1 | 157000 | 6335 | M |
| CV1000-CPU01-V1 | 157000 | 6335 | M |
| CV1000-DM151 | 138000 | 7201 | M |
| CV1000-DM251 | 148000 | 6743 | M |
| CV1000-DM641 | 147000 | 6801 | M |
| CV2000-CPU01 | 174000 | 5743 | M |
| CV2000-CPU01-EV1 | 157000 | 6335 | M |
| CV2000-CPU01-V1 | 157000 | 6335 | M |
| CV500-BC031 | 2741000 | 365 | M |
| CV500-BC051 | 2724000 | 367 | M |
| CV500-BC101 | 4347000 | 230 | M |
| CV500-BC105 | 3906000 | 256 | M |
| CV500-BI042 | 3793000 | 264 | M |
| CV500-BI062 | 3762000 | 266 | M |
| CV500-BI111 | 5102000 | 196 | M |
| CV500-BI112 | 5485000 | 182 | M |
| CV500-BSC11 | 143000 | 6971 | M |
| CV500-BSC21 | 135000 | 7376 | M |
| CV500-BSC31 | 295000 | 3379 | M |
| CV500-BSC41 | 264000 | 3785 | M |
| CV500-BSC51 | 307000 | 3249 | M |
| CV500-BSC61 | 273000 | 3654 | M |
| CV500-CIF01 | 2270000 | 441 | M |
| CV500-CPU01 | 158000 | 6293 | M |
| CV500-CPU01-E | 158000 | 6293 | M |
| CV500-CPU01-EV1 | 158000 | 6293 | M |
| CV500-CPU01-V1 | 158000 | 6293 | M |
| CV500-DAC11 | 160000 | 6232 | M |
| CV500-ETN01 | 221000 | 4513 | M |

| | | | |
|-----------------|---------|--------|---|
| CV500-FDD01 | 9000 | 102243 | M |
| CV500-FDD02 | 4000 | 202255 | M |
| CV500-FHD01 | 5000 | 168739 | M |
| CV500-FHD02 | 5000 | 168739 | M |
| CV500-HDD01 | 5000 | 168525 | M |
| CV500-HDD02 | 5000 | 168525 | M |
| CV500-HDD11 | 136000 | 7324 | M |
| CV500-IC101 | 991000 | 1009 | M |
| CV500-IC201 | 1319000 | 758 | M |
| CV500-IC301 | 1430000 | 699 | M |
| CV500-IF001 | 1361000 | 734 | M |
| CV500-II101 | 664000 | 1506 | M |
| CV500-II201 | 865000 | 1155 | M |
| CV500-IPS01 | 135000 | 7407 | M |
| CV500-ISX01 | 1277000 | 783 | M |
| CV500-KYB01 | 222000 | 4505 | M |
| CV500-LK201 | 145000 | 6875 | M |
| CV500-MAP01 | 315000 | 3175 | M |
| CV500-MC221 | 151000 | 6617 | M |
| CV500-MC421 | 122000 | 8152 | M |
| CV500-MCW01 | 181000 | 5516 | M |
| CV500-MIF01 | 720000 | 1387 | M |
| CV500-MP601 | 2599000 | | M |
| CV500-MP602 | 1846000 | 542 | M |
| CV500-MR261 | 423000 | 2361 | M |
| CV500-MR262 | 485000 | 2061 | M |
| CV500-MR601 | 2599000 | 385 | M |
| CV500-PS211 | 135000 | 7407 | M |
| CV500-PS221 | 135000 | 7407 | M |
| CV500-RM001-PV1 | 272000 | | M |
| CV500-RM001-V1 | 272000 | | M |
| CV500-RM211 | 195000 | 5128 | M |
| CV500-RM221 | 270000 | 3704 | M |
| CV500-RT001-PV1 | 294000 | | M |
| CV500-RT001-V1 | 294000 | | M |
| CV500-RT002-PV1 | 277000 | | M |
| CV500-RT002-V1 | 277000 | | M |
| CV500-RT211 | 207000 | 4831 | M |
| CV500-RT221 | 294000 | 3401 | M |
| CV500-SLK11 | 175000 | 5685 | M |
| CV500-SLK21 | 242000 | 4128 | M |
| CV500-SNT31 | 113000 | 8826 | M |
| CV500-TLK01 | 402000 | 2482 | M |
| CV500-UP111-E | 140000 | 7117 | M |
| CV500-UP121-E | 138000 | 7217 | M |
| CV500-VP111 | 140000 | 7117 | M |
| CV500-VP111-E | 140000 | 7117 | M |
| CV500-VP121 | 138000 | 7217 | M |
| CV500-VP121-E | 138000 | 7217 | M |
| CV500-VP213 | 165000 | 6058 | M |
| CV500-VP213-E | 165000 | 6058 | M |
| CV500-VP217 | 143000 | 6974 | M |
| CV500-VP217-E | 143000 | 6974 | M |
| CV500-VP223 | 165000 | 6058 | M |
| CV500-VP223-E | 165000 | 6058 | M |
| CV500-VP227 | 143000 | 6974 | M |
| CV500-VP227-E | 143000 | 6974 | M |
| CV510-MAP01 | 315000 | 3175 | R |
| CVM1-BC053 | 4739000 | 211 | M |
| CVM1-BC103 | 4739000 | 211 | M |
| CVM1-BI064 | 5464000 | 183 | M |
| CVM1-BI114 | 5464000 | 183 | M |
| CVM1-CPU01 | 187000 | 5342 | M |
| CVM1-CPU01-EV1 | 158000 | 6293 | M |
| CVM1-CPU01-EV2 | 158000 | 6293 | M |

| | | | |
|---------------------|----------|--------|---|
| CVM1-CPU01-V1 | 158000 | 6293 | M |
| CVM1-CPU01-V2 | 158000 | 6293 | M |
| CVM1-CPU11 | 180000 | 5543 | M |
| CVM1-CPU11-EV1 | 157000 | 6335 | M |
| CVM1-CPU11-EV2 | 157000 | 6335 | M |
| CVM1-CPU11-V1 | 157000 | 6335 | M |
| CVM1-CPU11-V2 | 157000 | 6335 | M |
| CVM1-CPU21-EV2 | 157000 | 6335 | M |
| CVM1-CPU21-V2 | 157000 | 6335 | M |
| CVM1-CPU21-V2 | 157000 | 6335 | R |
| CVM1D-BC051 | 417000 | | M |
| CVM1D-BI101 | 612000 | | M |
| CVM1D-BI102 | 642000 | | M |
| CVM1D-CPU21 | 183000 | | M |
| CVM1D-DPL01 | 140000 | | M |
| CVM1D-PA208 | 559000 | | M |
| CVM1D-PA212 | 135000 | | M |
| CVM1-DRM21 | 745000 | 1342 | M |
| CVM1-DRM21-V1 | 745000 | | M |
| CVM1-MP201-V1 | 428000 | 2335 | M |
| CVM1-MP701 | 17452000 | 57 | M |
| CVM1-PA208 | 559000 | 1788 | M |
| CVM1-PRO01 | 420000 | 2381 | M |
| CVM1-PRS21-EV1 | 428000 | 2335 | M |
| CVM1-PRS21-V1 | 428000 | 2335 | M |
| CVM1-PRS71 | 428000 | 2335 | M |
| DRT1-AD04H | 108000 | | A |
| DRT1-COM | 322439 | | R |
| DRT1-DA02 | 260000 | | A |
| DRT1-HD16S | 138000 | | A |
| DRT1-ID08 | 340000 | | A |
| DRT1-ID16 | 242000 | | A |
| DRT1-ID16P | 226000 | | R |
| DRT1-ID16X | 256000 | | A |
| DRT1-ND16S | 149000 | | A |
| DRT1-OD08 | 307000 | | A |
| DRT1-OD16 | 256000 | | A |
| DRT1-OD16P | 201000 | | R |
| DRT1-OD16X | 223000 | | A |
| DRT1-TS04P | 108000 | | A |
| DRT1-TS04T | 108000 | | A |
| DRT-AD04 | 123000 | | A |
| EEROM-H | 14992000 | 67 | M |
| FC-9801-RF1 | 110000 | 9091 | M |
| FC-9813-FD2 | 12000 | 83333 | M |
| FIT10-IF001-V1 | 3898000 | 257 | M |
| FIT10-IF002 | 470000 | 2126 | M |
| FIT10-IF003 | 419000 | 2383 | M |
| FIT10-SET11 | 13000 | 71942 | M |
| FIT10-SET11-E | 13000 | 71942 | M |
| FIT20-CPN01 | 20000 | 49549 | M |
| FIT20-CPU01 | 20000 | 49549 | M |
| FIT20-EXA01 | 18000 | 52838 | M |
| FU200-11 | 8000 | 125000 | M |
| FU210-11 | 8000 | 125000 | M |
| FU210-13 | 8000 | 125000 | M |
| FU301-10 | 8000 | 125000 | M |
| FU302-10 | 8000 | 125000 | M |
| FU500-10 | 8000 | 125000 | M |
| FZ-3000 | 122000 | 8197 | M |
| FZ-3010 | 122000 | 8197 | M |
| G70D-SOC16-1 DC24 | 85000 | | R |
| G71-OD16 DC12 | 147000 | | R |
| G72C-VID16-VA DC24 | 87800 | | R |
| G730-ROC04 DC SPEC. | 82000 | | R |

| | | | |
|----------------------|----------|------|---|
| G7TC-OC16 DC12 (P7TF | 112000 | | R |
| GL10S1-C1DR-D | 169000 | 5917 | M |
| GL10S1-C2DR-D | 171000 | 5848 | M |
| GL10S1-C3DR-D | 165000 | 6061 | M |
| GL10S1-C5DR-D | 164000 | 6098 | M |
| GL10S1-C6DR-D | 165000 | 6061 | M |
| GL10S1-C7DR-D | 160000 | 6250 | M |
| GL10S1-EDR-D | 223000 | 4484 | M |
| GL10S2-C1DR-D | 157000 | 6369 | M |
| GL10S2-C2DR-D | 158000 | 6329 | M |
| GL10S2-C3DR-D | 154000 | 6494 | M |
| GL10S2-C5DR-D | 152000 | 6579 | M |
| GL10S2-C6DR-D | 154000 | 6494 | M |
| GL10S2-C7DR-D | 149000 | 6711 | M |
| GL10S2-EDR-D | 203000 | 4926 | M |
| GL10S3-C1DR-D | 146000 | 6849 | M |
| GL10S3-C2DR-D | 146000 | 6849 | M |
| GL10S3-C3DR-D | 143000 | 6993 | M |
| GL10S3-C5DR-D | 141000 | 7092 | M |
| GL10S3-C6DR-D | 142000 | 7042 | M |
| GL10S3-C7DR-D | 139000 | 7194 | M |
| GL10S3-EDR-D | 184000 | 5435 | M |
| GL10S-AD001 | 122000 | 8197 | M |
| GL10S-BC031 | 7680000 | 130 | M |
| GL10S-BC051-V1 | 10416000 | 96 | M |
| GL10S-BC081-V1 | 7874000 | 127 | M |
| GL10S-DA001 | 124000 | 8065 | M |
| GL10S-DAC01 | 303000 | 3300 | M |
| GL10S-ID212 | 1782000 | 561 | M |
| GL10S-IDS01 | 596000 | 1678 | M |
| GL10S-IDS21 | 596000 | 1678 | M |
| GL10S-OC222 | 1157000 | 864 | M |
| GL10S-PR027 | 823000 | 1215 | M |
| GL10S-PS211 | 173000 | 5780 | M |
| GL10S-PS221 | 206000 | 4854 | M |
| GT1-AD08MX | 168000 | | R |
| GT1-CT01 | 176000 | | A |
| GT1-DA04MX | 194000 | | R |
| GT1-ID16 | 488525 | | R |
| GT1-ID16(-1) | 567000 | | R |
| GT1-ID16-1 | 488525 | | R |
| GT1-ID16DS | 569939 | | R |
| GT1-ID16DS(-1) | 566000 | | R |
| GT1-ID16DS-1 | 569939 | | R |
| GT1-ID16ML | 570589 | | R |
| GT1-ID16ML(-1) | 566000 | | R |
| GT1-ID16ML-1 | 570589 | | R |
| GT1-ID16MX | 425380 | | R |
| GT1-ID16MX(-1) | 425000 | | R |
| GT1-ID16MX-1 | 425380 | | R |
| GT1-ID32ML | 259224 | | R |
| GT1-ID32ML(-1) | 259000 | | R |
| GT1-ID32ML-1 | 259224 | | R |
| GT1-OD16 | 406415 | | R |
| GT1-OD16(-1) | 453000 | | R |
| GT1-OD16-1 | 395861 | | R |
| GT1-OD16DS | 455254 | | R |
| GT1-OD16DS(-1) | 453000 | | R |
| GT1-OD16DS-1 | 455254 | | R |
| GT1-OD16ML | 455669 | | R |
| GT1-OD16ML(-1) | 453000 | | R |
| GT1-OD16ML-1 | 455669 | | R |
| GT1-OD16MX | 450341 | | R |
| GT1-OD16MX(-1) | 438000 | | R |
| GT1-OD16MX-1 | 437418 | | R |

| | | | |
|-----------------|----------|--------|---|
| GT1-OD32ML | 302698 | | R |
| GT1-OD32ML(-1) | 291000 | | R |
| GT1-OD32ML-1 | 291136 | | R |
| GT1-ROP08 | 913279 | | R |
| GT1-ROP08 | 913000 | | R |
| GT1-ROS16 | 560822 | | R |
| GT1-ROS16 | 561000 | | R |
| HMC-AP001 | 3.44E+11 | | R |
| HMC-EE151 | 198000 | 5048 | M |
| HMC-EE641 | 208400 | 4798 | M |
| HMC-EF171 | 8130000 | 123 | M |
| HMC-EF371 | 6130000 | 163 | M |
| HMC-EF861 | 10530000 | 95 | M |
| HMC-EP161 | 478000 | 2090 | M |
| HMC-EP551 | 917000 | 1090 | M |
| HMC-ES151 | 429000 | 2330 | M |
| HMC-ES251 | 219000 | 4550 | M |
| HMC-ES551 | 111000 | 8990 | M |
| HMC-ES641 | 819000 | 1220 | M |
| IDSC-C1DT-A | 156000 | 6410 | M |
| KC2T-AL001 | 3300000 | 303 | M |
| NT10S-CFL01 | 20000 | 50000 | M |
| NT10S-SF121 | 47000 | 21277 | M |
| NT10S-SF122 | 123000 | 8130 | M |
| NT11S | 143500 | 6969 | R |
| NT2000M-CFL01 | 10000 | 100000 | M |
| NT2000M-DN131 | 210000 | 4762 | M |
| NT2000M-DN131B | 212000 | 4713 | M |
| NT2000M-DT131 | 218000 | 4570 | M |
| NT2000M-DT131 | 218000 | 4570 | R |
| NT20M-DF121 | 151000 | 6623 | M |
| NT20M-DF121-DFN | 369000 | 2710 | M |
| NT20M-DF121-E | 151000 | 6623 | M |
| NT20M-DF121-V1 | 151000 | 6623 | M |
| NT20M-DF125 | 145000 | 6892 | M |
| NT20M-DF125-E | 145000 | 6892 | M |
| NT20M-DF125-V1 | 145000 | 6892 | M |
| NT20M-DN121-V2 | 2138000 | 468 | M |
| NT20M-DN131 | 369000 | 2710 | M |
| NT20M-DT121 | 146000 | 6840 | M |
| NT20M-DT121-E | 146000 | 6840 | M |
| NT20M-DT121-V1 | 146000 | 6840 | M |
| NT20M-DT121-V2 | 2138000 | 468 | M |
| NT20M-DT125 | 140000 | 7112 | M |
| NT20M-DT125-E | 140000 | 7112 | M |
| NT20M-DT125-V1 | 140000 | 7112 | M |
| NT20M-DT131 | 369000 | 2710 | M |
| NT20M-DT132 | 369000 | 2710 | M |
| NT20M-IF001 | 8326000 | 120 | M |
| NT20M-LB121 | 430000 | 2326 | M |
| NT20M-LB121-V1 | 430000 | 2325 | M |
| NT20M-LB121-V2 | 430000 | 2326 | M |
| NT20M-LK201 | 1330000 | 752 | M |
| NT20M-LK201-DF | 500000 | 2000 | M |
| NT20M-LK201-EV1 | 1331000 | 751 | M |
| NT20M-LK201-V1 | 1331000 | 751 | M |
| NT20M-LK201-V2 | 1331000 | 751 | M |
| NT20M-LK202 | 1624000 | 615 | M |
| NT20M-LK202-EV1 | 1625000 | 615 | M |
| NT20M-LK202-V1 | 1625000 | 615 | M |
| NT20M-LK202-V2 | 1625000 | 615 | M |
| NT20M-LK203 | 500000 | 2000 | M |
| NT20M-LK203-EV1 | 1331000 | 751 | M |
| NT20M-LK203-V1 | 1331000 | 751 | M |
| NT20M-LK203-V2 | 1331000 | 751 | M |

| | | | |
|--------------------|----------|--------|---|
| NT20M-LPM11 | 1065000 | 939 | M |
| NT20M-LPM11-V1 | 1065000 | 939 | M |
| NT20M-LPM11-V2 | 1065000 | 939 | M |
| NT20M-LPM12 | 1065000 | 939 | M |
| NT20M-LPM13 | 816000 | 1225 | M |
| NT20M-MD211 | 1060000 | 943 | M |
| NT20M-MD212 | 349000 | 2861 | M |
| NT20M-RT121 | 604000 | 1656 | M |
| NT20M-RT121-EV1 | 558000 | 1791 | M |
| NT20M-RT121-V1 | 604000 | 1656 | M |
| NT20M-RT121-V2 | 558000 | 1791 | M |
| NT20M-RT221 | 570000 | 1754 | M |
| NT20M-RT221-V2 | 570000 | 1754 | M |
| NT20M-SMR06 | 816000 | 1225 | M |
| NT20S-ST121 | 238000 | 4198 | M |
| NT20S-ST121B | 238000 | 4198 | M |
| NT20S-ST121B-V1 | 238000 | 4198 | M |
| NT20S-ST121B-V2 | 238000 | 4198 | M |
| NT20S-ST121-V2 | 238000 | 4198 | M |
| NT20S-ST122B-V1 | 206000 | 4853 | M |
| NT20S-ST122-V1 | 206000 | 4853 | M |
| NT20S-ST128 | 238000 | 4198 | M |
| NT20S-ST128B | 238000 | 4198 | M |
| NT20S-ST161B-V3 | 238000 | | M |
| NT30C-CFL01 | 10000 | 100000 | M |
| NT30-CFL01 | 10000 | 100000 | M |
| NT30C-ST141 | 217000 | 4599 | M |
| NT30C-ST141B | 217000 | 4599 | M |
| NT30C-ST141B-EK | 216000 | 4621 | M |
| NT30C-ST141-EK | 216000 | 4621 | M |
| NT30-ST131 | 217000 | 4599 | M |
| NT30-ST131B | 217000 | 4599 | M |
| NT30-ST131B-EK | 217000 | 4599 | M |
| NT30-ST131-EK | 217000 | 4599 | M |
| NT31C-ST121 | 197200 | | R |
| NT31C-ST141(B) STN | 197200 | | A |
| NT31C-ST141B | 197200 | | M |
| NT31C-TT141B | 105700 | 9462 | M |
| NT31-ST121 | 197200 | | R |
| NT31-ST121(B) STN | 197200 | | A |
| NT31-ST121B | 197200 | | M |
| NT31-TT121B | 106300 | 9406 | M |
| NT600G-DF211 | 62000 | 15958 | M |
| NT600G-DF212 | 64000 | 15570 | M |
| NT600G-DF213 | 63000 | 15873 | M |
| NT600G-DT211 | 60000 | 16462 | M |
| NT600G-DT212 | 62000 | 16129 | M |
| NT600G-DT213 | 60000 | 16667 | M |
| NT600G-MP151 | 3092000 | 323 | M |
| NT600G-MR151 | 1154000 | 866 | M |
| NT600G-MR251 | 2452000 | 408 | M |
| NT600G-MR641 | 2143000 | 466 | M |
| NT600G-SMR01A | 10000000 | 100 | M |
| NT600G-SMR02A | 10000000 | 100 | M |
| NT600G-SMR03A | 10000000 | 100 | M |
| NT600M-DF121 | 101000 | 9814 | M |
| NT600M-DF121-E | 101000 | 9814 | M |
| NT600M-DF122 | 103000 | 9677 | M |
| NT600M-DN122 | 189000 | 5291 | M |
| NT600M-DN211 | 747000 | 1339 | M |
| NT600M-DT121 | 92000 | 10799 | M |
| NT600M-DT121-E | 92000 | 10799 | M |
| NT600M-DT122 | 94000 | 10636 | M |
| NT600M-DT211 | 704000 | 1420 | M |
| NT600M-IF001 | 8326000 | 120 | M |

| | | | | |
|---------------------|----------|-------|---|-----------------------|
| NT600M-LB121 | 430000 | 2325 | M | |
| NT600M-LB122 | 470000 | 2125 | M | |
| NT600M-LK201 | 1819000 | 550 | M | |
| NT600M-LK202 | 2450000 | 408 | M | |
| NT600M-LMP31 | 606000 | 1650 | R | |
| NT600M-LPM31 | 606000 | 1650 | M | |
| NT600M-MB121 | 430000 | 2325 | R | |
| NT600M-MD211 | 1060000 | 943 | M | |
| NT600M-MP251 | 24154000 | 41 | M | |
| NT600M-MR151 | 3559000 | 281 | M | |
| NT600M-MR251 | 2080000 | 481 | M | |
| NT600M-MR641 | 2680000 | 373 | M | |
| NT600M-RT121 | 604000 | 1656 | M | |
| NT600M-RT221 | 643000 | 1555 | M | |
| NT600MS-CPU01 | 178000 | 5618 | M | |
| NT600MS-DT211 | 119000 | 8380 | M | |
| NT600M-SMR01 | 20000000 | 50 | M | |
| NT600M-SMR01-E | 20000000 | 50 | M | |
| NT600M-SMR02 | 20000000 | 50 | M | |
| NT600M-SMR03 | 20000000 | 50 | M | |
| NT600M-SMR04 | 20000000 | 50 | M | |
| NT600MV-DT211 | 73000 | 13537 | M | |
| NT600S-ST121 | 236000 | 4224 | M | |
| NT600S-ST121B | 236000 | 4224 | M | |
| NT600S-ST121B-V1 | 236000 | 4224 | M | |
| NT600S-ST121B-V2 | 236000 | 4224 | M | |
| NT600S-ST121-V1 | 236000 | 4224 | M | |
| NT600S-ST121-V2 | 236000 | 4224 | M | |
| NT600S-ST211 | 87000 | 11459 | M | |
| NT600S-ST211B | 87000 | 11459 | M | |
| NT600S-ST211B-V1 | 87000 | 11459 | M | |
| NT600S-ST211B-V2 | 87000 | 11459 | M | |
| NT600S-ST211-V1 | 87000 | 11459 | M | |
| NT600S-ST211-V2 | 87000 | 11459 | M | |
| NT610C-DT151 | 35000 | 28335 | M | |
| NT610C-DT151B-V1 | 124000 | 8049 | M | |
| NT610C-DT151-V1 | 124000 | 8049 | M | |
| NT610G-DT211 | 69000 | 14310 | M | |
| NT610G-MF161 | 647000 | 1543 | M | |
| NT611G-DT211 | 70000 | 14171 | M | |
| NT611G-DT211B | 70000 | 14171 | M | |
| NT612G-DT211 | 70000 | 14182 | M | |
| NT612G-DT211B | 70000 | 14182 | M | |
| NT620C-ST141 | 148000 | 6718 | M | |
| NT620C-ST141B | 148000 | 6718 | M | |
| NT620C-ST141B-E | 148000 | 6718 | M | |
| NT620C-ST141B-EK | 148000 | 6718 | M | |
| NT620C-ST141-E | 148000 | 6718 | M | |
| NT620C-ST141-EK | 148000 | 6718 | M | |
| NT620C-ST142 | 148000 | 6718 | M | |
| NT620C-ST142B | 148000 | 6718 | M | |
| NT620S-ST211 | 300000 | 3328 | M | |
| NT620S-ST211B | 300000 | 3328 | M | |
| NT620S-ST211B-EK | 300000 | 3327 | M | |
| NT620S-ST211-E | 300000 | 3328 | M | |
| NT620S-ST211-EK | 300000 | 3327 | M | |
| NT620S-ST212B | 300000 | 3328 | M | |
| NT625C-ST152 | 136400 | 7330 | M | |
| NT631C-ST141(B) STN | 143400 | | A | (Display unit=50,000) |
| NT631C-ST141B | 143400 | | M | |
| NT631C-ST151(B) TFT | 145300 | | A | (Display unit=30,000) |
| NT631C-ST151B | 145300 | | M | |
| NT631C-ST151-V1 | 145300 | | M | |
| NT631-ST121B | 89200 | | R | |
| NT631-ST211(B) EL | 89200 | | A | (Display unit=30,000) |

| | | | |
|-----------------|---------|-------|---|
| NT631-ST211B | 89200 | | M |
| NT-AL001 | 996000 | 1003 | M |
| NT-B7A16 | 708000 | 1411 | M |
| NT-FK200 | 1298000 | 770 | M |
| R88A-E11 | 100000 | 10000 | M |
| R88A-RG08U | 500000 | 2000 | M |
| R88A-RG08UA | 500000 | 2000 | M |
| R88A-RG50 | 500000 | 2000 | M |
| R88D-UA* | 500000 | | R |
| R88D-UA02HA | 500000 | 2000 | M |
| R88D-UA02V | 500000 | 2000 | M |
| R88D-UA03HA | 500000 | 2000 | M |
| R88D-UA03LA | 500000 | 2000 | M |
| R88D-UA03V | 500000 | 2000 | M |
| R88D-UA04HA | 500000 | 2000 | M |
| R88D-UA04LA | 500000 | 2000 | M |
| R88D-UA04V | 500000 | 2000 | M |
| R88D-UA08HA | 500000 | 2000 | M |
| R88D-UA08V | 500000 | 2000 | M |
| R88D-UA10LA | 500000 | 2000 | M |
| R88D-UA12HA | 500000 | 2000 | M |
| R88D-UA12LA | 500000 | 2000 | M |
| R88D-UA12V | 500000 | 2000 | M |
| R88D-UA15LA | 500000 | 2000 | M |
| R88D-UA20HA | 500000 | 2000 | M |
| R88D-UA20V | 500000 | 2000 | M |
| R88D-UPEP* | 500000 | | R |
| R88D-UPEP04H | 500000 | 2000 | M |
| R88D-UPEP04V | 500000 | 2000 | M |
| R88D-UPEP08H | 500000 | 2000 | M |
| R88D-UPEP08V | 500000 | 2000 | M |
| R88D-UPEP10L | 500000 | 2000 | M |
| R88D-UPEP12H | 500000 | 2000 | M |
| R88D-UPEP12L | 500000 | 2000 | M |
| R88D-UPEP12L-R2 | 500000 | 2000 | M |
| R88D-UPEP12V | 500000 | 2000 | M |
| R88D-UPEP15L | 500000 | 2000 | M |
| R88D-UPEP20H | 500000 | 2000 | M |
| R88D-UPEP20V | 500000 | 2000 | M |
| R88D-UP* | 500000 | | R |
| R88D-UP02HA | 500000 | 2000 | M |
| R88D-UP02V | 500000 | 2000 | M |
| R88D-UP03HA | 500000 | 2000 | M |
| R88D-UP03L | 500000 | 2000 | M |
| R88D-UP03LA | 500000 | 2000 | M |
| R88D-UP03V | 500000 | 2000 | M |
| R88D-UP04HA | 500000 | 2000 | M |
| R88D-UP04HA | 500000 | 2000 | M |
| R88D-UP04LA | 500000 | 2000 | M |
| R88D-UP04V | 500000 | 2000 | M |
| R88D-UP04W | 500000 | 2000 | M |
| R88D-UP08HA | 500000 | 2000 | M |
| R88D-UP08V | 500000 | 2000 | M |
| R88D-UP10LA | 500000 | 2000 | M |
| R88D-UP10W | 500000 | 2000 | M |
| R88D-UP12HA | 500000 | 2000 | M |
| R88D-UP12LA | 500000 | 2000 | M |
| R88D-UP12L-R1 | 500000 | 2000 | M |
| R88D-UP12V | 500000 | 2000 | M |
| R88D-UP12W | 500000 | 2000 | M |
| R88D-UP15LA | 500000 | 2000 | M |
| R88D-UP20HA | 500000 | 2000 | M |
| R88D-UP20V | 500000 | 2000 | M |
| R88D-UT* | 500000 | | R |
| R88D-UT02V | 500000 | 2000 | M |

| | | | |
|---------------------|--------|------|---|
| R88D-UT04V | 500000 | 2000 | M |
| R88D-UT04W | 500000 | 2000 | M |
| R88D-UT08V | 500000 | 2000 | M |
| R88D-UT10W | 500000 | 2000 | M |
| R88D-UT110H | 500000 | 2000 | M |
| R88D-UT120H | 500000 | 2000 | M |
| R88D-UT12V | 500000 | 2000 | M |
| R88D-UT12W | 500000 | 2000 | M |
| R88D-UT15W | 500000 | 2000 | M |
| R88D-UT160H-E | 500000 | 2000 | M |
| R88D-UT20V | 500000 | 2000 | M |
| R88D-UT24H | 500000 | 2000 | M |
| R88D-UT40H | 500000 | 2000 | M |
| R88D-UT40H-E | 500000 | 2000 | M |
| R88D-UT60H | 500000 | 2000 | M |
| R88D-UT60H-E | 500000 | 2000 | M |
| R88D-UT80H | 500000 | 2000 | M |
| R88D-UT80H-E | 500000 | 2000 | M |
| R88M-U030* | 69000 | | R |
| R88M-U03030H | 69000 | | M |
| R88M-U03030HA | 69000 | | M |
| R88M-U03030HA-B | 69000 | | M |
| R88M-U03030HA-BG33E | 69000 | | M |
| R88M-U03030HA-G05B | 69000 | | M |
| R88M-U03030HA-G09B | 69000 | | M |
| R88M-U03030HA-G21BJ | 69000 | | M |
| R88M-U03030HA-G33B | 69000 | | M |
| R88M-U03030HA-G33BJ | 69000 | | M |
| R88M-U03030HA-S1 | 69000 | | M |
| R88M-U03030H-BS1 | 69000 | | M |
| R88M-U03030H-G21BK | 69000 | | M |
| R88M-U03030LA | 69000 | | M |
| R88M-U03030LA-B | 69000 | | M |
| R88M-U03030LA-G33BJ | 69000 | | M |
| R88M-U03030LA-OS1 | 69000 | | M |
| R88M-U03030LA-S1 | 69000 | | M |
| R88M-U03030L-BS1 | 69000 | | M |
| R88M-U03030SA | 69000 | | M |
| R88M-U03030SA-B | 69000 | | M |
| R88M-U03030TA | 69000 | | M |
| R88M-U03030TA-B | 69000 | | M |
| R88M-U03030TA-BG33E | 69000 | | M |
| R88M-U03030TA-G33B | 69000 | | M |
| R88M-U03030V | 69000 | | M |
| R88M-U03030VA-BS1 | 69000 | | M |
| R88M-U03030VA-S1 | 69000 | | M |
| R88M-U050* | 69000 | | R |
| R88M-U05030HA | 69000 | | M |
| R88M-U05030HA-B | 69000 | | M |
| R88M-U05030HA-G05B | 69000 | | M |
| R88M-U05030HA-G21B | 69000 | | M |
| R88M-U05030HA-G33BJ | 69000 | | M |
| R88M-U05030HA-S1 | 69000 | | M |
| R88M-U05030H-BS1 | 69000 | | M |
| R88M-U05030LA | 69000 | | M |
| R88M-U05030LA-B | 69000 | | M |
| R88M-U05030LA-BG09B | 69000 | | M |
| R88M-U05030LA-BOS1 | 69000 | | M |
| R88M-U05030LA-G09B | 69000 | | M |
| R88M-U05030LA-G09BJ | 69000 | | M |
| R88M-U05030LA-G33B | 69000 | | M |
| R88M-U05030LA-G33BJ | 69000 | | M |
| R88M-U05030LA-S1 | 69000 | | M |
| R88M-U05030L-BS1 | 69000 | | M |
| R88M-U05030SA | 69000 | | M |

| | | |
|---------------------|--------|---|
| R88M-U05030SA-B | 69000 | M |
| R88M-U05030TA | 69000 | M |
| R88M-U05030TA-B | 69000 | M |
| R88M-U05030TA-G21B | 69000 | M |
| R88M-U05030TA-G33BF | 69000 | M |
| R88M-U05030VA-BS1 | 69000 | M |
| R88M-U05030VA-S1 | 69000 | M |
| R88M-U05030W | 69000 | M |
| R88M-U40030* | 69000 | R |
| R88M-U40030HA | 69000 | M |
| R88M-U40030HA-B | 69000 | M |
| R88M-U40030HA-BG05E | 69000 | M |
| R88M-U40030HA-BG05E | 69000 | M |
| R88M-U40030HA-BG05E | 69000 | M |
| R88M-U40030HA-BG05C | 69000 | M |
| R88M-U40030HA-BG09C | 69000 | M |
| R88M-U40030HA-BG11E | 69000 | M |
| R88M-U40030HA-BG11E | 69000 | M |
| R88M-U40030HA-BG21E | 69000 | M |
| R88M-U40030HA-BG25C | 69000 | M |
| R88M-U40030HA-BG33E | 69000 | M |
| R88M-U40030HA-BG33E | 69000 | M |
| R88M-U40030HA-BS1 | 69000 | M |
| R88M-U40030HA-G05B | 69000 | M |
| R88M-U40030HA-G05BF | 69000 | M |
| R88M-U40030HA-G05BJ | 69000 | M |
| R88M-U40030HA-G05CJ | 69000 | M |
| R88M-U40030HA-G09CJ | 69000 | M |
| R88M-U40030HA-G11B | 69000 | M |
| R88M-U40030HA-G11BJ | 69000 | M |
| R88M-U40030HA-G15CJ | 69000 | M |
| R88M-U40030HA-G21B | 69000 | M |
| R88M-U40030HA-G21BJ | 69000 | M |
| R88M-U40030HA-G25CJ | 69000 | M |
| R88M-U40030HA-G33BJ | 69000 | M |
| R88M-U40030HA-S1 | 69000 | M |
| R88M-U40030TA | 69000 | M |
| R88M-U40030TA-B | 69000 | M |
| R88M-U40030TA-BG11B | 69000 | M |
| R88M-U40030TA-BG11B | 69000 | M |
| R88M-U40030TA-BS1 | 69000 | M |
| R88M-U40030TA-G05B | 69000 | M |
| R88M-U40030TA-G11B | 69000 | M |
| R88M-U40030TA-G11BJ | 69000 | M |
| R88M-U40030TA-G21B | 69000 | M |
| R88M-U40030TA-G21BJ | 69000 | M |
| R88M-U40030TA-G33BJ | 69000 | M |
| R88M-U40030TA-S1 | 69000 | M |
| R88M-U40030V | 69000 | M |
| R88M-U40030VA-BS1 | 69000 | M |
| R88M-U40030VA-S1 | 69000 | M |
| R88M-U40030V-BS1 | 69000 | M |
| R88M-U40030V-S1 | 69000 | M |
| R88M-U75030* | 160000 | R |
| R88M-U75030HA | 160000 | M |
| R88M-U75030HA-B | 160000 | M |
| R88M-U75030HA-BG05E | 160000 | M |
| R88M-U75030HA-BG11E | 160000 | M |
| R88M-U75030HA-BG11E | 160000 | M |
| R88M-U75030HA-BG15C | 160000 | M |
| R88M-U75030HA-BS1 | 160000 | M |
| R88M-U75030HA-G05B | 160000 | M |
| R88M-U75030HA-G05BJ | 160000 | M |
| R88M-U75030HA-G05CJ | 160000 | M |
| R88M-U75030HA-G09CJ | 160000 | M |

| | | | |
|---------------------|---------|-------|---|
| R88M-U75030HA-G11B | 160000 | | M |
| R88M-U75030HA-G11BJ | 160000 | | M |
| R88M-U75030HA-G15CJ | 160000 | | M |
| R88M-U75030HA-G21B | 160000 | | M |
| R88M-U75030HA-G21BJ | 160000 | | M |
| R88M-U75030HA-G33B | 160000 | | M |
| R88M-U75030HA-G33BF | 160000 | | M |
| R88M-U75030HA-G33BJ | 160000 | | M |
| R88M-U75030HA-S1 | 160000 | | M |
| R88M-U75030HA-W | 160000 | | M |
| R88M-U75030TA | 160000 | | M |
| R88M-U75030TA-B | 160000 | | M |
| R88M-U75030TA-BG05B | 160000 | | M |
| R88M-U75030TA-BG05E | 160000 | | M |
| R88M-U75030TA-BG33B | 160000 | | M |
| R88M-U75030TA-BS1 | 160000 | | M |
| R88M-U75030TA-G11B | 160000 | | M |
| R88M-U75030TA-G21B | 160000 | | M |
| R88M-U75030TA-S1 | 160000 | | M |
| R88M-U75030V | 160000 | | M |
| R88M-U75030VA-BS1 | 160000 | | M |
| R88M-U75030VA-S1 | 160000 | | M |
| R88M-U75030V-BS1 | 160000 | | M |
| R88M-UE10030* | 160000 | | R |
| R88M-UE10030H-BS1 | 160000 | | M |
| R88M-UE10030H-S1 | 160000 | | M |
| R88M-UE10030L-BG05C | 160000 | | M |
| R88M-UE10030L-BS1 | 160000 | | M |
| R88M-UE10030L-G09CJ | 160000 | | M |
| R88M-UE10030L-S1 | 160000 | | M |
| R88M-UE10030V-BS1 | 160000 | | M |
| R88M-UE10030V-S1 | 160000 | | M |
| R88M-UE20030* | 160000 | | R |
| R88M-UE20030H-BS1 | 160000 | | M |
| R88M-UE20030H-G25CJ | 160000 | | M |
| R88M-UE20030H-S1 | 160000 | | M |
| R88M-UE20030L-BS1 | 160000 | | M |
| R88M-UE20030L-R2 | 160000 | | M |
| R88M-UE20030L-S1 | 160000 | | M |
| R88M-UE20030V-BS1 | 160000 | | M |
| R88M-UE20030V-S1 | 160000 | | M |
| R88M-UE30030* | 160000 | | R |
| R88M-UE30030L-BS1 | 160000 | | M |
| R88M-UE30030L-S1 | 160000 | | M |
| R88M-UE40030* | 160000 | | R |
| R88M-UE40030H-BS1 | 160000 | | M |
| R88M-UE40030H-G09CJ | 160000 | | M |
| R88M-UE40030H-G25CJ | 160000 | | M |
| R88M-UE40030H-S1 | 160000 | | M |
| R88M-UE40030V-BS1 | 160000 | | M |
| R88M-UE40030V-S1 | 160000 | | M |
| R88M-UE75030* | 160000 | | R |
| R88M-UE75030H-BS1 | 160000 | | M |
| R88M-UE75030H-G25CJ | 160000 | | M |
| R88M-UE75030H-S1 | 160000 | | M |
| R88M-UE75030V-BS1 | 160000 | | M |
| R88M-UE75030V-S1 | 160000 | | M |
| R88S-H* | 500000 | | R |
| R88S-H205G | 500000 | | M |
| R88S-H306G | 500000 | | M |
| R88S-H310G | 500000 | | M |
| ROM-I | 3333000 | 300 | M |
| S3200-CPS03 | 20000 | 50000 | M |
| S3200-LSU03 | 55000 | 18182 | M |
| S3200-LSU03-01E | 55000 | 18182 | M |

| | | | |
|----------------------|---------|-------|---|
| S3200-LSU03-V1 | 55000 | 18182 | M |
| S3200-NSB03 | 78000 | 12821 | M |
| S3200-NSB03-V1 | 78000 | 12821 | M |
| S3200-NSB03-V2 | 78000 | 12821 | M |
| S3200-NSB11-E | 78000 | 12821 | M |
| S3200-NSU-1-V1 | 25000 | 40000 | M |
| S3200-NSU-2-V1 | 25000 | 40000 | M |
| S3200-NSUA1-00E | 25000 | 40000 | M |
| S3200-NSUA1-10 | 25000 | 40000 | M |
| S3200-NSUG4-00E | 19000 | 52632 | M |
| S3200-NSUG4-10 | 19000 | 52632 | M |
| SCYM5R-IO021 | 196000 | 5100 | M |
| Servo U/UE driver | 500000 | | R |
| SK20-C1DR-D | 437000 | 2288 | M |
| SK20-C1DT-D | 347000 | 2874 | M |
| SK20-C2DR-D | 462000 | 2163 | M |
| SK20-C2DT-D | 371000 | 2694 | M |
| SP10-AL001 | 5931000 | 169 | M |
| SP10-CIF01 | 5271000 | 190 | M |
| SP10-DR-A | 216000 | 4622 | M |
| SP10-DR-D | 411000 | 2431 | M |
| SP10-DT-A | 228000 | 4383 | M |
| SP10-DT-D | 456000 | 2192 | M |
| SP10-PRO01-V1 | 121000 | 8223 | M |
| SP16-DR-A | 233000 | 4292 | M |
| SP16-DR-D | 252000 | 3963 | M |
| SP16-DT-A | 250000 | 3999 | M |
| SP16-DT-D | 273000 | 3652 | M |
| SP20-DR-A | 203000 | 4922 | M |
| SP20-DR-D | 233000 | 4275 | M |
| SP20-DT-A | 236000 | 4222 | M |
| SP20-DT-D | 258000 | 3875 | M |
| SRM1-CO1 | 286000 | | R |
| SRM1-CO2 | 282000 | | R |
| SRT1-ID16T | 438006 | | R |
| SRT1-ID16T-1 | 438006 | | R |
| SRT1-MD16T | 413019 | | R |
| SRT1-MD16T-1 | 413019 | | R |
| SRT1-OD04S DC SPEC. | 245000 | | R |
| SRT1-OD16T | 422804 | | R |
| SRT1-OD16T-1 | 422804 | | R |
| SRT1-TID04S DC SPEC. | 397000 | | R |
| SRT1-XID04S DC SPEC. | 1720000 | | R |
| T1000H-CPU01-EV1H | 92000 | 10870 | M |
| T1000H-CPU01-V1H | 92000 | 10870 | M |
| T1000H-IP006-V1 | 421000 | 2375 | M |
| T1000H-MP302-V1 | 2037000 | 491 | M |
| T1000H-MP402-V1 | 2037000 | 491 | M |
| T1000H-MP602-V1 | 980000 | 1020 | M |
| T1000H-MP702-V1 | 2037000 | 491 | M |
| T1000H-TLK01 | 421000 | 2373 | M |
| T200H-CPU01 | 363000 | 2755 | M |
| T200H-IA121 | 1900000 | 526 | M |
| T200H-IA122 | 1000000 | 1000 | M |
| T200H-ID211 | 3800000 | 263 | M |
| T200H-ID212 | 3400000 | 294 | M |
| T200H-MIF01 | 599000 | 1669 | M |
| T200H-MIF01-V1 | 599000 | 1669 | M |
| T200H-OA221 | 1300000 | 769 | M |
| T200H-OC221 | 60000 | 16667 | M |
| T200H-OC224 | 45000 | 22222 | M |
| T200H-OC225 | 20000 | 48309 | M |
| T200H-OD212 | 4000000 | 250 | M |
| T200H-OD213 | 3500000 | 286 | M |
| T200H-OD411 | 6997000 | 143 | M |