


Pass & Seymour




Hospital Grade Devices Straight Blade Plugs & Connectors

2 Pole, 3 Wire Grounding 15 & 20A, 125 & 250V

IP20
Suitability




PS5266XHG




PS5269XHG



PS5266HGAN



PS8115



PS8119

Features – Extra-Hard Use (EHU)

- Unit arrives completely ready-to-wire, cuts installation time significantly.
- Nylon housing provides impact and chemical resistance.
- Rugged two-piece cord grip provides more uniform cord retention.
- Internal dust shield keeps terminals free of contaminants.
- Tri-drive assembly screws are standard on Hospital Grade plugs and connectors (angle plugs not included).
- All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.
- Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.
- Cord-grip screws recessed to protect installer against screwdriver head slippage.

Catalog Number	Rating A. V.	Description	Cord Diameter	NEMA Config. No.	3rd Party Compliance		
					UL498	FSUL WC596	C22.2 No. 42
Hospital Grade – Extra-Hard Use (EHU)							
PS5266XHG	15 125	Plug, Black & Clear	.230"-.720"	5-15P	•	•	•
PS5266HGAN	15 125	Angle Plug, Black & Clear	.320"-.655"	5-15P	•	•	•
PS5269XHG	15 125	Connector, Black & Clear	.230"-.720"	5-15R	•	•	•
PS5366XHG	20 125	Plug, Black & Clear	.230"-.720"	5-20P	•	•	•
PS5366HGAN	20 125	Angle Plug, Black & Clear	.320"-.655"	5-20P	•	•	•
PS5369XHG	20 125	Connector, Black & Clear	.230"-.720"	5-20R	•	•	•
PS5666XHG	15 250	Plug, Black & Clear	.230"-.720"	6-15P	•	•	•
PS5666HGAN	15 250	Angle Plug, Black & Clear	.320"-.655"	6-15P	•	•	•
PS5669XHG	15 250	Connector, Black & Clear	.230"-.720"	6-15R	•	•	•
PS5466XHG	20 250	Plug, Black & Clear	.230"-.720"	6-20P	•	•	•
PS5466HGAN	20 250	Angle Plug, Black & Clear	.320"-.655"	6-20P	•	•	•
PS5469XHG	20 250	Connector, Black & Clear	.230"-.720"	6-20R	•	•	•
Hospital Grade MaxGrip® M³							
PS8115	15 125	Plug, Gray	.230"-.720"	5-15P	•	•	•
PS8119	15 125	Connector, Gray	.230"-.720"	5-15R	•	•	•



NEMA
5-15P



NEMA
5-15R



NEMA
6-15P



NEMA
6-15R



NEMA
5-20P



NEMA
5-20R



NEMA
6-20P



NEMA
6-20R

Catalog Number	Description
Accessories	
EHU15AN	15 & 20A EHU Straight Blade, Right Angle Adapter
FC22GL	EHU-Strain Relief Grip*
FC30GL	EHU-Strain Relief Grip*
FC40GL	EHU-Strain Relief Grip*
FC52GL	EHU-Strain Relief Grip*

*For further information consult the Flexcor® Section L.