



TFC Split Ferrite in plastic case for panel mounting



A high quality range of easy fit hinged ferrite clamps with the unique feature of being able to panel mount the units using a 3mm screw and/or adhesive tape. The units employ high performance Nickel-Zinc ferrites giving them high performance against high frequency noise. Suitable for single or multiple cables.

The plastic case has UL94V-0 approval.



Mounting Clip

Specification

KItagawa Part No	Farnell Code	Dimensions					Impedance Ω 1 turn		Impedance Ω 2 turn		Maximum Cable Dia
		A	B	C	D	E	25MHz	100MHz	25MHz	100MHz	
TFCM-16-8-16 (Fig1)	9415858	19.8	7.6	21.9	22.3		73	139	300	597	7.2
TFC-20-10-10 (Fig2)	9415866	24.2	8.8	13.5	27.9	19.6	47	92	192	410	8.5
TFC-23-11-14 (Fig2)	9415874	27.4	10.8	17.5	33.9	23.9	72	132	301	547	10.5
TFC-25-15-12 (Fig2)	9415840	28.6	13.6	15.4	35.2	21.8	41	88	167	390	13.0
TFP2014-T (fig3)	9415882	20.0	13.5	7.2	4.8	-	Mounting Part with adhesive tape				
TFP2014-V (fig3)	9415890	20.0	13.5	7.2	4.8	-	Mounting part for Screw (\varnothing 3.4mm)				