


8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	5/6/08	D.GRIFFIN
B	ECN 99999: DELETED "PVC" FROM CABLE CALLOUT	8/7/08	D.CASTRO
C	ECN 3695: ADDED 1M & 4M LENGTHS	11/7/08	D.CASTRO



(2X) 20 PIN DISPLAYPORT MALE CONNECTOR

WIRING MAP				
CABLE	"P1"	SIGNAL NAME	COLOR	"P2"
TWISTED PAIR 1	1	ML_LANE 0(p)	BROWN	12
	2	GND	DRAIN	11
	3	ML_LANE 0(n)	WHITE	10
TWISTED PAIR 2	4	ML_LANE 1(p)	RED	9
	5	GND	DRAIN	8
TWISTED PAIR 3	6	ML_LANE 1(n)	WHITE	7
	7	ML_LANE 2(p)	GREEN	6
	8	GND	DRAIN	5
TWISTED PAIR 4	9	ML_LANE 2(n)	WHITE	4
	10	ML_LANE 3(p)	ORANGE	3
	11	GND	DRAIN	2
TWISTED PAIR 5	12	ML_LANE 3(n)	WHITE	1
	13	GND	BROWN	13
	14	GND	RED	14
	15	AUX CH(p)	BLUE	15
	16	GND	DRAIN	16
	17	AUX CH(n)	WHITE	17
	18	HOT PLUG DETECT	YELLOW	18
	19	DP_PWR RETURN	ORANGE	19
	20	N/A	N/C	20
	SHELL	GND	BRAID	SHELL

CABLE: (5) SHIELDED TWISTED PAIR 30AWG WITH 30 AWG DRAIN WIRE.
 (4) 30 AWG SINGLE CONDUCTORS.
 JACKET: BLACK, LOW SMOKE, ZERO HALOGEN.

PART NUMBER	LENGTH	
	FEET	METERS
DPCAZMM-1M	3.28	1.0
DPCAZMM-2M	6.56	2.0
DPCAZMM-3M	9.84	3.0
DPCAZMM-4M	13.12	4.0

RoHS Compliant ✓

NOTES:
 CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
 CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED IN A POLYBAG.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY D.CASTRO	5/1/08				
OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = -2[51] / -0 >60 [1524] ≤ 120 [3048] = +4 / -0 >120 [3048] ≤ 300 [7620] = +6 / -0 >300 [7620] = +5% / -0%	CHECKED BY J.RUST	5/1/08	CATEGORY VIDEO			
	ALL OTHER DIMENSIONAL TOLERANCES: $.X = .3$ $.XX = .15$	APPROVED BY G.PEPIN	5/1/08	PRODUCT DESCRIPTION DISPLAYPORT CABLE LSZH M/M		
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. DPCAZMM	REV. C
			SCALE: NONE	CAD FILE: DPCAZMM.SLDRW	SHEET 1 OF 1	