



GARDTEC

Part Number:

GHP50-24 ("90" Plug)

Wire: **SPT1 2 conductor 105°C, 300 volts**

Length: **24"**


Thermostat:


Designed to turn AC fan on as ambient temperature approaches 88°F (-3/+5), turns off fan as ambient temperature moves below 80°F, cycle life 6,000.

Other options:

- **custom lengths**
- **terminal connections (any)**
- **heat shrink**
- **labeling**
- **stripping**
- **tinning**
- **complete wire harness assemblies**
(rated at 105°C, 300 volts)

Listings:

 UL listed E156798
Rated 10 AMP/125 VAC

 CSA listed (LR76679-1)
Rated 7 AMP/125 VAC

