

universal enclosure Spacial 3D steel enclosure

Accessories selection guide page 19052/2

Dimensions page 19068/2



external dimensions			no. of doors	universal enclosure reference				glazed door		sheet thickness (mm)
height	width	depth		plain door		with plain chassis		without chassis	weight (kg)	
300	200	150	1	83015	3	83315	3.5	—	—	
		300	1	83002	3.5	83302	4.5	83502	3.5	
	200	1	83003	4	83303	5	83503	4.5		
400	300	150	1	83012	4.5	83312	6	83512	5	
		200	1	83017	4.5	83317	6	83517	4.5	
	200	1	83018	5	83318	6.5	83518	5.5		
	400	1	83019	6.2	83319	8	83519	6.5		
	600	1	83031	10	83331	13	83531	10.5		
	250	1	83032	10.5	83332	13.5	83532	11		
500	300	200	1	83021	7.5	83321	9	83521	8	
		400	1	83023	9	83323	11.5	83523	9.5	
	250	1	83024	10	83324	12	83524	10		
	500	1	83022	10.5	83322	13	83522	10.5		
	250	1	83025	11.5	83325	14.5	83525	12		
600	400	200	1	83026	10.5	83326	13.5	83526	11	
		250	1	83027	11.5	83327	14	83527	12	
	600	1	83028	14	83328	18	83528	14		
	250	1	83029	15	83329	19.5	83529	15.5		
	300	1	83030	16.5	83330	21	83530	16.5		
	400	1	83039	18.5	83339	23	83539	19		
800	1	83037	25	83337	30.5	83537	25			
700	500	250	1	83035	15	83335	19.5	83535	15.5	
800	600	200	1	83043	21.5	83343	27.5	83543	21.5	
		250	1	83056	23.5	83356	29	83556	23.5	
	300	1	83057	25	83357	31	83557	25		
	400	1	83044	28.5	83344	34.5	83544	29		
	800	1	83045	28.5	83345	39.8	83545	29		
	300	1	83046	30.8	83346	41.8	83546	31		
1000	300	1	83047	36.5	83347	50.5	—	—		
1000	600	250	1	83054	28	83354	38.5	83554	28.5	
		400	1	83059	39	83359	44	83559	34	
	800	1	83060	34.5	83360	48.5	83560	34.5		
	300	1	83061	36.5	83361	50.5	83561	36		
	400	1	83062	41	83362	55	83562	41		
1000	300	1	83070	43.5	83370	65	83570	43		
1200	300	2*	83063	44.5	83363	66	83563	44		
1200	300	2*	83066	52	83366	77.5	—	—		
1200	800	300	1	83064	43	83364	63	83564	42	
		400	1	83067	47.5	83367	68	83567	47	
	1000	1	83071	50.5	83371	76	83571	50		
	300	2*	83065	52	83365	77.5	83565	51		

* 2 door enclosures are protection IP 55.

customized offer



page 19071/2

specific offer



page 19070/2