

RockStar® Housings IP65 / NEMA Type 4X

Side locking, lower side

Size 8


Hood



Hood, Cable Entry sideways



a	Version	Cover	b (mm)	Designation	Order No.
M25	with thread		61	HDC 24B TSBU 1M25G	1787760000
M25	with thread		76	HDC 64D TSBU 1M25G	1786780000
M32	with thread		61	HDC 24B TSBU 1M32G	1787750000
M32	with thread		76	HDC 64D TSBU 1M32G	1786770000
M40	with thread		61	HDC 24B TSBU 1M40G	1902480000
PG 21	with thread		61	HDC 24B TSBU 1PG21G	1661230000
PG 21	with thread		76	HDC 64D TSBU 1PG21G	1661300000
PG 29	with thread		61	HDC 24B TSBU 1PG29G	1661240000
PG 29	with thread		76	HDC 64D TSBU 1PG29G	1661320000




D

Hood, Cable Entry at top




a	Version	Cover	b (mm)	Designation	Order No.
M25	with thread		61	HDC 24B TOBU 1M25G	1787820000
M32	with thread		61	HDC 24B TOBU 1M32G	1787810000
M32	with thread		76	HDC 64D TOBU 1M32G	1786830000
M40	with thread		61	HDC 24B TOBU 1M40G	1902980000
PG 21	with thread		61	HDC 24B TOBU 1PG21G	1661370000
PG 21	with thread		76	HDC 64D TOBU 1PG21G	1661440000
PG 29	with thread		61	HDC 24B TOBU 1PG29G	1661380000
PG 29	with thread		76	HDC 64D TOBU 1PG29G	1661460000



Cover



Version	Designation	Order No.
for hoods	HDC 24B DMDQ 2QB	1665640000



Side locking, lower side

Size 8




Base

Bulkhead housing




Version	Cover	b (mm)	Designation	Order No.
	without cover	29.3	HDC 24B ABU	1212400000



Base housing




a	Version	Cover	b (mm)	Designation	Order No.
M25	with thread	without cover	64	HDC 24B SBU 1M25G	1901150000
M25	with thread	without cover	84	HDC 64D SBU 1M25G	1904340000
M25	with thread	without cover	64	HDC 24B SBU 2M25G	1787870000
M25	with thread	without cover	84	HDC 64D SBU 2M25G	1786890000
M32	with thread	without cover	84	HDC 64D SBU 1M32G	1904350000
M32	with thread	without cover	84	HDC 64D SBU 2M32G	1786880000
PG 21	with thread	without cover	64	HDC 24B SBU 1PG21G	1661510000
PG 21	with thread	without cover	64	HDC 24B SBU 2PG21G	1661520000
PG 21	with thread	without cover	84	HDC 64D SBU 2PG21G	1661590000
PG 29	with thread	without cover	84	HDC 64D SBU 2PG29G	1661630000



Coupling hood



a	Version	Cover	b (mm)	Designation	Order No.
M25	with thread		65	HDC 24B KBU 1M25G	1787920000
M32	with thread		79	HDC 64D KBU 1M32G	1786960000
PG 21	with thread		65	HDC 24B KBU 1PG21G	1661720000
PG 29	with thread		65	HDC 24B KBU 1PG29G	1661730000
PG 29	with thread		79	HDC 64D KBU 1PG29G	1661810000



Cover



Version	Designation	Order No.
for bases	HDC 24B DODQ 4B0	1665630000

