



## SPECIFICATION

CONTACT FORM/STYLE		Changover
SWITCHING VOLTAGE	Max. Vac	175
SWITCHING CURRENT	Max. A	0.5
SWITCHING CAPACITY (RESISTIVE)	Max. VA	5
CONTACT RESISTANCE	Max. mΩ	150
SWITCHING DISTANCE	Min. mm	5.0
OPERATING TEMPERATURE		
CONTINUOUS	Deg. °C	-20° + 85°
INTERMITTENT	Deg. °C	-20° + 105°
STORAGE TEMPERATURE	Deg. °C	-25° +90°
CASE MATERIAL		Nylon 66

This product is fully sealed to give maximum mechanical protection and minimise the ingress of dust and moisture. As a guide, the product is expected to meet the requirements of IP65.

### PROXIMITY - Reed Switch - Rectangular - Plastic

PART NUMBER  
**PSC 175/30**

Rev. No.	Revision Note	Date	Signature
E	Web Site 2003	14-2-01	RG

The Comus Group of Companies consist of:  
Assemtech Europe Limited  
E. Bachem GmbH  
Comus International  
W. Gunther GmbH  
Gunther Belgium  
Gunther France  
S.I.G.

As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and details of our full design and manufacturing service. All products are supplied to our standard conditions of sale otherwise agreed in writing.