

# SUPER MICRO CONNECTORS



SERIES

# 5047

## プラグ(H=5.0mm)

## Plug (H=5.0mm)

金具無 without metal



### 注文コード Ordering Code

嵌合高さ STACKING HEIGHT	型番 P/N					
5.0mm	FEMALE	24	5047	XXX	X00	XXX
	MALE	14	5047	XXX	X50	XXX

極数 NO. OF POS.		寸法 DIMENSION B	VARIATION CODE	FINISH CODE
9	020	7.5	9 吸着テープ付 WITH VACUUM TAPE	接触部 CONTACT AREA
4	030	10.0	4 吸着テープ無 WITHOUT VACUUM TAPE	
	040	12.5		856 Au 0.1 μm/ MIN
	050	15.0		861 Au 0.2 μm/ MIN
	060	17.5		
	070	20.0		
	080	22.5		
	090	25.0		
	100	27.5		

# SUPER MICRO CONNECTORS




SERIES

# 5047


## プラグ(H=7.0mm)

## Plug (H=7.0mm)


金具無 without metal



嵌合高さ  
STACKING HEIGHT  
H=7mm TYPE




FEMALE : 24 5047 XXX X00 XXX



MALE : 14 5047 XXX X70 XXX

極数 NO. OF POS.	A	B	C
20	4.5	7.5	0.25
30	7.0	10.0	0.5
40	9.5	12.5	0.25
50	12.0	15.0	0.5
60	14.5	17.5	0.25
70	17.0	20.0	0.5
80	19.5	22.5	0.25
90	22.0	25.0	0.5
100	24.5	27.5	0.25



基板取付け寸法  
MOUNTING LAYOUT

### 注文コード Ordering Code

嵌合高さ STACKING HEIGHT	型番 P/N					
7.0mm	FEMALE	24	5047	XXX	X00	XXX
	MALE	14	5047	XXX	X70	XXX

極数 NO. OF POS.	寸法 DIMENSION B
020	7.5
030	10.0
040	12.5
050	15.0
060	17.5
070	20.0
080	22.5
090	25.0
100	27.5

### VARIATION CODE

9	吸着テープ付 WITH VACUUM TAPE
4	吸着テープ無 WITHOUT VACUUM TAPE

### FINISH CODE



接触部 CONTACT AREA	
856	Au 0.1 μm/ MIN
861	Au 0.2 μm/ MIN

# SUPER MICRO CONNECTORS

SERIES



# 5047

## プラグ エンボス(H=5.0, 7.0mm) Plug Tape and Reel Package (H=5.0, 7.0mm)



HEIGHT	G
H=5.0	4.8
H=7.0	6.8

	種数 NO. OF PCS.	A	B	C	D
32mm TAPE	20	7.5	26.5	28.4	32.0
	30	10.0			
	40	12.5			
	50	15.0			
	60	17.5			
44mm TAPE	70	20.0	38.5	40.4	44.0
	80	22.5			
	90	25.0			
	100	27.5			



HEIGHT	G
H=5.0	4.8
H=7.0	6.8

	種数 NO. OF PCS.	A	B	C	D
32mm TAPE	20	9.5	26.5	28.4	32.0
	30	12.0			
	40	14.5			
	50	17.0			
	60	19.5			
44mm TAPE	70	22.0	38.5	40.4	44.0
	80	24.5			
	90	27.0			
	100	29.5			


# SUPER MICRO CONNECTORS

SERIES

# 5047

リセ(H=5.0, 7.0mm)  
Receptacle (H=5.0, 7.0mm)

金具無 without metal



## 注文コード Ordering Code

嵌合高さ STACKING HEIGHT		型番 P/N				
5.0mm	FEMALE	24	5047	XXX	X00	XXX
	MALE	14	5047	XXX	X50	XXX
7.0mm	FEMALE	24	5047	XXX	X00	XXX
	MALE	14	5047	XXX	X70	XXX

極数 NO. OF POS.	寸法 DIMENSION B
020	7.5
030	10.0
040	12.5
050	15.0
060	17.5
070	20.0
080	22.5
090	25.0
100	27.5

**VARIATION CODE**

4	吸着テープ無 WITHOUT VACUUM TAPE
---	-------------------------------

**FINISH CODE**

	接触部 CONTACT AREA
856	Au 0.1 μm/ MIN
861	Au 0.2 μm/ MIN



# SUPER MICRO CONNECTORS

SERIES



# 5047

## リセ エンボス

## Receptacle Tape and Reel Package



	極数 NO. OF POS.	A	B	C	D
32mm TAPE	20	7.5	26.5	28.4	32.0
	30	10.0			
	40	12.5			
	50	15.0			
	60	17.5			
44mm TAPE	70	20.0	38.5	40.4	44.0
	80	22.5			
	90	25.0			
	100	27.5			



	極数 NO. OF POS.	A	B	C	D
32mm TAPE	20	9.5	26.5	28.4	32.0
	30	12.0			
	40	14.5			
	50	17.0			
	60	19.5			
44mm TAPE	70	22.0	38.5	40.4	44.0
	80	24.5			
	90	27.0			
	100	29.5			