






Model 56

Window Diameter 2.06"



| Catalogue Number | Current Ratio | Accuracy at 60Hz | Burden VA at 60Hz |
|------------------|---------------|------------------|-------------------|
| 56 **-500 | 50:5 | ± 3% | 0.5 |
| 56 **-750 | 75:5 | ± 1% | 0.5 |
| 56 **-101 | 100:5 | ± 1% | 1.0 |
| 56 **-151 | 150:5 | ± 1% | 2.5 |
| 56 **-201 | 200:5 | ± 1% | 4.0 |
| 56 **-251 | 250:5 | ± 1% | 6.0 |
| 56 **-301 | 300:5 | ± 1% | 7.5 |
| 56 **-401 | 400:5 | ± 1% | 10.0 |
| 56 **-501 | 500:5 | ± 1% | 12.5 |
| 56 **-601 | 600:5 | ± 1% | 15.0 |
| 56 **-751 | 750:5 | ± 1% | 7.0 |
| 56 **-801 | 800:5 | ± 1% | 8.0 |
| 56 **-102 | 1000:5 | ± 1% | 10.0 |
| 56 **-122 | 1200:5 | ± 1% | 12.5 |

****NOTE:** When ordering, prefix Catalogue Number with model designation required, i.e. 56RL - 101.

Application

With ammeters, wallmeters and cross current compensation.

Frequency


50-400Hz

Insulation Level

0.6kV, 10kV full wave

- Flexible leads are UL 1015 105°C, CSA approved #16 AWG, 24" long
- Non-standard length to be specified.
- Terminals are brass studs No. 8 - 32 UNC with one flat washer, lockwasher and regular nut
- SFT case style also available as SFL with leads
- Approximate weight: 0.6 lb

Approvals

CSA  **US** UL 257877
CSA 223647