


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|---|---------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE-COURTESY COPY TO CUSTOMER | 3/29/10 | D.GRIFFIN |
| | | | |
| | | | |



| LENGTH CODE CHART | | |
|-------------------|--------------------------------------|----------------------------|
| CABLE# & LENGTH | LENGTH SYMBOL | EXAMPLES OF PART# USED |
| CA-QPRQJBAXXX | WHERE XXX = LENGTH IN FEET | CA-QPRQJBA010 (10 FEET) |
| CA-QPRQJBANXX | WHERE NXX = LENGTH IN INCHES | CA-QPRQJBAN16 (16 INCHES) |
| CA-QPRQJBAMXX | WHERE MXX = LENGTH IN METERS | CA-QPRQJBAM07 (7 METERS) |
| CA-QPRQJBAXMX | WHERE MXM = LENGTH IN DECIMAL METERS | CA-QPRQJBA3M5 (3.5 METERS) |

RoHS Compliant ✓

NOTES:

CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

| | | | | | |
|--|--|---------------------------------------|--|--|------------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005 | APPROVALS DRAWN BY D.FRISIELLO CHECKED BY C.BRAN APPROVED BY K.BURGNER | DATE 3/26/10 3/26/10 3/26/10 | 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 | | |
| | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | CATEGORY COAXIAL | | PRODUCT DESCRIPTION CA, 195 QMA RA P/QMA J BKHD | |
| PROJECTION | COLOR VARIATIONS MAY OCCUR | SIZE A | FSCM NO. 43321 | DWG. NO. CA-QPRQJBA | REV. A |
| | | SCALE: NONE | CAD FILE: CA-QPRQJBA.SLDDRW | SHEET 1 OF 1 | |