

11 Wire Strippers



11 01 160



11 02 160



11 05 160



11 06 160




- ▶ for single, multiple and fine stranded conductors with plastic or rubber insulation max. 5.0 mm dia. or resp. 10.0 mm² cable cross section
- ▶ easy adjustment to the required diameter of solid or stranded wire with knurled screw and lock nut
- ▶ special tool steel, oil-hardened and tempered

Style 0:

- ▶ with opening spring

Style 1:

- ▶ without opening spring



Article-No.	EAN-Code	Style	Head	Handles	Stripping capacities			
					∅ mm	mm ²	AWG	g
11 01 160	013556	0 MMMM	polished	plastic coated	5.0	10.0	7	135
11 02 160	023180		polished	with two-colour dual component handles				160
11 05 160	039570		chrome plated	with two-colour dual component handles				160
11 06 160	021933		chrome plated	insulated with two-colour dual component handles				165
11 07 160	015499		chrome plated	plastic dipped insulated	▲ 1000 V	▲ VDE-tested		195
11 12 160	034964		1	polished	with two-colour dual component handles			160
11 15 160	042471	chrome plated		with two-colour dual component handles			160	
11 17 160	015505	chrome plated		plastic dipped insulated			195	
		▲ 1000 V		▲ VDE-tested				