

16 Dismantling Tool



16 40 150

- ▶ for dismantling round cables exceeding 25.0 mm dia.
- ▶ removes all kinds of insulation layers
- ▶ suitable for longitudinal and circular cutting
- ▶ cutting depth can be adjusted up to 5 mm
- ▶ replaceable blade (both sides can be used)

- ▶ tool body made of fibreglass reinforced polyamide



Adjustable cutting depth

Article-No.	EAN-Code	Handles	Stripping capacities		
			Length mm	ø mm	ø Inch g
16 40 150	026709	fibreglass reinforced polyamide		for round cables over 25.0	1.0 210
16 49 150	026716	spare blade			



Setting the tool for longitudinal cut



Longitudinal cut



Turning the tool for circular cut



Circular cut

16 Coax-Stripping Tool




16 60 05 SB



- ▶ for stripping Coax-cables (RG 58, RG 59 and RG 62)
- ▶ for stripping outer sheath, shield and dielectricum in one operating cycle
- ▶ with three built-in blades
- ▶ the cutting depth of each blade can be adjusted individually by means of a hexagonal Key (Allen Key)
- ▶ the blade spacing remains constant
- ▶ tool body made of plastic



3 stripping steps in one operation



Dismantling of a Coax-cable in three steps

Article-No.	EAN-Code	Cabel	Stripping capacities	
			Length mm	g
16 60 05 SB	044888	RG 58, RG 59 and RG 62	105	65