

20 Flat Nose Pliers

DIN ISO 5745

- ▶ short, flat jaws
- ▶ serrated gripping surfaces
- ▶ special tool steel, oil-hardened and tempered



20 01 160



20 02 160



20 05 160



20 06 160



Article-No.	EAN-Code	Head	Handles	Dimensions			⚖	
				L3	W3	T1		
	Length							
	mm	4003773-		mm	mm	mm	g	
20 01	125	014447	polished	plastic coated	27.0	14.5	8.0	80
	140	014454			28.0	15.5	9.5	110
	160	015017			30.0	17.0	9.5	140
	180	015666			35.0	19.0	10.0	190
	200	015673			38.0	21.0	12.0	275
20 02	140	043386	polished	with two-colour	28.0	15.5	9.5	145
	160	035008		dual component handles	30.0	17.0	9.5	170
20 05	140	042464	chrome	with two-colour	28.0	15.5	9.5	145
	160	042457	plated	dual component handles	30.0	17.0	9.5	170
20 06	160	033783	chrome	insulated with two-colour	30.0	17.0	9.5	175
			plated	dual component handles				

