

97

97 Crimping Plier



97 32 225



- ▶ for cutting cables, stripping wire and crimping insulated and non-insulated terminals and connectors
- ▶ with threaded holes for cutting copper and brass screws threaded M 2.6; 3.0; 3.5; 4.0 and 5.0 mm
- ▶ high strength special grade steel

Article-No.	EAN-Code	Head	Handles	Range of Application	Capacity		⚖
					mm ²	AWG	
97 32 225	019718	burnished	with plastic handles	 insulated terminals and plug connectors  non-insulated terminals and plug connectors	0.5 - 6.0	20 - 10	240

97

97 Insertion Tool for LSA-Plus and identical



97 40 10

- ▶ tool for putting on boards, sockets and fields
- ▶ pushing down and cutting in one operation
- ▶ for UTP and STP cables, conductor 0.4 - 0.8 mm dia.
- ▶ with integrated pulling hook and release blade
- ▶ plastic body



Insertion tool to connect without having to strip



Putting down and cutting the cable in one operation



Article-No.	EAN-Code	Body	Range of Application	Capacity			⚖
				ø mm	Length mm	g	
97 40 10	044895	plastic	UTP- and STP-cables, LSA-Plus and identical	0.4 - 0.8	175	95	