

98 Dismantling Knife



98 53 03



1000 V
IEC 60900
DIN EN 60900

- ▶ solid, fixed hook blade
- ▶ blade oil-hardened and tempered
- ▶ ergonomically shaped safety handle
- ▶ transparent protective cap
- ▶ VDE tested according to DIN EN/IEC 60900

Article-No.	EAN-Code	Blade length	Radius	Length	g
98 53 03	026549	28	7	155	70



with protective cap

98 Dismantling Knife



98 53 13



1000 V
IEC 60900
DIN EN 60900

- ▶ narrow, fixed hook blade, sickle shaped
- ▶ suitable for sector cables
- ▶ blade oil-hardened and tempered
- ▶ ergonomically shaped safety handle
- ▶ transparent protective cap
- ▶ VDE tested according to DIN EN/IEC 60900

Article-No.	EAN-Code	Blade length	Radius	Length	g
98 53 13	026556	50	40	180	70



with protective cap

98 Cable Knife



98 54



1000 V
IEC 60900
DIN EN 60900

- ▶ solid, fixed straight blade
- ▶ blade oil-hardened and tempered
- ▶ back of the blade plastic coated to avoid short circuit
- ▶ ergonomically shaped safety handle
- ▶ transparent protective cap
- ▶ VDE tested according to DIN EN/IEC 60900

Article-No.	EAN-Code	Blade length	Length	g
98 54	026563	50	180	75



with protective cap

98 Dismantling Knife



98 55



1000 V
IEC 60900
DIN EN 60900

- ▶ solid, fixed hook blade, sickle shaped
- ▶ with guide shoe at the blade point
- ▶ no damage of the conductor insulation
- ▶ blade made of stainless steel, vacuum hardened
- ▶ ergonomically shaped safety handle
- ▶ transparent protective cap
- ▶ VDE tested according to DIN EN/IEC 60900

Article-No.	EAN-Code	Blade length	Length	g
98 55	022558	38	155	90



with protective cap