

Part Number	27L946
Suffix	
Lead Time	Standard
Microfarad (uF) Single/1st	40
Microfarad (uF) Dual/2nd	5
Voltage Rating	440
Case Diameter (in)	2.5
Style of Case	Round
Case Height (in)	2.88
EIA Base Code	T
Brand	Genteq
Required Operation Life (Hrs)	60000
Operating Temperature (C)	-40°C to 70°C
Product Type	Oil-Filled (UL Approved)
Stud	No Stud
Special Features 1	
Special Features 2	

Model Suffixes:

S = Stock Item

RC / RR = Capacitor contains a bleed resistor

BX = Capacitor is individually boxed for resale

BR = Capacitor is individually boxed for resale and contains a bleed resistor

<http://www.thecapacitortoolbox.com>