

Twist-Lock® Devices

30 Ampere, 3Ø Y 120/208, 277/480 and 347/600 Volts AC

4 Pole, 5 Wire Grounding

Insulgrip® Connector Bodies and Receptacles



30A 3ØY
120/208V AC
NEMA L21-30R
UL/CSA
3 HP



30A 3ØY
277/480V AC
NEMA L22-30R
UL/CSA
10 HP



30A 3ØY
347/600V AC
NEMA L23-30R
UL/CSA

Connector Bodies

Watertight Safety-Shroud®		IP66 SUITABILITY		
Description	Cord Dia.	Catalog Numbers		
Black Valox® housing, white Valox® clamps.	.35"-1.15" (9-29)	HBL2813SW	-	-

Insulgrip		IP20 SUITABILITY		
Description	Cord Dia.	Catalog Numbers		
Black and white nylon.	.35"-1.15" (9-29)	HBL2813	HBL2823	HBL2833
Corrosion resistant, yellow nylon.	.35"-1.15" (9-29)	HBL28CM13	-	-
Black and white for flat cable.	.35"-1.15" (9-29)	HBL2813FC	-	-
All black nylon.	.35"-1.15" (9-29)	HBL2813BK	-	-

Accessories on page B-53.



HBL2813SW



HBL2813

Receptacles

Watertight Safety-Shroud, Back Wired		IP66 SUITABILITY		
Description	Catalog Numbers			
Gray Valox® housing and flange.	HBL2810SW - - -			

Safety-Shroud Twist-Lock, Back Wired		IP20 SUITABILITY		
Description	Catalog Numbers			
Gray Valox® angle housing, one gang.	HBL2810AR - - -			
Gray Valox® surface mounting, one gang.	HBL2810SR - - -			
Gray Valox® semi-flush, two gang.	HBL2810SR2 - - -			

Accessories on page B-54.



HBL2810SW

Single Flush, Back and Side Wired		IP20 SUITABILITY		
Description	Catalog Numbers			
Black nylon face.	HBL2810 HBL2820 HBL2830			
Isolated ground, orange nylon face.	IG2810 - - -			
Ring terminal connection.	HBL2810RT - - -			


Accessories on page B-52.




HBL2810AR

Insulgrip Flanged Receptacles		Catalog Numbers		
Nylon casing, back wired.	HBL2816 HBL2826 HBL2836			


Accessories on page B-52.



HBL2816



HBL2810



HBL2810SR2



HBL2810SR

Valox® is a trademark of SABIC Innovative Plastics, acquired from General Electric Company.

