



SPECIFICATION

SWITCHING VOLTAGE	Max. Vac	240
SWITCHING CURRENT	Max. A	0.50
SWITCHING CAPACITY	Max. VA	10
CONTACT RESISTANCE	Max. mΩ	150
DIFFERENTIAL ANGLE	Max. Deg.°	90
OPERATING TEMPERATURE	Deg. °C	-20° +70°
STORAGE TEMPERATURE	Deg. °C	-20° +70°
CASE MATERIAL		ABS
MECHANICAL LIFE	Min.	10 ⁵

These switches are sensitive to magnetic fields and ferrous materials. Care should be taken when housing. Switches should not be fitted to ferrous materials.

TILT SWITCH ASSEMBLIES

PART NUMBER
MTA 240

Rev. No.	Revision Note	Date	Signature
A	1998 Catalogue Page 21	1-4-98	RG



BS5750/ISO 9000
Reg. No. FM 21080