

TOWERSTAT THERMOSTATIC RADIATOR VALVE SPECIFICATIONS



Specification

- Fully reversible - For flow or return
- Vertical or horizontal head
- Range 8°C to 32°C
- Easy fit to suit 8, 10 or 15 mm
- Wax sensor
- Chrome plate body
- Frost protection setting
- Standard 1/2" tail
- Maximum working pressure 10 bar
- Push fit head fitting
- Pre coated PTFE tails

