



TENMA®

72-8710 PRODUCT SPECIFICATIONS

Feature	
Bandwidth	100 MHz
Rise Time	≤3.5 ns
Real-time Sampling Rate	1GS/s
Equivalent Sampling Range	50GS/s
Vertical Sensitivity	1mV ~ 20V/div
Record Length (Max)	2 x 600k
Scan Time Base	2ns ~ 50s/div
Trigger Type	Edge, Pulse, Alternate
Automatic Waveform Measurements	28
Frequency Counter	6 digits frequency counter
Ports	USB OTG
Mathematics	Add, Subtract, Multiply, Divide, FFT
Other Features	Special Print Screen Feature

GENERAL CHARACTERISTICS

Power	100 - 240VACRMS, 45Hz -440Hz, CAT II
LCD Size	Diagonal 178mm (7 inches)
Product Net Weight	2.2kg
Product Size	306mm x 147mm x 122mm
Accessories	Probe x 2 (1x, 10x switchable), Power Cord and English Manual UT-D05 USB Cable, PC Communication Software
Standard Individual Packing	Gift Box
Standard Quantity Per Carton	2 pcs
Standard Carton Measurement	445 x 410 x 270mm (0.055 CBM Per Export Carton)
Standard Carton Gross Weight	Around 8.5kg

Specifications and other information are subject to change without further notice