





D Anschluss **ausschließlich** durch ausgebildete Elektro-Fachkräfte.
GB Electrical connection is to be made by trained electrical specialists **only**.
F Le branchement doit **uniquement** être effectué par des professionnels.
I Il collegamento deve essere eseguito **solo** da elettricisti specializzati.
E La conexión **sólo** debe ser realizada por electricistas debidamente formados.
PT A ligação deve ser feita **exclusivamente** por profissional eléctrico especializado.
CZ Připojení smí **provádět** pouze kvalifikovaný personál.
PL Podłączenie **wyłącznie** przez specjalistów-elektryków.
FI Liittäminen kuuluu **ainoastaan** koulutettujen sähköalan ammattilaisten tehtäviin.
RUS Подключение проводится только специалистом-электриком.
TR Bağlantı **sadece** eğitimli elektrik teknisyenleri tarafından yapılmalıdır.
CN 布线需由专业电工执行








641 x00 00	12 – 240 V~
642 x00 75	24 V~, 100 mA
642 x00 77	115 V~, 20 mA
642 x00 78	230 V~, 10 mA
643 x00 55	24 V~, 125 mA
643 x00 67	115 V~, 20 mA
643 x00 68	230 V~, 15 mA
644 x20 55	24 V~, <30 mA (RD, YE)
644 x20 55	24 V~, <35 mA (GN, BU, CL)
644 x00 75	24 V~, <30 mA (RD, YE)
644 x00 75	24 V~, <25 mA (GN, BU, CL)
644 x00 67	115 V~, <20 mA
644 x00 68	230 V~, <20 mA
644 x10 75	24 V~, 60 mA
644 x30 75	24 V~, 70 mA
644 x40 55	24 V~, 200 mA (RD, YE)
644 x40 55	24 V~, 150 mA (GN, BU, CL)
645 800 75	85 dB, 24 V~, 25 mA
645 800 77	85 dB, 115 V~, 25 mA
645 800 68	85 dB, 230 V~, 25 mA
645 820 75	100 dB, 24 V~, 80 mA
645 820 67	100 dB, 115 V~, 40 mA
645 820 68	100 dB, 230 V~, 40 mA
645 850 55	100 dB, 24 V~, 80 mA
645 830 55	105 dB, 24 V~, 100 mA, (IP40)
645 810 55	24 V~, <150 mA, $I_0 < 500 \text{ mA}$
BA 15 d	
956 x00 75	24 V~, 45 mA
956 x00 67	115 V~, 15 mA
956 x00 68	230 V~, 15 mA
BA 15 d, < 42 mm	
955 840 34	12 V, 5 W
955 840 35	24 V, 5 W
955 840 37	115 V, 7 W
955 840 38	230 V, 5 W
955 840 57	115 V, 5 W





644 x40 55	
D Bei Epilepsie ungeeignet!	
GB Unsuitable for epilepsy sufferers	
F Ne convient pas aux personnes souffrant d'épilepsie	
I Inadatto per epilettici	
E Inadecuado para epilépticos	
PT Não aconselhável a pessoas que sofram de Epilepsia	
CZ Nevhodné pro epileptiky	
PL Nie stosować przy zchorzeniu padaczki	
FI Ei sovellu epileptikoille	
RUS Не подходит для страдающих эпилепсией	
TR Epilepsi hastalığı olanların kullanmaması önerilir	
CN 不适用于癫痫病患者	









- 1**
- 1a - 648 800 00, 648 820 00
 - 1b - 975 840 85, 975 840 86
 - 1c - 975 840 10, 975 840 90, 975 840 91
 - 1d - 960 000 01, 960 000 02



- 3**
- 3a - 640 820 00, 640 830 00
 - 3b - 640 800 00, 640 810 00



- 4**
- 4a - 640 800 00, 640 820 00
 - 4b - 640 800 00, 640 820 00 + 960 000 02
 - 4c - 640 810 00, 640 830 00 + 975 840 10
 - 4d - 975 840 10, ..., + 960 000 01



310.640.001.0708

© (D)

 **WERMA**
SIGNALTECHNIK