

PTFE Insulated, Twin Twisted Pair Types: K, J & T



- Single pair of solid conductors twisted
- PTFE Insulated 1/0.2
- Thermocouple types K, J and T
- Available on 25, 50 & 100mt reels
- Tolerance Class 1 for optimum accuracy
- Insulation Rating -75°C to 260°C
- IEC Colour coded

Length/Type	FARNELL code	Labfacility code	Lab Stock Code
25m K	335-8161	WK-200 x25	XF-243-FAR
50m K	163-3495	WK-200 x50	XF-536-FAR
100m K	163-3497	WK-200 x100	XF-537-FAR
25m T	335-8173	WT-300 x25	XF-244-FAR
50m T	163-3498	WT-300 x50	XF-538-FAR
100m T	163-3499	WT-300 x100	XF-539-FAR
25m J	358-8150	WJ-244 X 25	XF-242-FAR

Data Ref: FAR86 A-G