

## Mini Stripping Tool



12 80 100 SB



- Description
- precise stripping because of the tool's stepwise adjustment to the conductor's diameter
- with wire cutter
- adjustable length stop from 4.0 - 15.0 mm
- with locking device
- Housing: plastic, impact-resistant

Model 12 80 040 SB :

- for thin copper conductors dia. 0.12 to 0.4 mm

Model 12 80 100 SB :

- for thin copper conductors dia. 0.3 to 1.0 mm

No.	EAN 4003773-	Stripping capacities Ø mm	AWG	↔ mm	⚖ g
12 80 040 SB <b>N</b>	071655	0,12 - 0,4	36 - 26	100	52
12 80 100 SB <b>N</b>	043119	0,3 - 1,0	28 - 18	100	34

**N** New

**N** Upgrade

technical change and errors excepted