






ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
			AMU	25-10-10	JAG	25-10-10	XXX	04-11-10

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398



Dimensions : inches (mm)

Notes:

- Material : C1008 steel
- Plating : Bright nickel chrome
- Ring diameter : 2.4mm & 1.5mm
- Rib diameter : 2.4mm

Part Number Table

Description	Part Number
Wire Fan Guard	MC32655

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:

AMU

DATE:

25-10-10

CHECKED BY:

JAG

DATE:

25-10-10

APPROVED BY:

XXX

DATE:

04-11-10

DRAWING TITLE:

Wire Form Fan Guard

SIZE DWG. NO.

A MC32655

ELECTRONIC FILE

56P2932

SCALE:

NTS

U.O.M.: Millimeters

SHEET:

1 OF 1

DISCLAIMER:

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

REV

A