



Wind Speed Meter - Anemometer

tel: +44 (0)1946 816600

fax: +44 (0)1946 816625

email: sales@brannan.co.uk

web: www.brannan.co.uk



An easy to use, hand held, electronic instrument giving an accurate wind speed measurement and ambient temperature.

Product Features:

- Wind speed measure in mph, ft/min, Km/h, m/s or knots
- Wind speed in Beaufort wind scale bar graph
- Wind chill display
- Temperature display in Celsius or Fahrenheit
- LCD back light
- Auto power off
- Neckband included
- 3V lithium battery operation

Product Specifications:

Wind Speed Range				
Unit	Range	Resolution	Threshold	Accuracy
m/s	0 to 30	0.1	0.1	±5%
ft/min	0 to 5860	19	39	±5%
knots	0 to 55	0.2	0.1	±5%
km/hr	0 to 90	0.3	0.3	±5%
mph	0 to 65	0.2	0.2	±5%
Temperature Range				
Unit	Range	Resolution	Accuracy	
°C	-10 to +45°C	0.2	±2°C	
°F	14 to 113°F	0.36	±3.6°F	
Battery		CR2032.30V		
Bearing		Sapphire bearing		
Thermometer		NTC thermometer		
Operating Temperature		-10 to +45°C (-14 to 113°F)		
Operating Humidity		≤90% RH		
Store Temperature		-40 to +60°C (-40 to 140°F)		
Current Consumption		Approx 3 m A		
Weight		52g (including battery and lanyard)		
Product Number		13/430/0		



S Brannan & Sons Ltd

Leconfield Industrial Estate • Cleator Moor • Cumbria • CA25 5QE • UK

